

## Overview

The Cabling123® can offer 10G SFP+ SR optical transceiver. These optical transceiver module are designed for use in 10 Gigabit Ethernet links over multimode fiber, using a wavelength of 850nm via a LC duplex connector. This optical transceiver have a wide variety of high-density and low-power 10 Gigabit Ethernet connectivity options for data center, high-performance computing networks, enterprise core and distribution layers, and service provider applications.



## Features & Benefits

- Hot pluggable SFP+ form factor.
- Supports 10 Gb/s aggregate bit rate.
- LC duplex receptacle.
- +3.3V single power supply.
- Low power consumption.
- Support DDM.
- Generic compatible.
- Compliant to MSA, RoHS standard.

## Applications

- 10 Gigabit Ethernet.
- InfiniBand QDR, EDR.
- Switch / Router /HBA.
- Enterprise network SAN.
- Data storage and communication industry.
- Data center network.

## Specification

Parameter	Value
Form Type	SFP+
Connector Type	LC duplex
Maximum Distance	400 m @ OM4 MMF
Supported Data Rate	10 Gb/s
Wavelength(nm)	850
Output Power	Min: -7 dBm; Max: -1 dBm
Extinction Ratio	Min: 3dB;
Receiver Sensitivity	Max: -10 dBm
H x W x D (mm)	11.3 x 13.7 x 56.7
Weight (g)	20
Storage Temperature	-40 °C ~ 85 °C
Operatig Temperature	0 °C ~ 70 °C
Humidity	5%RH ~ 85%RH

## Product Selection

Part Number: C77-S010-SR

## Standards Compliance

- SFF-8432.
- IEEE Std802.3.
- RoHS.

