


# **Power OFF-delay Timer**

# **Order Code**




### **Technical criteria**

Rated supply voltage	24 to 48 VAC/DC, 50/60 Hz	
Operating mode	OFF delay	
Input method	None	
Minimum power-ON time	0.1 s	
Control Output	5 A at 250 VAC with resistive load (cosφ = 1),	
	5 A at 30 VDC with resistive load	
Accuracy of operating time	±1% of FS max. (±1% ±10 ms max. at 1.2-s range)	
Setting error	±10% of FS ±0.05 s max.	
Operating Temperature	-20 to 60°C	
Operating Humidity	25% to 85%	
IP	IP30 (Terminal block: IP20)	

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

#### **Nomenclature**




1	Power indicator
2	Time range switch
3	Main dial

## Time range


Time range setting	x0.1	x1
Set time range	0.1 to 1.2 s	1 to 12 s
Power ON time	0.1 s min.	
Scale numbers	12	

## **Timing Chart**



Note: Refer to the official Datasheet, how to use Gate input.

#### **Accessories**



OMRON Corporation Industrial Automation Company

Kyoto, JAPAN Contact: www.ia.omron.com