


Power OFF-delay Timer

Order Code




Technical criteria

Rated supply voltage	100 to 120 VAC, 50/60 Hz	
Operating mode	OFF delay	
Input method	None	
Minimum power-ON time	0.1 s	
Control Output	5 A at 250 VAC with resistive load ($\cos \varphi = 1$),	
	5 A at 30 VDC with resistive load	
Accuracy of operating time	±1% of FS max. (±1% ±10 ms max. at 1.2-s range)	
Setting error	±10% of FS ±0.05 s max.	
Operating Temperature	-20 to 60°C	
Operating Humidity	25% to 85%	
IP	IP30 (Terminal block: IP20)	

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Nomenclature




1	Power indicator
2	Time range switch
3	Main dial

Time range


Time range setting	x0.1	x1
Set time range	0.1 to 1.2 s	1 to 12 s
Power ON time	0.1 s min.	
Scale numbers	12	

Timing Chart



Note: Refer to the official Datasheet, how to use Gate input.

Accessories



OMRON Corporation Industrial Automation Company

Kyoto, JAPAN Contact: www.ia.omron.com

Regional Headquarters OMRON EUROPE B.V. Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300/Fax: (31) 2356-81-388 https://industrial.omron.eu/en/home

OMRON ELECTRONICS LLC 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900/Fax: (1) 847-843-7787

© OMRON Corporation 2019 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

Cat. No. L199-E1-01