


QuOmni 5G/LTE MIMO 2x2, ver. US

Omnidirectional ultra wideband 5G/LTE MIMO 2x2 antenna

QuOmni 5G/LTE omnidirectional MIMO 2x2 is ultra wideband LTE Outdoor antenna. It's primary designed for LTE/5G/3G/2G devices which require high efficiency connections. The antenna covers many LTE bands including the new Extended LTE Band 71, frequencies: 617 - 3800MHz. The mounting bracket allows the antenna to be installed on the buildings (on the pole or on the wall) as the client antenna or on the moving points like trains, buses, lorries, yachts, boats to receive Internet by LTE/5G/3G/2G. It's ideal solution to use with all industrial and domestic 2x2 LTE modems and routers like: Teltonika, DIGI, Mikrotik, Robustel, Cisco, etc.



OUTDOOR ANTENNA WORKS IN ANY WEATHER CONDITIONS, IP67



GALVANIZED STEEL, WALL OR POLE MOUNTING BRACKET



TWO SMA CONNECTORS



360° BEAMWIDTH



4DBI GAIN



MADE IN EUROPE



LTE ANTENNA SPECIFICATION

FREQUENCY	617 - 960 MHz 1.7 - 2.2 GHz 2.3 - 2.7 GHz 3.3 - 3.8 GHz
GAIN	617 - 960 MHz : 3 dBi 1.7 - 2.2 GHz : 3.5 dBi 2.3 - 2.7 GHz : 3.5 dBi 3.3 - 3.8 GHz : 4dBi
SUPPORTED LTE/5G BANDS	1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 12, 13, 14, 17, 18, 19, 20, 22, 23, 25, 26, 27, 28, 29, 30, 33, 34, 35, 36, 37, 38, 39, 40, 41, 42, 43, 44, 48, 49, 52, 53, 59, 62, 65, 66, 67, 68, 69, 71, 85, n78, n80, n81, n82, n83, n84, n86, n89, n90, n95
VSWR	<1.80, max <2.00
BEAMWIDTH	360°/35° ±5°
POLARIZATION	Vertical
IMPEDANCE	50 Ω

MECHANICAL SPECIFICATION

MATERIALS	ABS, aluminum, PTFE
CONNECTOR TYPE	2x SMA plug
INGRESS PROTECTION	IP67
DIMENSIONS	160 x 160 x 240 mm 6.3 x 6.3 x 9.45 inch
WEIGHT	1.5 kg 3.31 lbs
OPERATING TEMPERATURE	From -40°C to 75°C From -40°F to 167°F
CABLE LENGTH	5m (P/N: A05G2U) or 10m (P/N: A05G2U-1)
CABLE TYPE	LMR195 white

FREQUENCY BANDS

LTE / 4G GSM	5	6	8	12	13	14	17	617 MHz	960 MHz
	18	19	20	26	27	28	29		
	44	67	68	71	85	n81	n82		
	n83	n89							
LTE / 4G UMTS	1	2	3	4	9	10	25	1710 MHz	2170 MHz
	33	34	35	36	37	39	59		
	62	n80	n84	n86	n95				

LTE / 4G WCS DARS	2300 MHz	30	40	2400 MHz					
LTE / 4G	2400 MHz	7	38	41	53	69	n90	2700 MHz	
LTE / 5G	3300 MHz	22	42	43	48	49	52	n78	3800 MHz

COMPATIBLE ROUTERS


VARIANTS: A05G2U, A05G2U-1

TELTONIKA	RUT200, RUT230, RUT240, RUT241, RUT900, RUT901, RUT950, RUT951, RUT955, RUT956, RUTX09, RUTX11
DIGI	6310-DX, 6330-MX, EX12, EX15, IX10, IX20, WR31
ROBUSTEL	EG5100, LG5100, R1500, R1510, R1511, R1520 Global, R2010, R2011, R2110, R3000 Industrial, R3000 LG, R3000 Lite, R3000 Quad, R3010
SIEMENS	6GK5876-4AA00-2BA2, 6GK5876-4AA00-2DA2, 6GK5876-4AA10-2BA2
ANYBUS	Wireless Router WLAN
COMSET	CM210A-W, CM210Q-W, CM510Q-W, CM685T-W, CM685V-1, CM685V-4, CM685V-6, CM685V-6-G, CM820T-W, CM820V-4, CM820V-W
CRADLEPOINT	CBA550, E100, E102, IBR200, IBR600C, IBR900, L950
D-LINK	G415 AX1500, G416 AX1500, N300 4G
FORTINET	FEX-101F, FEX-201F, FEX-211E, FEX-212F
FOUR-FAITH	4G Cellular Router F-R100, Cellular Wireless Router F-R200, Dual-sim WiFi Router F3946, Industrial WiFi Router F3X36Q, LAN Port Router F3X26 V2, LTE Industrial Router F3X27 V2, LTE Wireless Router F3x36



PEPLINK	MAX BR1 Classic, MAX BR1 ENT, MAX BR1 M2M, MAX BR1 Mini, MAX BR1 MK2, MAX BR1 Pro, MAX BR1 Slim
PROROUTE	H685 4G Router
SIERRA WIRELESS	AirLink LX40, AirLink LX60, AirLink MP70, AirLink RV50X, AirLink RV55, AirLink RX55
WAVETEL	W2400 LTE , W3600 4G/LTE Dual WAN, W3604 Multi-WAN, W3608 Multi-WAN, W421, W4600, W4600-S2
WLINK	G200, G510, G520, R210, R220, R520

PLOTS



VSWR for LTE antenna





From 650MHz to 950MHz





From 1.71GHz to 2.17GHz



From 2.3GHz to 2.7GHz



From 3.3GHz to 3.8GHz



DIMENSIONS

