



# **EPITAXIAL PLANAR NPN**

 GENERAL PURPOSE AMPLIFIER AND SWITCH

### **DESCRIPTION**

The 2N2102 is a silicon Planar Epitaxial NPN transistor in Jedec TO-39 metal case. It is intended for a wide variety of small-signall and medium power applications in military and industrial equipments.





# ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Value	Unit
$V_{CBO}$	Collector-Base Voltage (I <sub>E</sub> = 0)	120	V
V <sub>CEO</sub>	Collector-Emitter Voltage (I <sub>B</sub> = 0)	65	V
$V_{CER}$	Collector-Emitter Voltage ( $R_{BE} \le 10\Omega$ )	80	V
V <sub>EBO</sub>	Emitter-Base Voltage (I <sub>C</sub> = 0)	7	V
Ic	Collector Current	1	А
$P_{tot}$	Total Dissipation at T <sub>amb</sub> ≤ 25 °C	1	W
	at T <sub>C</sub> ≤ 25 °C	5	W
T <sub>stg</sub>	Storage Temperature	-65 to 175	°C
Tj	Max. Operating Junction Temperature	175	°C

December 2002 1/4

## THERMAL DATA

Rthj	-case	Thermal	Resistance	Junction-Case	Max	30	°C/W	
Rth	j-amb	Thermal	Resistance	Junction-Ambient	Max	150	°C/W	

# **ELECTRICAL CHARACTERISTICS** ( $T_{case} = 25$ $^{\circ}C$ unless otherwise specified)


Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
Ісво	Collector Cut-off Current (I <sub>E</sub> = 0)	V <sub>CB</sub> = 60 V V <sub>CB</sub> = 60 V T <sub>C</sub> = 150 °C			2 2	nΑ μΑ
I <sub>EBO</sub>	Emitter Cut-off Current (I <sub>C</sub> = 0)	V <sub>EB</sub> = 5 V			5	nA
V <sub>(BR)CBO</sub>	Collector-Base Breakdown Voltage (I <sub>E</sub> = 0)	I <sub>C</sub> = 100 μA	120			54
V <sub>CEO(sus)</sub> *	Collector-Emitter Sustaining Voltage (I <sub>B</sub> = 0)	Ic = 30 mA	65	09/		V
V <sub>CE(sat)</sub> *	Collector-Emitter Saturation Voltage	I <sub>C</sub> = 150 mA I <sub>B</sub> = 15 mA			0.5	V
$V_{BE(sat)^*}$	Base-Emitter Saturation Voltage	I <sub>C</sub> = 150 mA	)		1.1	V
h <sub>FE</sub> *	DC Current Gain	$\begin{array}{llllllllllllllllllllllllllllllllllll$	10 20 35 40 25 10		120	
h <sub>fe</sub> *	High Frequency Current Gain	I <sub>U</sub> = 50 mA V <sub>CE</sub> = 10 V f = 20 MHz		6		
NF	Noise Figure	$I_{C} = 300 \ \mu A$ $V_{CE} = 10 \ V$ $f = 1 \ KHz$ $BW = 1 \ Hz$ $R_{g} = 510 \ \Omega$			8	dB
Ссво	Collector-Save	I <sub>E</sub> = 0 V <sub>CB</sub> = 10 V f = 1MHz			15	pF
Сево	Emitter-Base Capacitance	I <sub>C</sub> = 0 V <sub>EB</sub> = 0.5 V f = 1MHz			80	pF

<sup>\*</sup> Pulse d: Pulse duration = 300 μs, duty cycle ≤ 1 %

2/4

# **TO-39 MECHANICAL DATA**

DIM.	mm			inch			
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	
А	12.7			0.500			
В			0.49			0.019	
D			6.6			0.26)	
E			8.5		AU	0.334	
F			9.4		2100	0.370	
G	5.08			0.200			
Н			1.2	Ole		0.047	
I			0.9			0.035	
L			45° (	(typ.)			



47/

Obsolete Product(s). Obsolete Product(s)

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specification mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is a trademark of STMicroelectronics

© 2002 STMicroelectronics – Printed in Italy – All Rights Reserved STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - Canada - China - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States.

http://www.st.com

47/