

# PC410L0NIP0F Series

# High Speed 10Mb/s, High CMR Mini-flat Package \*OPIC Photocoupler



#### ■ Description

**PC410L0NIP0F Series** contains a LED optically coupled to an OPIC chip.

It is packaged in a 5 pin mini-flat.

Input-output isolation voltage(rms) is 3.75 kV.

High speed response(TYP. 10 Mb/s) and CMR is MIN. 10 kV/ $\mu$ s.

#### **■** Features

- 1. 5 pin Mini-flat package
- 2. Double transfer mold package (Ideal for Flow Soldering)
- 3. High noise immunity due to high instantaneous common mode rejection voltage (CM<sub>H</sub> : MIN.10 kV/ $\mu$ s, CM<sub>L</sub> : MIN. –10 kV/ $\mu$ s)
- 4. High speed response

(t<sub>PHL</sub>: TYP. 48 ns, t<sub>PLH</sub>: TYP. 50 ns)

- 5. High isolation voltage between input and output  $(V_{iso(rms)}: 3.75 \text{ kV})$
- 6. Lead-free and RoHS directive compliant

#### ■ Agency approvals/Compliance

- 1. Recognized by UL1577 (Double protection isolation), file No. E64380 (as model No. **PC410L**)
- 2. Approved by VDE, DIN EN60747-5-2<sup>(\*)</sup> (as an option), file No. 40009162 (as model No. **PC410L**)
- 3. Package resin: UL flammability grade (94V-0)

#### ■ Applications


- 1. Programmable controllers
- 2. Inverter

<sup>(\*)</sup> DIN EN60747-5-2: successor standard of DIN VDE0884

<sup>\* &</sup>quot;OPIC"(Optical IC) is a trademark of the SHARP Corporation. An OPIC consists of a light-detecting element and a signal-processing circuit integrated onto a single chip.



#### ■ Internal Connection Diagram




- 1 Anode
- 3 Cathode
- 4 GND
- ⑤ V<sub>O</sub> (Open collector)
- $^{\circ}$   $V_{CC}$

#### **■** Outline Dimensions

(Unit: mm)

# 1. Mini-flat Package [ex. PC410L0NIP0F] 1.27<sup>±0.25</sup> SHARP mark "S" PC410L Anode `S Date code 1 0.4<sup>±0.1</sup> Factory identification mark $5.3^{\pm0.3}$ Epoxy resin 45° $0.5^{+0.4}_{-0.2}$ $7.0^{+0.2}_{-0.7}$ Product mass: approx. 0.1g



Plating material: SnCu (Cu: TYP. 2%)



#### Date code (2 digit)

1st digit				2nd digit		
	Year of p	roduction		Month of production		
A.D.	Mark	A.D	Mark	Month	Mark	
1990	A	2002	P	January	1	
1991	В	2003	R	February	2	
1992	С	2004	S	March	3	
1993	D	2005	T	April	4	
1994	Е	2006	U	May	5	
1995	F	2007	V	June	6	
1996	Н	2008	W	July	7	
1997	J	2009	X	August	8	
1998	K	2010	A	September	9	
1999	L	2011	В	October	0	
2000	M	2012	С	November	N	
2001	N	:	:	December	D	

repeats in a 20 year cycle

# Factory identification mark

Factory identification Mark	Country of origin		
no mark	- Japan		
	Indonesia		
_	China		

<sup>\*</sup> This factory marking is for identification purpose only. Please contact the local SHARP sales representative to see the actual status of the production.

#### Rank mark

There is no rank mark indicator.



■ Absolute Maximum Ratings

	<b>Absolute Maximum Ratings</b> $(T_a=25^{\circ}C)$						
	Parameter	Symbol	Rating	Unit			
<del></del>	Forward current	$I_F$	20	mA			
Input	Reverse voltage	$V_R$	5	V			
_	Power dissipation	P	40	mW			
	Supply voltage	$V_{CC}$	7	V			
Output	High level output voltage	V <sub>OH</sub>	7	V			
	Low level output current	$I_{OL}$	50	mA			
	Collector power dissipation	P <sub>C</sub>	85	mW			
	Operating temperature	Topr	-40 to +85	°C			
Storage temperature		$T_{stg}$	-40 to +125	°C			
*1 Isolation voltage		V <sub>iso (rms)</sub>	3.75	kV			
*2 Soldering temperature		T <sub>sol</sub>	260	°C			

<sup>\*1 40</sup> to 60%RH, AC for 1minute, f=60Hz

# **■** Electro-optical Characteristics

(unless otherwise specified  $T_a=-40$  to  $85^{\circ}$ C)

(unless otherwise specified $T_a$ =-40 to 85 C)									
Parameter			Symbol	Conditions		MIN.	TYP.	MAX.	Unit
	Forward voltage		$V_{F}$	$T_a=25^{\circ}C, I_F=10mA$		_	1.6	1.9	V
Input	Rev	Reverse current		$T_a=25^{\circ}C, V_R=5V$		_	_	10	μΑ
Terminal capacitance		$C_{t}$	$T_a=25$ °C, V=0, f=1MHz		-	60	150	pF	
	Low	v level output voltage	$V_{OL}$	$I_{OL}=13 \text{mA}, V_{CC}=5.5 \text{V}, I_{F}=5 \text{mA}$		-	0.4	0.6	V
Output	Hig	h level output current	$I_{OH}$	$V_{CC}=V_{O}=5$	$V_{CC}=V_{O}=5.5V, I_{F}=250\mu A$		0.02	100	μA
Output	Low	v level supply current	$I_{CCL}$	V <sub>CC</sub> =5.5V, I <sub>F</sub> =10mA		-	7	13	mA
	High	h level supply current	$I_{CCH}$	$V_{CC}=5.5V, I_{F}=0$		-	5	10	mA
	"High→Low" input threshold current		$I_{FHL}$	$V_{CC}=5V, V_{O}=0.8V, R_{L}=350\Omega$		_	2.5	5	mA
	Isolation resistance		$R_{ISO}$	T <sub>a</sub> =25°C, DC5	5×10 <sup>10</sup>	$10^{11}$	_	Ω	
	Floa	Floating capacitance		$T_a=25$ °C, V=0, f=1MHz		_	0.6	_	pF
	ue	"High→Low" propagation delay time	ow" propagation delay time tphl				48	75	ns
Transfer	time	"Low $\rightarrow$ High" propagation delay time $t_{PLH}$ *3 Distortion of pulse width $\Delta t_{w}$ Rise time $t_{r}$		$T_a$ =25°C, $V_{CC}$ =5V, $I_F$ =7.5mA, $R_L$ =350 $\Omega$ , $C_L$ =15pF,		25	50	75	ns
charac-	)Suc					_	_	35	ns
teristics	Rise time		$t_r$			_	20	_	ns
	R	Fall time				_	10	_	ns
	Instantaneous common mode rejection voltage (High level output)		СМн	$I_F = 0 \\ V_{O(MIN.)} = 2V$	$T_a=25$ °C, $V_{CC}=5V$ $V_{CM}=1kV_{(P-P)}$ ,	10	20	_	kV/μs
	Instantaneous common mode rejection voltage (Low level output)		$CM_L$	$I_F = 5mA$ $V_{O(MAX.)} = 0.8V$	$R_L=350\Omega$	-10	-20	_	kV/μs

<sup>\*3</sup> Distortion of pulse width  $\Delta t_w = |t_{PHL} - t_{PLH}|$ 

<sup>\*2</sup> For 10s



#### **■** Model Line-up

Doolsooo	Taping		
Package	3 000pcs/reel		
DIN EN60747-5-2		Approved	
Model No.	PC410L0NIP0F	PC410L0YIP0F	

Please contact a local SHARP sales representative to inquire about production status.



#### Fig.1 Test Circuit for Propagation Delay Time and Rise Time, Fall Time




Fig.2 Test Circuit for Instantaneous Common Mode Rejection Voltage




Fig.3 Forward Current vs. Ambient Temperature




Fig.4 Collector Power Dissipation vs. Ambient Temperature






Fig.5 Forward Current vs. Forward Voltage




Fig.7 Low Level Output Voltage vs. Ambient Temperature




Fig.9 Input Threshold Current vs.
Ambient Temperature




Fig.6 High Level Output Current vs. Ambient Temperature




Fig.8 Output Voltage vs. Forward Current




Fig.10 Propagation Delay time vs. Forward Current







Fig.11 Propagation Delay Time vs. Ambient Temperature



Remarks: Please be aware that all data in the graph are just for reference and not for guarantee.



#### **■** Design Considerations

#### Recommended operating conditions

Parameter	Symbol	MIN.	TYP.	MAX.	Unit
Low level input current	$I_{FL}$	0	-	250	μΑ
High level input current	$I_{FH}$	8	_	15	mA
Supply voltage	$V_{CC}$	4.5	_	5.5	V
Fan out (TTL load)	N	_	_	5	-
Operating temperature	Topr	-40	-	+70	°C

#### Notes about static electricity

Transistor of detector side in bipolar configuration may be damaged by static electricity due to its minute design.

When handling these devices, general countermeasure against static electricity should be taken to avoid breakdown of devices or degradation of characteristics.

#### Design guide

In order to stabilize power supply line, we should certainly recommend to connect a by-pass capacitor of  $0.01\mu F$  or more between  $V_{CC}$  and GND near the device.

In case that some sudden big noise caused by voltage variation is provided between primary and secondary terminals of photocoupler some current caused by it is floating capacitance may be generated and result in false operation since current may go through LED or current may change.

If the photocoupler may be used under the circumstances where noise will be generated we recommend to use the bypass capacitors at the both ends of LED.

The detector which is used in this device, has parasitic diode between each pins and GND.

There are cases that miss operation or destruction possibly may be occurred if electric potential of any pin becomes below GND level even for instant.

Therefore it shall be recommended to design the circuit that electric potential of any pin does not become below GND level.

This product is not designed against irradiation and incorporates non-coherent LED.


#### Degradation

In general, the emission of the LED used in photocouplers will degrade over time.

In the case of long term operation, please take the general LED degradation (50% degradation over 5 years) into the design consideration.

Please decide the input current which become 2 times of MAX. I<sub>FHL</sub>.

#### Recommended Foot Print (reference)



(Unit: mm)

<sup>☆</sup> For additional design assistance, please review our corresponding Optoelectronic Application Notes.



#### ■ Manufacturing Guidelines


#### Soldering Method

#### Reflow Soldering:

Reflow soldering should follow the temperature profile shown below.

Soldering should not exceed the curve of temperature profile and time.

Please don't solder more than twice.



#### Flow Soldering:

Due to SHARP's double transfer mold construction submersion in flow solder bath is allowed under the below listed guidelines.

Flow soldering should be completed below 260°C and within 10s.

Preheating is within the bounds of 100 to 150°C and 30 to 80s.

Please don't solder more than twice.

#### Hand soldering

Hand soldering should be completed within 3s when the point of solder iron is below 400°C.

Please don't solder more than twice.

#### Other notices

Please test the soldering method in actual condition and make sure the soldering works fine, since the impact on the junction between the device and PCB varies depending on the tooling and soldering conditions.



#### Cleaning instructions

#### Solvent cleaning:

Solvent temperature should be 45°C or below Immersion time should be 3 minutes or less

#### Ultrasonic cleaning:

The impact on the device varies depending on the size of the cleaning bath, ultrasonic output, cleaning time, size of PCB and mounting method of the device.

Therefore, please make sure the device withstands the ultrasonic cleaning in actual conditions in advance of mass production.

#### Recommended solvent materials:

Ethyl alcohol, Methyl alcohol and Isopropyl alcohol

In case the other type of solvent materials are intended to be used, please make sure they work fine in actual using conditions since some materials may erode the packaging resin.

#### Presence of ODC

This product shall not contain the following materials.

And they are not used in the production process for this product.

Regulation substances: CFCs, Halon, Carbon tetrachloride, 1.1.1-Trichloroethane (Methylchloroform)

Specific brominated flame retardants such as the PBBOs and PBBs are not used in this product at all.

This product shall not contain the following materials banned in the RoHS Directive (2002/95/EC).

•Lead, Mercury, Cadmium, Hexavalent chromium, Polybrominated biphenyls (PBB), Polybrominated diphenyl ethers (PBDE).



#### ■ Package specification

#### ● Tape and Reel package


Package materials

Carrier tape: A-PET (with anti-static material)

Cover tape: PET (three layer system)

Reel: PS


#### Carrier tape structure and Dimensions




**Dimensions List** 

C D Е F A G  $8.0^{\pm0.1}$ 12.0±0.3  $5.5^{\pm0.1}$ 1.75<sup>±0.1</sup>  $2.0^{\pm0.1}$  $4.0^{\pm0.1}$ φ1.5<del>+</del>8.1 Η J K  $7.4^{\pm0.1}$  $0.3^{\pm0.05}$ 3.1<sup>±0.1</sup> 4.0<sup>±0.1</sup>


#### Reel structure and Dimensions






Dimensio	ns List	(Unit: mm)			
a	b	с	d		
370	13.5 <sup>±1.5</sup>	80 <sup>±1.0</sup>	13 <sup>±0.5</sup>		
e	f	g			
21 <sup>±1.0</sup>	2.0±0.5	2.0 <sup>±0.5</sup>			

### Direction of product insertion





[Packing: 3 000pcs/reel]



#### **■** Important Notices

- · The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- · Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- · Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:
- (i) The devices in this publication are designed for use in general electronic equipment designs such as:
  - --- Personal computers
  - --- Office automation equipment
  - --- Telecommunication equipment [terminal]
  - --- Test and measurement equipment
  - --- Industrial control
  - --- Audio visual equipment
  - --- Consumer electronics
- (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection

with equipment that requires higher reliability such as:

- --- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
- --- Traffic signals
- --- Gas leakage sensor breakers
- --- Alarm equipment
- --- Various safety devices, etc.
- (iii) SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:
  - --- Space applications
  - --- Telecommunication equipment [trunk lines]
  - --- Nuclear power control equipment
  - --- Medical and other life support equipment (e.g., scuba).
- · If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- · This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- Contact and consult with a SHARP representative if there are any questions about the contents of this publication.

[E250] Sheet No.: D2-A04802EN