SHARP

PC901V0NSZXF Series

Digital Output, Normal ON Operation DIP 6 pin *OPIC Photocoupler



Description

PC901V0NSZXF Series contains an IRED optically coupled to an OPIC chip.

It is packaged in a 6 pin DIP.

Input-output isolation voltage(rms) is 5.0kV.

Features

- 1.6 pin DIP package
- 2. Double transfer mold package
 - (Ideal for Flow Soldering)
- 3. Normal ON operation, open collector output
- 4. TTL and LSTTL compatible output
- 5. Operating supply voltage (V_{CC}=3 to 15 V)
- 6. Isolation voltage (V_{iso(rms)} : 5.0 kV)
- 7. Lead-free and RoHS directive compliant

Agency approvals/Compliance

- 1. Recognized by UL1577 (Double protection isolation), file No. E64380 (as model No. **PC901V**)
- 2. Approved by VDE, DIN EN60747-5-2^(*) (as an option), file No. 40008189 (as model No. **PC901V**)
- 3. Package resin : UL flammability grade (94V-0)

(*) DIN EN60747-5-2 : successor standard of DIN VDE0884

Applications


- 1. Programmable controllers
- 2. PC peripherals
- 3. Electronic musical instruments

* "OPIC"(Optical IC) is a trademark of the SHARP Corporation. An OPIC consists of a light-detecting element and a signal-processing circuit integrated onto a single chip.

Notice The content of data sheet is subject to change without prior notice. In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc. Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.




Internal Connection Diagram



Outline Dimensions

(Unit : mm)



Plating material : SnCu (Cu : TYP. 2%)



Date code (2 digit)

1st digit				2nd digit		
Year of production				Month of production		
A.D.	Mark	A.D	Mark	Month	Mark	
1990	А	2002	Р	January	1	
1991	В	2003	R	February	2	
1992	С	2004	S	March	3	
1993	D	2005	Т	April	4	
1994	Е	2006	U	May	5	
1995	F	2007	V	June	6	
1996	Н	2008	W	July	7	
1997	J	2009	Х	August	8	
1998	K	2010	А	September	9	
1999	L	2011	В	October	0	
2000	М	2012	С	November	N	
2001	N	:	:	December	D	

repeats in a 20 year cycle

Country of origin

Japan

Rank mark

There is no rank mark indicator.

■ Absolute Maximum Ratings

Parameter		Symbol	Rating	Unit
	Forward current	I_F	50	mA
Input	*1 Peak forward current	I _{FM}	1	А
	Reverse voltage	V _R	6	V
	Power dissipation	Р	70	mW
	Supply voltage	V _{CC}	16	V
Output	High level output voltage	V _{OH}	16	V
	Low level output current	I _{OL}	50	mA
	Power dissipation	Po	150	mW
Total power dissipation		P _{tot}	170	mW
Operating temperature		T _{opr}	-25 to +85	°C
Storage temperature		T _{stg}	-40 to +125	°C
*2 Isolation voltage		V _{iso (rms)}	5.0	kV
*3 Soldering temperature		T _{sol}	260	°C

 $(T_a=25^{\circ}C)$

*1 Pulse width≤100µs, Duty ratio:0.001 *2 40 to 60%RH, AC for 1minute, f=60Hz

*3 For 10s

■ Electro-optical Characteristics

(unless otherwise specified $T_a=0$ to $+70^{\circ}C$)

Parameter		Symbol	Conditions	MIN.	TYP.	MAX.	Unit		
	Г	Forward voltage		I _F =4mA	-	1.1	1.4	- v	
	Forwa			$I_F=0.3mA$	0.7	1.0	-		
Input Reverse current		Ir	$T_a=25^{\circ}C, V_R=4V$	-	-	10	μΑ		
	Terminal capacitance		Ct	$T_a=25^{\circ}C$, V=0, f=1kHz	-	30	250	pF	
	Opera	ating supply voltage	Vcc	_	3	-	15	V	
	Low	level output voltage	Vol	I_{OL} =16mA, V_{CC} =5V, I_{F} =0	-	0.2	0.4	V	
	High level output current		Іон	$V_O = V_{CC} = 15V, I_F = 4mA$	-	-	100	μΑ	
	Low level supply current		ICCL	$V_{CC}=5V, I_{F}=0$	-	2.5	5.0	mA	
	High level supply current		Іссн	$V_{CC}=5V, I_F=4mA$	-	2.7	5.5	mA	
Output ^{*4} "Low→High" input threshold		→High" input threshold	IFLH	$T_a=25^{\circ}C, V_{CC}=5V, R_L=280\Omega$	-	1.1	2.0	mA	
curren	nt	V_{CC} =5V, R_L =280 Ω		-	-	4.0			
	^{*5} "High→Low" input threshold current		IFHL	$T_a=25^{\circ}C, V_{CC}=5V, R_L=280\Omega$	0.4	0.8	-	mA	
				$V_{CC}=5V, R_L=280\Omega$	0.3	-	-		
	*6 Hysteresis		IFHL/IFLH	$V_{CC}=5V, R_{L}=280\Omega$	0.5	0.7	0.9	_	
	Isolation voltage		Riso	T _a =25°C, DC500V, 40 to 60%RH	5×10 ¹⁰	1×10 ¹¹	-	Ω	
		"Low→High" propagation delay time	t PLH		-	1	3	μs	
time Transfer	Response	"High→Low" propagation delay time	t PHL	$T_a=25^{\circ}C$	-	2	6		
	time	Rise time	tr	V_{CC} =5V, I_{F} =4mA R_{L} =280 Ω	-	0.1	0.5		
		Fall time	tſ	NL-2001	1	0.05	0.5		
charac- teristics			СМн	$V_{CM}=600V(peak), V_{O}(MIN.)=2V$ I _F =4mA, R _L =280 Ω , T _a =25°C	_	-2 000	_	V/µs	
	Instantaneous common mode rejection voltage "Output : Low level"		CML	V_{CM} =600V(peak), V_0 (MAX.)=0.8V I _F =0, R _L =280 Ω , T _a =25°C	_	2 000	_	V/µs	

*4 I_{FLH} represents forward current when output goes from low to high.

*5 I_{FHL} represents forward current when output goes from high to low.
*6 Hysteresis stands for I_{FHL}/I_{FLH}.




■ Model Line-up

Lead Form	Through-Hole		
Dealeaga	Sleeve		
Package	50 pcs/sleeve		
DIN EN60747-5-2		Approved	
Model No.	PC901V0NSZXF	PC901V0YSZXF	

Please contact a local SHARP sales representative to inquire about production status.



Fig.1 Test Circuit for Response Time







Fig.2 Test Circuit for Instantaneous Common Mode Rejection Voltage






Fig.3 Forward Current vs. Ambient Temperature




Fig.4 Power Dissipation vs. Ambient Temperature








Fig.5 Forward Current vs. Forward Voltage












Fig.6 Relative Input Threshold Current vs. Supply Voltage




Fig.8 Low Level Output Voltage vs. Low Level Output Current




Fig.10 High Level Output Current vs. Forward Current







Fig.11 High Level Output Current vs. Ambient Temperature







Remarks : Please be aware that all data in the graph are just for reference and not for guarantee.

Fig.12 Supply Current vs. Supply Voltage





Fig.14 Rise Time, Fall Time vs. Load Resistance





Design Considerations

Notes about static electricity

Transistor of detector side in bipolar configuration may be damaged by static electricity due to its minute design.

When handling these devices, general countermeasure against static electricity should be taken to avoid breakdown of devices or degradation of characteristics.

• Design guide

In order to stabilize power supply line, we should certainly recommend to connect a by-pass capacitor of $0.01 \mu F$ or more between V_{CC} and GND near the device.

In case that some sudden big noise caused by voltage variation is provided between primary and secondary terminals of photocoupler some current caused by it is floating capacitance may be generated and result in false operation since current may go through IRED or current may change.

If the photocoupler may be used under the circumstances where noise will be generated we recommend to use the bypass capacitors at the both ends of IRED.

The detector which is used in this device, has parasitic diode between each pins and GND.

There are cases that miss operation or destruction possibly may be occurred if electric potential of any pin becomes below GND level even for instant.

Therefore it shall be recommended to design the circuit that electric potential of any pin does not become below GND level.

This product is not designed against irradiation and incorporates non-coherent IRED.

Degradation

In general, the emission of the IRED used in photocouplers will degrade over time.

In the case of long term operation, please take the general IRED degradation (50% degradation over 5 years) into the design consideration.

Please decide the input current which become 2 times of MAX. IFLH.

☆ For additional design assistance, please review our corresponding Optoelectronic Application Notes.



Manufacturing Guidelines

Soldering Method

Flow Soldering :

Due to SHARP's double transfer mold construction submersion in flow solder bath is allowed under the below listed guidelines.

Flow soldering should be completed below 270°C and within 10s. Preheating is within the bounds of 100 to 150°C and 30 to 80s. Please don't solder more than twice.

Hand soldering

Hand soldering should be completed within 3s when the point of solder iron is below 400°C. Please don't solder more than twice.

Other notices

Please test the soldering method in actual condition and make sure the soldering works fine, since the impact on the junction between the device and PCB varies depending on the tooling and soldering conditions.



• Cleaning instructions

Solvent cleaning:

Solvent temperature should be 45°C or below Immersion time should be 3 minutes or less

Ultrasonic cleaning:

The impact on the device varies depending on the size of the cleaning bath, ultrasonic output, cleaning time, size of PCB and mounting method of the device.

Therefore, please make sure the device withstands the ultrasonic cleaning in actual conditions in advance of mass production.

Recommended solvent materials:

Ethyl alcohol, Methyl alcohol and Isopropyl alcohol

In case the other type of solvent materials are intended to be used, please make sure they work fine in actual using conditions since some materials may erode the packaging resin.

Presence of ODC

This product shall not contain the following materials. And they are not used in the production process for this product. Regulation substances : CFCs, Halon, Carbon tetrachloride, 1.1.1-Trichloroethane (Methylchloroform)

Specific brominated flame retardants such as the PBBOs and PBBs are not used in this product at all.

This product shall not contain the following materials banned in the RoHS Directive (2002/95/EC).
•Lead, Mercury, Cadmium, Hexavalent chromium, Polybrominated biphenyls (PBB), Polybrominated diphenyl ethers (PBDE).



Package specification


• Sleeve package


Package materials Sleeve : HIPS (with anti-static material) Stopper : Styrene-Elastomer

Package method

MAX. 50 pcs. of products shall be packaged in a sleeve.Both ends shall be closed by tabbed and tabless stoppers.The product shall be arranged in the sleeve with its anode mark on the tabless stopper side.MAX. 20 sleeves in one case.

Sleeve outline dimensions





SHARP

Important Notices

• The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.

• Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.

• Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:

(i) The devices in this publication are designed for use in general electronic equipment designs such as:

- --- Personal computers
- --- Office automation equipment
- --- Telecommunication equipment [terminal]
- --- Test and measurement equipment
- --- Industrial control
- --- Audio visual equipment
- --- Consumer electronics

(ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection with equipment that requires higher reliability such as:

- --- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
- --- Traffic signals
- --- Gas leakage sensor breakers
- --- Alarm equipment
- --- Various safety devices, etc.

(iii) SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:

- --- Space applications
- --- Telecommunication equipment [trunk lines]
- --- Nuclear power control equipment
- --- Medical and other life support equipment (e.g., scuba).

• If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Law of Japan, it is necessary to obtain approval to export such SHARP devices.

• This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.

 \cdot Contact and consult with a SHARP representative if there are any questions about the contents of this publication.