

S202SE1 Series

*Zero cross type is also available. (S202SE2 Series)

I_T(rms)≤8A, Reinforced Insulation Type Non-Zero Cross type SIP 4pin Triac output SSR

■ Description

S202SE1 Series reinforced insulation type Solid State Relays (SSR) are an integration of an infrared emitting diode (IRED), a Phototriac Detector and a main output Triac. These devices are ideally suited for controlling high voltage AC loads with solid state reliability while providing 3.0kV isolation ($V_{iso}(rms)$) from input to output.

■ Features

- 1. Output current, I_T(rms)≤8.0A
- 2. Non-zero crossing functionary
- 3. 4 pin SIP package
- 4. High repetitive peak off-state voltage (V_{DRM}: 600V)
- 5. Reinforced insulation type (MIN. 0.4mm internal separation)
- 6. High isolation voltage between input and output $(V_{iso}(rms): 3.0kV)$
- 7. Lead-free terminal components are also available (see Model Line-up section in this datasheet)
- 8. Screw hole for heat sink

■ Agency approvals/Compliance


- 1. Recognized by UL508, file No. E94758 (as models No. **S202SE1**)
- Approved by CSA 22.2 No.14, file No. LR63705 (as models No. S202SE1)
- 3. Approved by TÜV EN60950 (reinforced insulation), file No. R9051479 (as models No. **S202SE1**)
- 4. Package resin : UL flammability grade (94V-0)

■ Applications

- 1. Isolated interface between high voltage AC devices and lower voltage DC control circuitry.
- 2. Switching motors, fans, heaters, solenoids, and valves.
- 3. Phase or power control in applications such as lighting and temperature control equipment.




■ Internal Connection Diagram



- ① Output (Triac T2)
- ② Output (Triac T1)
- (3) Input (+) (4) Input (-)

■ Outline Dimensions

(Unit: mm)



(): Typical dimensions



Date code (2 digit)

| 1st digit | | | | 2nd digit | | |
|--------------------|------|------|------|---------------------|------|--|
| Year of production | | | | Month of production | | |
| A.D. | Mark | A.D | Mark | Month | Mark | |
| 1990 | A | 2002 | P | January | 1 | |
| 1991 | В | 2003 | R | February | 2 | |
| 1992 | С | 2004 | S | March | 3 | |
| 1993 | D | 2005 | T | April | 4 | |
| 1994 | Е | 2006 | U | May | 5 | |
| 1995 | F | 2007 | V | June | 6 | |
| 1996 | Н | 2008 | W | July | 7 | |
| 1997 | J | 2009 | X | August | 8 | |
| 1998 | K | 2010 | A | September | 9 | |
| 1999 | L | 2011 | В | October | 0 | |
| 2000 | M | 2012 | С | November | N | |
| 2001 | N | : | : | December | D | |

repeats in a 20 year cycle

Country of origin Japan

Rank mark


There is no rank mark indicator and currently there are no rank offered for this device.



■ Absolute Maximum Ratings

 $(T_a=25^{\circ}C)$

| | | | | -a / |
|-------------------------|---|------------------------|-------------|------|
| | Parameter | Symbol | Rating | Unit |
| T4 | Forward current | I_{F} | 50 *3 | mA |
| Input | Reverse voltage | V_R | 6 | V |
| | RMS ON-state current | I _T (rms) | 8 *3 | A |
| | Peak one cycle surge current | I _{surge} | 80 *4 | A |
| Output | Repetitive peak OFF-state voltage | Vdrm | | V |
| | Non-Repetitive peak OFF-state voltage | Vdsm | 600 | V |
| | Critical rate of rise of ON-state current | dI _T /dt | 50 | A/μs |
| | Operating frequency | f | 45 to 65 | Hz |
| *1 Isolation voltage | | V _{iso} (rms) | 3.0 | kV |
| Operating temperature | | Topr | -25 to +100 | °C |
| Storage temperature | | T_{stg} | -30 to +125 | °C |
| *2Soldering temperature | | T_{sol} | 260 | °C |



■ Electro-optical Characteristics

 $(T_a=25^{\circ}C)$

| (" - | | | | | | | |
|--------------------------|--|-----------------------|--|-----------|------|------|------|
| Parameter | | Symbol | Conditions | | TYP. | MAX. | Unit |
| T . | Forward voltage | V_F | I _F =20mA | - | 1.2 | 1.4 | V |
| Input | Reverse current | I_R | $V_R=3V$ | _ | 1 | 100 | μΑ |
| | Repentitive peak OFF-stage current | I_{DRM} | $V_D = V_{DRM}$ | ı | 1 | 100 | μΑ |
| | ON-state voltage | V _T (rms) | I _T (rms)=2A, Resistance load, I _F =20mA | _ | ı | 1.5 | V |
| Output | Holding current | I_{H} | _ | _ | - | 50 | mA |
| | Critical rate of rise of OFF-state voltage | dV/dt | $V_D=2/3 \bullet V_{DRM}$ | 30 | - | _ | V/µs |
| | Critical rate of rise of OFF-state voltage at commutaion | (dV/dt)c | $T_j=125^{\circ}C, V_D=2/3 \bullet V_{DRM}, dI_T/dt=-4.0A/ms$ | 5 | _ | - | V/µs |
| Transfer characteristics | Minimum trigger current | I_{FT} | $V_D=12V$, $R_L=30\Omega$ | _ | - | 8 | mA |
| | Isolation resistance | R _{ISO} | DC500V, 40 to 60%RH | 10^{10} | - | _ | Ω |
| | Turn-on time | t _{on} | V _D (rms)=200V, AC60Hz | _ | _ | 1 | ms |
| | Turn-off time | t _{off} | I _T (rms)=2A, Resistance load, I _F =20mA | - | - | 9.3 | ms |
| Theorem | | | Between junction and case | - | 4.5 | _ | °C/W |
| Thermal resistance | | R _{th} (j-a) | Between junction and ambient | - | 40 | _ | C/W |

^{*1 40} to 60%RH, AC for 1minute, f=60Hz *2 For 10s *3 Refer to Fig.1, Fig.2 *4 f=60Hz sine wave, T_j=25°C start



■ Model Line-up (1) (Lead-free terminal components)

| Shipping Package | ase cs/case | V _{DRM} | $I_{FT}[mA]$ (V_D =12V, | |
|---------------------------------|----------------|------------------|-------------------------------|--|
| EN60950 (reinforced insulation) | Approved | [V] | $R_L=30\Omega$) | |
| Model No. | S202SE1F | 600 | MAX.8 | |

■ Model Line-up (2) (Lead solder plating components)

| Shipping Package | Ca | ase | 3.7 | $I_{FT}[mA]$ ($V_D=12V$, | |
|---------------------------------|-------|----------|-----------|-------------------------------|--|
| Sinpping I ackage | 200pc | es/case | V_{DRM} | | |
| EN60950 (reinforced insulation) | | Approved | [V] | $R_L=30\Omega$) | |
| Model No. | | S202SE1 | 600 | MAX.8 | |

Please contact a local SHARP sales representative to see the actual status of the production.



Fig.1 Forward Current vs.
Ambient Temperature




Fig.3 RMS ON-state Current vs. Case Temperature




Fig.5 Surge Current vs. Power-on Cycle




Fig.2 RMS ON-state Current vs. Ambient Temperature




Fig.4 Forward Current vs. Forward Voltage





Fig.6 Maximum ON-state Power Dissipation vs. RMS ON-state Current



Sheet No.: D4-A03201EN



Fig.7 Minimum Trigger Current vs.
Ambient Temperature





Fig.8 Repetitive Peak OFF-state Current vs. Ambient Temperature



Remarks: Please be aware that all data in the graph are just for reference.



■ Design Considerations

Recommended Operating Conditions

| Parameter | | Symbol | Conditions | MIN. | MAX. | Unit |
|-----------------------|-----------------------------------|------------------------|---|------|------------------------------|------|
| Input | Input signal current at ON state | I _F (ON) | _ | 16 | 24 | mA |
| | Input signal current at OFF state | I _F (OFF) | _ | 0 | 0.1 | mA |
| Output | Load supply voltage | V _{OUT} (rms) | _ | 80 | 240 | V |
| | Load supply current | I _{OUT} (rms) | Locate snubber circuit between output terminals (Cs=0.022 μ F, Rs=47 Ω) | 0.1 | I _T (rms) ×80%(*) | mA |
| | Frequency | f | _ | 47 | 63 | Hz |
| Operating temperature | | T_{opr} | - | -20 | 80 | °C |

^(*) See Fig.2 about derating curve (I_T(rms) vs. ambient temperature).

Design guide

In order for the SSR to turn off, the triggering current (I_F) must be 0.1mA or less.

In phase control applications or where the SSR is being by a pulse signal, please ensure that the pulse width is a minimum of 1ms.

When the input current (I_F) is below 0.1mA, the output Triac will be in the open circuit mode. However, if the voltage across the Triac, V_D , increases faster than rated dV/dt, the Triac may turn on. To avoid this situation, please incorporate a snubber circuit. Due to the many different types of load that can be driven, we can merely recommend some circuit vales to start with : $Cs=0.022\mu F$ and $Rs=47\Omega$. The operation of the SSR and snubber circuit should be tested and if unintentional switching occurs, please adjust the snubber circuit component values accordingly.

When making the transition from On to Off state, a snubber circuit should be used ensure that sudden drops in current are not accompanied by large instantaneous changes in voltage across the Triac.

This fast change in voltage is brought about by the phase difference between current and voltage.

Primarily, this is experienced in driving loads which are inductive such as motors and solenoids.

Following the procedure outlined above should provide sufficient results.

Any snubber or Varistor used for the above mentioned scenarios should be located as close to the main output triac as possible.

The load current should be within the bounds of derating curve. (Refer to Fig.2) Also, please use the optional heat sink when necessary.

In case the optional heat sink is used and the isolation voltage between the device and the optional heat sink is needed, please locate the insulation sheet between the device and the heat sink.

When the optional heat sink is equipped, please set up the M3 screw-fastening torque at 0.3 to 0.5N•m. In order to dissipate the heat generated from the inside of device effectively, please follow the below suggestions.

- (a) Make sure there are no warps or bumps on the heat sink, insulation sheet and device surface.
- (b) Make sure there are no metal dusts or burrs attached onto the heat sink, insulation sheet and device surface.
- (c) Make sure silicone grease is evenly spread out on the heat sink, insulation sheet and device surface.



Silicone grease to be used is as follows;

- 1) There is no aged deterioration within the operating temperature ranges.
- 2) Base oil of grease is hardly separated and is hardly permeated in the device.
- 3) Even if base oil is separated and permeated in the device, it should not degrade the function of a device.


Recommended grease: G-746 (Shin-Etsu Chemical Co., Ltd.)

: G-747 (Shin-Etsu Chemical Co., Ltd.)

: SC102 (Dow Corning Toray Silicone Co., Ltd.)

In case the optional heat sink is screwed up, please solder after screwed.

In case of the lead frame bending, please keep the following minimum distance and avoid any mechanical stress between the base of terminals and the molding resin.




Some of AC electromagnetic counters or solenoids have built-in rectifier such as the diode.


In this case, please use the device carefully since the load current waveform becomes similar with rectangular waveform and this results may not make a device turn off.

Example how to equip optional heat sink for reinforced isolation

1) Case of isolation sheet whose thickness is 0.4mm or more (V_{iso}: 3kV or more)



2) Case of the use of double isolation sheet (Viso: each 3kV or more)



Please keep 5mm distance as minimum between naked metal portion of SSR and heat sink, and also between naked metal portion of SSR and bis/nut/washer.

However, please avoid the natural rubber for isolation sheet.

Degradation


In general, the emission of the IRED used in SSR will degrade over time.

In the case where long term operation and / or constant extreme temperature fluctuations will be applied to the devices, please allow for a worst case scenario of 50% degradation over 5years.

Therefore in order to maintain proper operation, a design implementing these SSRs should provide at least twice the minimum required triggering current from initial operation.



Standard Circuit



[☆] For additional design assistance, please review our corresponding Optoelectronic Application Notes.



■ Manufacturing Guidelines

Soldering Method

Flow Soldering (No solder bathing)

Flow soldering should be completed below 260°C and within 10s.

Preheating is within the bounds of 100 to 150°C and 30 to 80s.

Please solder within one time.

Other notices

Please test the soldering method in actual condition and make sure the soldering works fine, since the impact on the junction between the device and PCB varies depending on the tooling and soldering conditions.

Sheet No.: D4-A03201EN



Cleaning instructions

Solvent cleaning:

Solvent temperature should be 45°C or below. Immersion time should be 3minutes or less.

Ultrasonic cleaning:

The impact on the device varies depending on the size of the cleaning bath, ultrasonic output, cleaning time, size of PCB and mounting method of the device.

Therefore, please make sure the device withstands the ultrasonic cleaning in actual conditions in advance of mass production.

Recommended solvent materials:

Ethyl alcohol, Methyl alcohol and Isopropyl alcohol.

In case the other type of solvent materials are intended to be used, please make sure they work fine in actual using conditions since some materials may erode the packaging resin.

Presence of ODC

This product shall not contain the following materials.

And they are not used in the production process for this device.

Regulation substances: CFCs, Halon, Carbon tetrachloride, 1.1.1-Trichloroethane (Methylchloroform)

Specific brominated flame retardants such as the PBBOs and PBBs are not used in this product at all.

Sheet No.: D4-A03201EN



■ Package specification

Package materials

Packing case: Corrugated cardboard
Partition: Corrugated cardboard
Pad: Corrugated cardboard
Cushioning material: Polyethylene


Molt plane: Urethane

Package method

The product should be located after the packing case is partitioned and protected inside by 4 pads.

Each partition should have 5 products with the lead upward.

Cushioning material and molt plane should be located after all products are settled (1 packing contains 200 pcs).





■ Important Notices

- · The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- · Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- · Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:
- (i) The devices in this publication are designed for use in general electronic equipment designs such as:
 - --- Personal computers
 - --- Office automation equipment
 - --- Telecommunication equipment [terminal]
 - --- Test and measurement equipment
 - --- Industrial control
 - --- Audio visual equipment
 - --- Consumer electronics
- (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection

with equipment that requires higher reliability such as:

- --- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
- --- Traffic signals
- --- Gas leakage sensor breakers
- --- Alarm equipment
- --- Various safety devices, etc.
- (iii) SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:
 - --- Space applications
 - --- Telecommunication equipment [trunk lines]
 - --- Nuclear power control equipment
 - --- Medical and other life support equipment (e.g., scuba).
- · If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- · This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- Contact and consult with a SHARP representative if there are any questions about the contents of this publication.