







| General ordering data | |
|-----------------------|--|
| Order No. | 1597220000 |
| Part designation | SL 3.5/3/90 3.2SN OR |
| Version | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 3, 90°, Box |
| EAN | 4008190121792 |
| Qty. | 100 pc(s). |
| System parameters | |
| Fitted to PCB | Soldered connection |
| Outraina albaur | 000 |

| Soldered connection |
|---------------------|
| 90° |
| 3.5 mm |
| 0.138 inch |
| 3 |
| 3.2 mm |
| Yes |
| 1 |
| 1 |
| 1.3 mm |
| + 0.1 mm |
| 7 mm |
| 0.276 inch |
| 1 ΜΩ |
| |



| System parameters | |
|---|--------------------------------|
| Electric shock protection to DIN VDE 0470 | IP 10 |
| Electric shock protection to DIN VDE 0470 | Safe from back-of-hand touch |
| Electric check protection to Bit VBE 0470 | Care from back of fland todoff |
| Material data | |
| Insulating material | PBT |
| Colour | orange |
| colour chart | Similar to RAL 2000 |
| Insulating material group | Illa |
| Flammability class UL 94 | V-0 |
| CTI | >= 200 |
| Contact base material | CuSn |
| Contact surface | tinned |
| Constant operating temp., min. | -25 °C |
| Constant operating temp., max. | 100 °C |
| Storage temperature, min. | -25 °C |
| Storage temperature, max. | 55 °C |
| Max. relative humidity during storage | 80 % |
| | |
| DIN IEC rating data | |
| Rated current, min. No. pins (Tu=20°C) | 17 A |
| Rated current, max. No. pins (Tu=20°C) | 12 A |
| Rated current, min. No. pins(Tu=40°C) | 14.5 A |
| Rated current, max. No. pins (Tu=40°C) | 10 A |
| Rated voltage for overvoltage class/pollution | 160 V |
| severity III/3 | |
| Rated impulse withstand voltage for overvoltage | 2.5 kV |
| class/pollution severity III/3 | |
| Rated voltage for overvoltage class/pollution | 160 V |
| severity III/2 | |
| Rated impulse withstand voltage for overvoltage | 2.5 kV |
| class/pollution severity III/2 | |
| Rated voltage for overvoltage class/pollution | 320 V |
| severity II/2 | |
| Rated impulse withstand voltage for overvoltage | 2.5 kV |
| class/pollution severity II/2 | |
| Short-time withstand current resistance | 3 x 1s with 100 A |
| | |
| CSA rating data | |
| Rated voltage (Use group D) | 300 V |
| Rated current (Use group D) | 10 A |
| | |
| UL 1059 rating data | 000.14 |
| Rated voltage (Use group D) | 300 V |
| Rated current (Use group D) | 10 A |



Approvals

Approvals institutes





| Downloads | |
|---------------------------------------|-------------|
| CAD Library (P-CAD Format - Standard) | SL.LIB |
| | |
| Classifications | |
| ETIM 2.0 | NK |
| ETIM 3.0 | EC001284 |
| eClass 4.1 | 27-26-07-01 |
| eClass 5.0 | 27-26-07-01 |
| eClass 5.1 | 27-26-07-04 |

Similar products

| 1597210000 | SL 3.5/2/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 2, 90°, Box |
|------------|-----------------------|---|
| 1597230000 | SL 3.5/4/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 4, 90°, Box |
| 1597240000 | SL 3.5/5/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 5, 90°, Box |
| 1597250000 | SL 3.5/6/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 6, 90°, Box |
| 1597260000 | SL 3.5/7/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 7, 90°, Box |
| 1597270000 | SL 3.5/8/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 8, 90°, Box |
| 1597280000 | SL 3.5/9/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 9, 90°, Box |
| 1597290000 | SL 3.5/10/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 10, 90°, Box |
| 1597300000 | SL 3.5/11/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 11, 90°, Box |
| 1597310000 | SL 3.5/12/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 12, 90°, Box |
| | | |



| 1597320000 | SL 3.5/13/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 13, 90°, Box |
|------------|-----------------------|---|
| 1597330000 | SL 3.5/14/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 14, 90°, Box |
| 1597340000 | SL 3.5/15/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 15, 90°, Box |
| 1597350000 | SL 3.5/16/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 16, 90°, Box |
| 1618990000 | SL 3.5/17/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 17, 90°, Box |
| 1619000000 | SL 3.5/18/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 18, 90°, Box |
| 1619010000 | SL 3.5/19/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 19, 90°, Box |
| 1619020000 | SL 3.5/20/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 20, 90°, Box |
| 1619030000 | SL 3.5/21/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 21, 90°, Box |
| 1619040000 | SL 3.5/22/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 22, 90°, Box |
| 1619050000 | SL 3.5/23/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 23, 90°, Box |
| 1619060000 | SL 3.5/24/90 3.2SN OR | PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 24, 90°, Box |