



# **SPECIFICATION**

(Reference sheet)

• Supplier : Samsung electro-mechanics • Samsung P/N : CL05A435MR5NWNC


• Product : Multi-layer Ceramic Capacitor • Description : CAP, 4.3 µF, 4V, ±20%, X5R, 0402


# A. Samsung Part Number

<u>CL</u> <u>05</u> <u>A</u> <u>435</u> <u>M</u> <u>R</u> <u>5</u> <u>N</u> <u>W</u> <u>N</u> <u>C</u> ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

1	Series	Samsung Multi-layer Ceramic Capacitor			
2	Size	0402 (inch code)	L: 1.05 ± 0.05 mm	W: 0.65 ± 0.05 mm	
3	Dielectric	X5R	Inner electrode	Ni	
4	Capacitance	<b>4.3</b> μF	Termination	Cu	
(5)	Capacitance	±20 %	Plating	Sn 100% (Pb Free)	
	tolerance		Product	3-Terminal	
6	Rated Voltage	4 V	10 Special	Reserved for future use	
7	Thickness	0.45 ±0.05 mm	11) Packaging	Cardboard Type, 7" reel	

# **B. Structure and Dimensions**





Samsung P/N	Dimension(mm)					
(Lead Free)	L	W	Т	A	BW B	С
CL05A435MR5NWNC	1.05±0.05	0.65±0.05	0.45±0.05	0.17±0.10	0.35±0.10	0.15±0.10

### C. Samsung Reliability Test and Judgement condition

	Performance	Test condition		
Capacitance	Within specified tolerance	*A capacitor prior to measuring the capacitance is heat treated at 150 °C+0/-10 °C for 1hour and maintained in		
Tan δ (DF)	0.125 max.	ambient air for 24±2 hours.		
Insulation	10,000Mohm or 50Mohm. <i>µ</i> F	Rated Voltage 60~120 sec.		
Resistance	Whichever is smaller			
Appearance	No abnormal exterior appearance	Visual inspection		
Withstanding No dielectric breakdown or		250% of the rated voltage		
Voltage	mechanical breakdown			
Temperature	X5R			
Characteristics	(From -55℃ to 85℃, Capacitance chang	ge should be within ±15%)		
Adhesive Strength	No peeling shall be occur on the	500g·F, for 10±1 sec.		
of Termination	terminal electrode			
Bending Strength	Capacitance change: within ±12.5%	Bending to the limit (1mm)		
		with 1.0mm/sec.		
Solderability	More than 75% of terminal surface	SnAg3.0Cu0.5 solder		
	is to be soldered newly	245±5℃, 3±0.3sec.		
		(preheating : 80~120 °C for 10~30sec.)		
Resistance to	Capacitance change: within ±7.5%	Solder pot : 270±5 ℃, 10±1sec.		
Soldering heat	Tan δ, IR : initial spec.			
Vibration Test	Capacitance change: within ±5%	Amplitude : 1.5mm		
	Tan δ, IR : initial spec.	From 10Hz to 55Hz (return : 1min.)		
		2hours × 3 direction (x, y, z)		
Moisture	Capacitance change: within ±12.5%	With rated voltage		
Resistance	Tan δ : 0.25 max	40±2℃, 90~95%RH, 500+12/-0hrs		
	IR : 500Mohm or 8.8 Mohm $\cdot \mu$ F			
	Whichever is smaller			
High Temperature	Capacitance change: within ±12.5%	With 100% of the rated voltage		
Resistance	Tan δ : 0.25 max	Max. operating temperature		
	IR : 1,000Mohm or 17.7Mohm · μF			
	Whichever is smaller	1000+48/-0hrs		
Temperature	Capacitance change : within ±10%	1 cycle condition		
Cycling	Tan δ, IR : initial spec.	Min. operating temperature → 25 °C		
		→ Max. operating temperature → 25°C		
		5 cycle test		
Vibration Test  Moisture Resistance  High Temperature Resistance  Temperature	Capacitance change: within ±5% Tan δ, IR: initial spec.  Capacitance change: within ±12.5% Tan δ: 0.25 max IR: 500Mohm or 8.8 Mohm · μF	From 10Hz to 55Hz (return : 1min.) 2hours × 3 direction (x, y, z)  With rated voltage 40±2°C, 90~95%RH, 500+12/-0hrs  With 100% of the rated voltage Max. operating temperature  1000+48/-0hrs 1 cycle condition Min. operating temperature → 25°C → Max. operating temperature → 25°C		

<sup>\*</sup> The reliability test condition can be replaced by the corresponding accelerated test condition.

### D. Recommended Soldering method :

Reflow (Reflow Peak Temperature: 260±5°C, 30sec.)

Product specifications included in the specifications are effective as of March 1, 2013.

Please be advised that they are standard product specifications for reference only.

We may change, modify or discontinue the product specifications without notice at any time.

So, you need to approve the product specifications before placing an order.

Should you have any question regarding the product specifications, please contact our sales personnel or application engineers.

This MLCC with the test voltage at 100% of the rated voltage in the high temperature resistance test should be applied with the derating voltage and temperature according to 3-1 derating guide