


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19 .
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
AJ	16				C	OBS -2 PER 0U20-0072-01	16APR01	M0

- ① PHOSPHOR BRONZE PER QQ-B-750
- ② ZINC PER QQ-Z-363
- ③ POLYMETHYLPENTENE: GENERAL PURPOSE
- ④ NICKEL PLATE PER QQ-N-290, 3.81µm [.000150] MIN THICKNESS
- ⑤ GOLD PLATE PER MIL-G-45204, 0.38µm [.000015] MIN THICKNESS



OBSOLETE	414414-2
	414414-1
PART NUMBER	

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.05 [∅.002] 3 PLC DEC ± - ANGLES ± -		DR 9-8-92 M.E. COWHER	AMP AMP Incorporated Harrisburg, PA 17105-3608		
MATERIAL ① ② ③		CHK 9-14-92 M. PHILLIPS			
FINISH ④ ⑤		APPD 9-14-92 M. PHILLIPS	NAME JACK ADAPTER ASSEMBLY, COML BNC		
		APPD 9-14-92 M.E. COWHER	SIZE B	CAGE CODE 00779	DRAWING NO C-414414
		PRODUCT SPEC -	SCALE 4:1		SHEET 1 OF 1
		APPLICATION SPEC -			
		WEIGHT -			

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.