TOSHIBA CMOS Digital Integrated Circuit Silicon Monolithic

TC74VHC02F,TC74VHC02FN,TC74VHC02FT,TC74VHC02FK

Quad 2-Input NOR Gate

The TC74VHC02 is an advanced high speed CMOS 2-INPUT NOR GATE fabricated with silicon gate C²MOS technology.

It achieves the high speed operation similar to equivalent Bipolar Schottky TTL while maintaining the CMOS low power dissipation.


The internal circuit is composed of 3 stages including buffer output, which provide high noise immunity and stable output.

An input protection circuit ensures that 0 to 5.5~V can be applied to the input pins without regard to the supply voltage. This device can be used to interface 5~V to 3~V systems and two supply systems such as battery back up. This circuit prevents device destruction due to mismatched supply and input voltages.

Features

- High speed: $t_{pd} = 3.6$ ns (typ.) at $V_{CC} = 5$ V
- Low power dissipation: $I_{CC} = 2 \mu A \text{ (max)}$ at $T_{a} = 25 \text{°C}$
- High noise immunity: V_{NIH} = V_{NIL} = 28% V_{CC} (min)
- Power down protection is provided on all inputs.
- Balanced propagation delays: $t_{pLH} \simeq t_{pHL}$
- Wide operating voltage range: V_{CC} (opr) = 2 V to 5.5 V
- Low noise: VOLP = 0.8 V (max)
- Pin and function compatible with 74ALS02

Note: xxxFN (JEDEC SOP) is not available in Japan.



Weight


 SOP14-P-300-1.27A
 : 0.18 g (typ.)

 SOL14-P-150-1.27
 : 0.12 g (typ.)


 TSSOP14-P-0044-0.65A
 : 0.06 g (typ.)

 VSSOP14-P-0030-0.50
 : 0.02 g (typ.)

Pin Assignment



IEC Logic Symbol



Truth Table

Α	В	Υ
L	L	Н
L	Н	L
Н	L	L
Н	Н	L

Absolute Maximum Ratings (Note)

Characteristics	Symbol	Rating	Unit
Supply voltage range	V _{CC}	−0.5 to 7.0	V
DC input voltage	V _{IN}	-0.5 to 7.0	V
DC output voltage	Vout	-0.5 to V _{CC} + 0.5	V
Input diode current	lik	-20	mA
Output diode current	lok	±20	mA
DC output current	Гоит	±25	mA
DC V _{CC} /ground current	Icc	±50	mA
Power dissipation	PD	180	mW
Storage temperature	T _{stg}	-65 to 150	°C

Note: Exceeding any of the absolute maximum ratings, even briefly, lead to deterioration in IC performance or even destruction.

Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings and the operating ranges.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).



Operating Ranges (Note)

Characteristics	Symbol	Rating	Unit	
Supply voltage	V _{CC}	2.0 to 5.5	V	
Input voltage	V _{IN}	0 to 5.5	V	
Output voltage	V _{OUT}	0 to V _{CC}	V	
Operating temperature	T _{opr}	−40 to 85	°C	
Input rise and fall time	dt/dv	0 to 100 (V _{CC} = 3.3 ± 0.3 V)	ns/V	
input rise and fair time	ui/uv	0 to 20 (V _{CC} = 5 ± 0.5 V)		

Note: The operating ranges must be maintained to ensure the normal operation of the device. Unused inputs must be tied to either VCC or GND.

Electrical Characteristics

DC Characteristics

Characteristics Symbol		Test Condition V _{CC} (V)		Ta = 25°C			Ta = -40 to 85°C		Unit		
				V _{CC} (V)	Min	Тур.	Max	Min	Max	OTHE	
High-level input voltage	V _{IH}	_		2.0 3.0 to 5.5	1.50 V _{CC} × 0.7	_ _	1 1	1.50 V _{CC} × 0.7	1 1	٧	
Low-level input voltage	V_IL	_		2.0 3.0 to 5.5	_ _	_ _	0.50 V _{CC} × 0.3		0.50 V _{CC} × 0.3	V	
High-level output voltage	Voн	V _{IN} = V _{IL}	Ι _{ΟΗ} = -50 μΑ	2.0 3.0 4.5	1.9 2.9 4.4	2.0 3.0 4.5	_ _ _	1.9 2.9 4.4	_ 	٧	
			$I_{OH} = -4 \text{ mA}$ $I_{OH} = -8 \text{ mA}$	3.0 4.5	2.58 3.94	_	_	2.48 3.80	_		
Low-level output voltage V_{OL} $V_{IN} = V_{II}$ V_{IL}	= V _{IH} or		2.0 3.0 4.5	_ _ _	0.0 0.0 0.0	0.1 0.1 0.1	_ 	0.1 0.1 0.1	V		
		VIL	$I_{OL} = 4 \text{ mA}$ $I_{OL} = 8 \text{ mA}$		_	_	0.36 0.36	_	0.44 0.44		
Input leakage current	I _{IN}	V _{IN} = 5.5 V or GND		0 to 5.5	_	_	±0.1	ı	±1.0	μΑ	
Quiescent supply current	Icc	V _{IN} = V _{CC} or GND		5.5	_	_	2.0	_	20.0	μΑ	

3



AC Characteristics (input: $t_r = t_f = 3 \text{ ns}$)

Characteristics Symbol	Symbol	Test Condition		Ta = 25°C			Ta = −40 to 85°C		Unit	
	- ,		V _{CC} (V)	C _L (pF)	Min	Тур.	Max	Min	Max	
Propagation delay tpLH time tpHL		_	3.3 ± 0.3	15	_	5.6	7.9	1.0	9.5	- ns
	·			50	_	8.1	11.4	1.0	13.0	
			5.0 ± 0.5	15	_	3.6	5.5	1.0	6.5	
				50	_	5.1	7.5	1.0	8.5	
Input capacitance	C _{IN}	_			_	4	10	_	10	pF
Power dissipation capacitance	C _{PD}			(Note)	_	15	_	_	_	pF

Note: C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load.


Average operating current can be obtained by the equation:

 $I_{CC (opr)} = C_{PD} \cdot V_{CC} \cdot f_{IN} + I_{CC}/4 \text{ (per gate)}$

Noise Characteristics (input: $t_r = t_f = 3 \text{ ns}$)


Characteristics	Symbol	Test Condition	Ta =	- Unit		
Characteristics	Symbol		V _{CC} (V)	Тур.	Limit	Offic
Quiet output maximum dynamic V _{OL}	V _{OLP}	C _L = 50 pF	5.0	0.3	8.0	V
Quiet output minimum dynamic V _{OL}	V _{OLV}	C _L = 50 pF	5.0	-0.3	-0.8	V
Minimum high level dynamic input voltage	V _{IHD}	C _L = 50 pF	5.0	_	3.5	V
Maximum low level dynamic input voltage	V _{ILD}	C _L = 50 pF	5.0	_	1.5	V

Input Equivalent Circuit



Package Dimensions

SOP14-P-300-1.27A Unit: mm




5

Weight: 0.18 g (typ.)



Package Dimensions (Note)



6


Note: This package is not available in Japan.


Weight: 0.12 g (typ.)


Package Dimensions


TSSOP14-P-0044-0.65A

Unit: mm










Weight: 0.06 g (typ.)

Package Dimensions

VSSOP14-P-0030-0.50 Unit: mm



8

Weight: 0.02 g (typ.)

RESTRICTIONS ON PRODUCT USE

- Toshiba Corporation, and its subsidiaries and affiliates (collectively "TOSHIBA"), reserve the right to make changes to the information in this document, and related hardware, software and systems (collectively "Product") without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before creating and producing designs and using, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application that Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- Product is intended for use in general electronics applications (e.g., computers, personal equipment, office equipment, measuring equipment, industrial robots and home electronics appliances) or for specific applications as expressly stated in this document. Product is neither intended nor warranted for use in equipment or systems that require extraordinarily high levels of quality and/or reliability and/or a malfunction or failure of which may cause loss of human life, bodily injury, serious property damage or serious public impact ("Unintended Use"). Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, devices related to electric power, and equipment used in finance-related fields. Do not use Product for Unintended Use unless specifically permitted in this document
- · Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any
 applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE
 FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY
 WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR
 LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND
 LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO
 SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS
 FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without
 limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile
 technology products (mass destruction weapons). Product and related software and technology may be controlled under the
 Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product
 or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product.
 Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. TOSHIBA assumes no liability for damages or losses occurring as a result of noncompliance with applicable laws and regulations.