CPC1973Y Power SIP Relay





	RF	any	

	CPC1973Y	Units
Blocking Voltage	400	V _P
Load Current	0.35	A _{rms}
On-Resistance	5	Ω

Features

- Power SIP Package
- · Handle Load Currents Up to 0.5A
- · High Reliability
- No Moving Parts
- Low Drive Power Requirements (TTL/CMOS Compatible)
- Arc-Free With No Snubbing Circuits
- 2500V_{rms} Input/Output Isolation
- No EMI/RFI Generation
- · Machine Insertable, Wave Solderable

Applications

- Industrial Controls
- Motor Control
- Robotics
- Medical Equipment—Patient/Equipment Isolation
- Instrumentation
 - Multiplexers
 - · Data Acquisition
 - · Electronic Switching
 - I/O Subsystems
 - Meters (Watt-Hour, Water, Gas)
- IC Equipment
- Home Appliances

Description

Clare and IXYS have combined to bring OptoMOS[®] technology, reliability and compact size to a new family of high power solid state relays. As part of that family, the CPC1973Y is a 1-Form-A solid state relay. The CPC1973Y employs optically coupled MOSFET technology to provide 2500V_{rms} of input to output isolation. The efficient MOSFET switches and photovoltaic die use Clare's patented OptoMOS architecture while the input is controlled by a highly efficient GaAIAs infrared LED. The combination of low on resistance and high load current handling capabilities makes the relay suitable for a variety of high performance switching applications.

Approvals


- UL recognized component: File # E69938
- Certified to: UL 508

Ordering Information


Part #	Description
CPC1973Y	Power SIP Package (25 per tube)

Pin Configuration

CPC1973Y Pinout



Switching Characteristics of Normally Open (Form A) Devices





Absolute Maximum Ratings (@ 25° C)

Parameter	Ratings	Units
Blocking Voltage	400	V _P
Reverse Input Voltage	5	V
Input control Current	50	mA
Peak (10ms)	1	А
Input Power Dissipation ¹	150	mW
Isolation voltage Input to Output	2500	V _{rms}
Operational Temperature	-40 to +85	°C
Storage Temperature	-40 to +125	°C

Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at conditions beyond those indicated in the operational sections of this data sheet is not implied.

¹ Derate Linearly 3.33 mw / °C

Electrical Characteristics

Parameter	Conditions	Symbol	Min	Тур	Max	Units
Output Characteristics @ 25°C	·		•	,		
Load Current, Continuous	free air	ΙL	-	-	0.35	A _{rms}
Peak Load Current	T=10ms	I _{LPK}	-	-	3.5	A _{rms}
On-Resistance ¹	I _L =350mA	R _{on}	-	3.4	5	Ω
Off-State Leakage Current	V _L =400V	ILEAK	-	-	1	μA
Switching Speeds Turn-On	I _F =10mA, V _L =10V	T _{ON}	-	-	5	ms
Turn-Off	I _F =10mA, V _L =10V	T _{OFF}	-	-	3	ms
Input Characteristics @ 25°C						
Input Control Current	I _L =350mA	I _F	10	-	-	mA
Input Dropout Current	-	I _F	-	-	-	mA
Input Voltage Drop	I _F =5mA	V _F	0.9	1.2	1.4	V
Reverse Input Current	V _R =5V	I _B	-	-	10	μA
Input/Output Characteristics @ 25°C						
Capacitance Input/Output	f=1MHz	C _{1/0}	-	2	-	pF
Load current derates linearly from 600mA @ 25°C to 480mA @80°C				2		

 1 Load current derates linearly from 600mA @ 25°C to 480mA @80°C. 2 Measurement taken within 1 second of on time.


³ For applications requiring high temperature operation (greater than 60°C) an LED drive current of 3mA is recommended.


Thermal Characteristics


Parameter	Conditions	Symbol	Min	Тур	Мах	Units
Thermal Resistance (junction to case)	-	R _{eJC}	-	1.5	-	°C/W



PERFORMANCE DATA*







CPC1973Y Typical Turn-Off Time

(N=50 Ambient Temperature = 25° C) (Load Current = $0.5A_{DC}$; I_F = $10mA_{DC}$)

0.008 0.010 0.012 0.014 0.016 0.018 0.020

Turn-Off (ms)

25

20


15


10


5


0


Device Count (N)























*The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.




PERFORMANCE DATA*









*The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.



Manufacturing Information


Soldering

Recommended soldering processes are limited to 245°C component body temperature for 10 seconds.

Washing

Clare does not recommend ultrasonic cleaning or the use of chlorinated solvents.

MECHANICAL DIMENSIONS



NOTE: Pin location tolerances are non-cumulative.

Dimensions: inches (mm)

For additional information please visit our website at: www.clare.com

Clare, Inc. makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to specifications and product descriptions at any time without notice. Neither circuit patent licenses nor indemnity are expressed or implied. Except as set forth in Clare's Standard Terms and Conditions of Sale, Clare, Inc. assumes no liability whatsoever, and disclaims any express or implied warranty, relating to its products including, but not limited to, the implied warranty of merchantability, fitness for a particular purpose, or infringement of any intellectual property right.

The products described in this document are not designed, intended, authorized or warranted for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or where malfunction of Clare's product may result in direct physical harm, injury, or death to a person or severe property or environmental damage. Clare, Inc. reserves the right to discontinue or make changes to its products at any time without notice.

Specification: DS-CPC1973Y-R03 @Copyright 2005, Clare, Inc. OptoMOS[®] is a registered trademark of Clare, Inc. All rights reserved. Printed in USA. 5/26/05