

GP1S74PJ000F

Gap: 5mm Slit: 0.5mm
Phototransistor Output,
Snap-in fixing
Transmissive Photointerrupter with
Connector

■ Description

GP1S74PJ000F is a standard, phototransistor output, transmissive photointerrupter with opposing emitter and detector in a case, providing non-contact sensing. For this family of devices, the emitter and detector are inserted in a case, and a 3-pin connector is included to allow remote-mount or off-board designs.

■ Features

- 1. Transmissive with phototransistor output
- 2. Highlights:
 - Special position hooks compatible with 3 different plate thicknesses (1.0, 1.2, 1.6mm)
 - Snap insertion
- 3. Key Parameters:
 - · Gap Width: 5mm
 - · Slit Width (detector side): 0.5mm
 - Package: 17×12.8×8mm (without connector and hooks)
 - Connector: Tyco Electronics AMP K.K.

(PN: 292133-3)

4. Lead free and RoHS directive compliant

■ Agency approvals/Compliance

1. Compliant with RoHS directive


■ Applications

- General purpose detection of object presence or motion.
- 2. Example: PPC, FAX, Printer


1



■ Internal Connection Diagram



Product mass: approx. 0.8g



Connector terminal plating material: Sn



Date code (2 digit)				
1st digit		2nd digit		
Year of production		Month of production		
A.D.	Mark	Month	Mark	
2000	0	1	1	
2001	1	2	2	
2002	2	3	3	
2003	3	4	4	
2004	4	5	5	
2005	5	6	6	
2006	6	7	7	
2007	7	8	8	
2008	8	9	9	
2009	9	10	X	
2010	0	11	Y	
:	:	12	Z	

repeats in a 10 year cycle

Country of origin

Japan or Philippines (Indicated on the packing case)



■ Absolute Maximum Ratings (T _a =25				
	Parameter	Symbol	Rating	Unit
	*1 Forward current	I_{F}	50	mA
Innut	*1, ² Peak forward current	I_{FM}	1	A
Input	Reverse voltage	V_R	6	V
	Power dissipation	P	75	mW
	Collector-emitter voltage	V_{CEO}	35	V
Output	Emitter-collector voltage	V_{ECO}	6	V
Output	Collector current	I_{C}	20	mA
	*1 Collector power dissipation	P _C	75	mW
*3Operating temperature		T _{opr}	-25 to +85	°C
*3Storage temperature		T_{stg}	_40 to +85	°C

■ Electro-optical Characteristics

 $(T_a=25^{\circ}C)$

•							,	ra-25 C)
Parameter		Symbol	Condition	MIN.	TYP.	MAX.	Unit	
	Forward voltage		$V_{\rm F}$	I _F =20mA	_	1.2	1.4	V
Input	Input Peak forward voltage		V_{FM}	I _{FM} =0.5A		3	4	V
Reverse current		I_R	$V_R=3V$	_	_	10	μΑ	
Output	out Collector dark current		I_{CEO}	V _{CE} =20V	_	1	100	nA
Transfor	Collector current		I_{C}	V _{CE} =5V, I _F =20mA	0.5	_	15	mA
Transfer Collector-emitter saturation v		ration voltage	V _{CE(sat)}	I _F =40mA, I _C =0.5mA	_	-	0.4	V
teristics Response time	Ri	Rise time	t _r	V 2V I 2 A P 1000	_	3	15	
	Fall time	$t_{\rm f}$	$V_{CE}=2V$, $I_{C}=2mA$, $R_{L}=100\Omega$	_	4	20	μs	

^{*1} Refer to Fig. 1, 2, 3
*2 Pulse width ≤ 100μs, Duty ratio=0.01
*3 The connector should be plugged in/out at normal temperature.



Fig.1 Forward Current vs. Ambient Temperature




Fig.3 Peak Forward Current vs. Duty Ratio




Fig.5 Collector Current vs. Forward Current




Fig.2 Collector Power Dissipation vs. Ambient Temperature




Fig.4 Forward Current vs. Forward Voltage




Fig.6 Collector Current vs.
Collector-emitter Voltage






Fig.7 Collector Current vs.

Ambient Temperature




Fig.9 Response Time vs. Load Resistance




Fig.11 Frequency Response




Fig.8 Collector-emitter Saturation Voltage vs. Ambient Temperature




Fig.10 Test Circuit for Response Time




Fig.12 Collector Dark Current vs.
Ambient Temperature








Fig.13 Detecting Position Characteristics (1)

Fig.14 Detecting Position Characteristics (2)





Remarks: Please be aware that all data in the graph are just for reference and not for guarantee.



■ Design Considerations

Design guide


1) Prevention of detection error

To prevent photointerrupter from faulty operation caused by external light, do not set the detecting face to the external light.

2) Position of opaque board

Opaque board shall be installed at place 4mm or more from the top of elements.

(Example)



This product is not designed against irradiation and incorporates non-coherent IRED.

Degradation

In general, the emission of the IRED used in photocouplers will degrade over time.

In the case of long term operation, please take the general IRED degradation (50% degradation over 5 years) into the design consideration.

Parts

This product is assembled using the below parts.

• Photodetector (qty.: 1)

Category	Material	Maximum Sensitivity wavelength (nm)	Sensitivity wavelength (nm)	Response time (μs)
Phototransistor	Silicon (Si)	930	400 to 1 200	3

• Photo emitter (qty.: 1)

Category	Material	Maximum light emitting wavelength (nm)	I/O Frequency (MHz)
Infrared emitting diode (non-coherent)	Gallium arsenide (GaAs)	950	0.3

Material


Case	Lead frame	Connector terminal finish
Black polycarbonate resin (UL94 V-2)	42Alloys (No plating)	Sn plating




Recommended Installation Hole drawing

- 1) We recommend to fix the product at punching side on the fixing plate (metal plate).
- 2) Please decide the final dimensions at your side after confirmation by the actual applications. Because mounting efficiency and mounted stabilization are dependent on mounting hole corner curve and punched state.
- 3) Tolerance shall be ±0.1mm

Normal type



Reverse-insertion prevention type





■ Manufacturing Guidelines

Notes of cleaning

Please carry out neither the immersion cleaning nor the ultrasonic cleaning to avoid the solvent residue inside the case.

When necessary, dust and stain shall clean by air-blow or wipe off by soft cloth soaked in cleaning agent. The cleaning agent used to wipe off must use only the following kind. Ethyl alcohol, Methyl alcohol and Isopropyl alcohol.

Presence of ODC

This product shall not contain the following materials.

And they are not used in the production process for this product.

Regulation substances: CFCs, Halon, Carbon tetrachloride, 1.1.1-Trichloroethane (Methylchloroform)

Specific brominated flame retardants such as the PBBOs and PBBs are not used in this product at all.

This product shall not contain the following materials banned in the RoHS Directive (2002/95/EC).

•Lead, Mercury, Cadmium, Hexavalent chromium, Polybrominated biphenyls (PBB), Polybrominated diphenyl ethers (PBDE).



■ Package specification

Case package

Package materials

Anti-static plastic bag: Polyethtylene

Moltopren: Urethane

Partition: Corrugated fiberboard
Packing case: Corrugated fiberboard


Package method

100 pcs of products shall be packaged in a plastic bag, Ends shall be sealed by stapler. The bottom of the packing case is covered with moltopren, and the partition is set in the packing case. Each partition should have 1 plastic bag.

The 10 plastic bags containing a product are put in the packing case.

Moltopren should be located after all product are settled (1 packing conteains 1 000 pcs).

Packing composition





■ Important Notices

- The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- · Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- · Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:
- (i) The devices in this publication are designed for use in general electronic equipment designs such as:
 - --- Personal computers
 - --- Office automation equipment
 - --- Telecommunication equipment [terminal]
 - --- Test and measurement equipment
 - --- Industrial control
 - --- Audio visual equipment
 - --- Consumer electronics
- (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection

with equipment that requires higher reliability such as:

- --- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
- --- Traffic signals
- --- Gas leakage sensor breakers
- --- Alarm equipment
- --- Various safety devices, etc.
- (iii) SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:
 - --- Space applications
 - --- Telecommunication equipment [trunk lines]
 - --- Nuclear power control equipment
 - --- Medical and other life support equipment (e.g., scuba).
- · If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- · Contact and consult with a SHARP representative if there are any questions about the contents of this publication.