GP1A30R

■ Features

- 1. 2-phase (A, B) digital output
- 2. Possible to use plastic disk
- 3. High sensing accuracy (Disk slit pitch: 0.7mm)
- 4. TTL compatible output
- 5. Compact and light

■ Applications

- 1. Electronic typewriters, printers
- 2. Numerical control machines

■ Absolute Maximum Ratings


 $(Ta=25^{\circ}C)$

Parameter		Symbol	Rating	Unit	
Input	Forward current	I_F	65	mA	
	*1Peak forward current	I _{FM}	1	Α	
	Reverse voltage	V _R	6	V	
	Power dissipation	P	100	mW	
Output	Supply voltage	V _{CC}	7	V	
	Low level output current	IoL	20	mA	
	Power dissipation	Po	250	mW	
Operating temperature		Topr	0 to + 70	°C	
Storage temperature		T_{stg}	- 40 to + 80	°C	
*2Soldering temperature		Tsol	260	°C	


^{*1} Pulse width $\leq 100 \mu s$, Duty ratio= 0.01


OPIC Photointerrupter with Encoder Function

■ Outline Dimensions









4 ± 0.15

10.5^{MIN.}

* Tolerance:± 0.3mm *(): Reference dimensions

*"OPIC" (Optical IC) is a trademark of the SHARP Corporation.

An OPIC consists of a light-detecting element and signalprocessing circuit integrated onto a single chip.

■ Electro-optical Characteristics

(Unless otherwise specified, $Ta = 0 \text{ to} + 70^{\circ}\text{C}$)

Parameter		Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Input	Forward voltage	VF	Ta= 25°C, I _F = 30mA	-	1.2	1.5	V
	Reverse current	I_R	Ta= 25° C, V _R = 3 V	-	-	10	μΑ
Output -	Operating supply voltage	Vcc		4.5	5.0	5.5	V
	High level output voltage	V _{OH}	*3V _{CC} = 5V, I _F = 30mA	2.4	4.9	-	V
	Low level output voltage	Vol	$^{*3}I_{OL} = 8mA, V_{CC} = 5V, I_F = 30mA$	-	0.1	0.4	V
	Supply current	Icc	$^{*3*4}I_F = 30mA, V _{CC} = 5V$	-	5	20	mA
Transfer characteristics	Duty ratio	*5DA	$V_{CC}=5V$, $I_{F}=30mA$,	20	50	80	%
		*5D _B	*3f= 2.5kHz	20	50	80	%
	Response frequency	f MAX.	*3V _{CC} = 5V, I _F = 30mA	-	-	5	kHz

^{*3} Measured under the condition shown in Measurement Conditions.


$$D_A = \frac{t_{AH}}{t_{AP}} \times 100, \ D_B = \frac{t_{BH}}{t_{BP}} \times 100$$

" In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that occur in equipment using any of SHARP's devices, shown in catalogs, data books, etc. Contact SHARP in order to obtain the latest version of the device specification sheets before using any SHARP's device."

^{*2} For 5 seconds

^{*4} In the condition that output A and B are low level.

■ Output Waveforms



Rotational direction: Counterclockwise when seen from OPIC light detector

Fig. 1 Forward Current vs. Ambient Temperature




Fig. 3 Duty Ratio vs. Frequency




Fig. 2 Output Power Dissipation vs.
Ambient Temperature




Fig. 4 Phase Difference vs. Frequency




Fig. 5 Duty Ratio vs. Ambient Temperature




Fig. 7 Duty Ratio vs. Distance (X direction)




Fig. 9 Duty Ratio vs. Distance (Y direction)




Fig. 6 Phase Difference vs. Ambient Temperature




Fig. 8 Phase Difference vs.
Distance (X direction)




Fig.10 Phase Difference vs.
Distance (Y direction)






Fig.11 Duty Ratio vs. Distance (Z direction)




■ Measurement Conditions



■ Precautions for Use

- (1) This module is designed to be operated at $I_F=30 \text{mA}$ TYP.
- (2) Fixing torque: MAX. 0.6Nm (6kgf cm)
- (3) In order to stabilize power supply line, connect a by-pass capacitor of more than 0.01μF between Vcc and GND near the device.
- (4) As for other general cautions, refer to the chapter "Precautions for Use".

Fig.12 Phase Difference vs.
Distance (Z direction)



<Basic Design>

 $R_{\rm O}$ (distance between the disk center and half point of a slit), P (slit pitch), $S_{\rm 1}$ and $S_{\rm 2}$ (installing position of photointer-rupter) will be provided by the following equations.


Slit pitch: P (slit center)

$$R_0 = \frac{N}{120} \times 13.45 \text{ (mm)} \quad N: \text{ number of slits}$$

$$P = \frac{2x \text{ p. x. } R_0}{N} \text{ (mm)}$$

$$S_1 = R_{O} - 1.765 (mm), S_2 = S_1 + 6.7 (mm)$$

Note) When the number of slits is changed, values in parenthesis are also changed according to the number.



NOTICE

- •The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- •Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:
 - (i) The devices in this publication are designed for use in general electronic equipment designs such as:
 - Personal computers
 - Office automation equipment
 - Telecommunication equipment [terminal]
 - Test and measurement equipment
 - Industrial control
 - Audio visual equipment
 - Consumer electronics
 - (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection with equipment that requires higher reliability such as:
 - Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
 - Traffic signals
 - Gas leakage sensor breakers
 - Alarm equipment
 - Various safety devices, etc.
 - (iii) SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:
 - Space applications
 - Telecommunication equipment [trunk lines]
 - Nuclear power control equipment
 - Medical and other life support equipment (e.g., scuba).
- •Contact a SHARP representative in advance when intending to use SHARP devices for any "specific" applications other than those recommended by SHARP or when it is unclear which category mentioned above controls the intended use.
- •If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Control Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- •This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- Contact and consult with a SHARP representative if there are any questions about the contents of this
 publication.