

STV-674/502V-R01

Reference design for STV0674 Digital Processor and VS6502VF VGA CMOS Sensor

DATA BRIEFING

Features

Camera Mode

- Still image capture
- Movie clip capture (synchronized audio\video)
- Audio Clip capture

WebCam Mode

- DirectShow Driver Support
- Real-time video up to 30fps VGA
- Real-time audio
- DirectCap sample DirectShow application

Native Mass Storage (NMS) Mode

- Flash memory
- Behaves as removable disk drive for data storage when tethered
- •~400Kbyte/s Write ~500Kbytes/s Read.

Description

The STV-674/502V-R01 reference design is intended to represent an actual production solution for a flashdrive memory with built-in camera.

Images, audio and video clips are stored in the DOS-formatted on-board NAND. When the board is tethered over USB it will appear as either a disc drive in NMS mode or a USB composite device in webcam mode.

The VS6502V/F is a VGA resolution SmOP sensor module. SmOP technology combines the image sensor and fixed focus lens system in a single module.

The RDK includes the following:

- Reference design board
- Schematic and BOM
- USB cable
- Application software
- User manual

Minimum Requirements

- IBM PC or compatible
- Windows 98SE, Win ME, Win2K + SP3 or WinXP + SP1 Operating System
- DirectX8.1 or later
- Graphics Adapter capable of 800x600 resolution, 64k colours ("thousands of colours")
- CDROM drive
- PII 266 with 64M RAM (Win98/ME) or 128M RAM (Win2K/XP)
- NMS supported on Mac OSX & MacOS9

Technical documentation

Datasheet

STV0674 - CMOS digital camera signal processor

User manuals

User manual for STV-674/502V-R01 reference kit.

Tri- mode camera reference design for STV0674 companion processor and VS6502V VGA CMOS sensor with nand flash

Ordering Information

Sale type	Description
STV0674T100	CMOS digital camera signal processor
VS6502V015	Sensor module with socket option.
VS6502F015	Sensor module with flex option.
STV-674/502V-R01	Reference design for STV0674 digital processor and VS6502V CMOS image sensor with VGA output resolution

لرکم

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is a registered trademark of STMicroelectronics

© 2003 STMicroelectronics - All Rights Reserved

Purchase of I²C Components by STMicroelectronics conveys a license under the Philips I²C Patent. Rights to use these components in an I²C system is granted provided that the system conforms to the I²C Standard Specification as defined by Philips.

STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - Canada - China - Finland - France - Germany - Hong Kong - India - Israel -Italy - Japan - Malaysia - Malta-Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States

www.st.com