

PR22MA11NTZ Series PR32MA11NTZ Series

I_T(rms)≤0.15A, Non-Zero Cross type DIP 6pin SSR



■ Description

PR22MA11NTZ Series and PR32MA11NTZ Series

Solid State Relays (SSR) are an integration of an infrared emitting diode (IRED), a Phototriac Detector. These devices are ideally suited for controlling high voltage AC loads with solid state reliability while providing 5.0kV isolation ($V_{iso}(rms)$) from input to output.

■ Features

- 1. Output current, I_T(rms)≤0.15A
- 2. Non-zero crossing functionary
- 3. 6 pin DIP package, (SMT gullwing also available)
- 4. High repetitive peak off-state voltage

(V_{DRM}: 600V, PR32MA11NTZ Series)

(V_{DRM}: 400V, PR22MA11NTZ Series)

- 5. Superior noise immunity (dV/dt : MIN. 100V/µs)
- 6. Response time, ton: MAX. 100μs
- 7. Lead-free components are also available (see Model Line-up section in this datasheet)
- 8. Double transfer mold construction (Ideal for Flow Soldering)
- 9. High isolation voltage between input and output (V_{iso}(rms) : 5.0kV)

■ Agency approvals/Compliance


1. Package resin: UL flammability grade (94V-0)

■ Applications

- 1. Isolated interface between high voltage AC devices and lower voltage DC control circuitry.
- 2. Switching small capacity motors, fans, heaters, solenoids, and valves.
- 3. Phase or power control in applications such as lighting and temperature control equipment.



■ Internal Connection Diagram




- 1 Anode
- 2 Cathode
- ③ NC


 θ : 0 to 13°

- 4 Anode/Cathode
- (5) No external connection
- ⑥ Cathode/Anode

■ Outline Dimensions


(Unit: mm)






3. Through-Hole [ex. PR32MA11NTZF]

Product mass: approx. 0.35g





*Pin 5 is not allowed external connection



Date code (2 digit)

	1st o	digit		2nd digit		
	Year of p	roduction		Month of production		
A.D.	Mark	A.D	Mark	Month	Mark	
1990	A	2002	P	January	1	
1991	В	2003	R	February	2	
1992	С	2004	S	March	3	
1993	D	2005	T	April	4	
1994	Е	2006	U	May	5	
1995	F	2007	V	June	6	
1996	Н	2008	W	July	7	
1997	J	2009	X	August	8	
1998	K	2010	A	September	9	
1999	L	2011	В	October	0	
2000	M	2012	С	November	N	
2001	N	:	:	December	D	

repeats in a 20 year cycle

Factory identification mark

Factory identification Mark	Country of origin
no mark	Ionon
	Japan

^{*} This factory marking is for identification purpose only.

Please contact the local SHARP sales representative to see the actural status of the production.

Rank mark


There is no rank mark indicator and currently there are no rank offered for this device.



■ Absolute Maximum Ratings

 $(T_a=25^{\circ}C)$

(1a-23)							
	Parameter	Symbol	Rating	Unit			
Inmust	Forward current		I_{F}	50 *3	mA		
Input	Reverse voltage		V_R	6	V		
	RMS ON-state cu	I _T (rms)	150 *3	mA			
044	Peak one cycle su	rge current	I _{surge}	1.2 *4	A		
Output	Repetitive	PR22MA11NTZ		400	V		
	peak OFF-state voltage	PR32MA11NTZ	VDRM	600			
*1 Isolatic	on voltage		V _{iso} (rms)	5.0	kV		
	ing temperature	Topr	-30 to +85	°C			
Storage	e temperature	T_{stg}	-40 to +125	°C			
*2Solderi	ng temperature		T_{sol}	270 *5	°C		



■ Electro-optical Characteristics

 $(T_a=25^{\circ}C)$

Parameter		Symbol	Conditions	MIN.	TYP.	MAX.	Unit
T4	Forward voltage	$V_{\rm F}$	I _F =20mA	-	1.2	1.4	V
Input	Reverse current	I_R	$V_R=3V$	_	ı	10	μΑ
	Repetitive peak OFF-state current	I_{DRM}	$V_D = V_{DRM}$	_	ı	2.0	μΑ
0	ON-state voltage	V_{T}	I _T =150mA	_	_	3.0	V
Output	Holding current	I_{H}	$V_D=6V$	0.1	_	3.5	mA
	Critical rate of rise of OFF-state voltage	dV/dt	$V_D=1/\sqrt{2} \cdot V_{DRM}$	100	_	-	V/µs
Transfer	Minimum trigger current	I_{FT}	$V_{D}=6V, R_{L}=100\Omega$	-	_	10	mA
charac-	Isolation resistance	R _{ISO}	DC500V,40 to 60%RH	5×10 ¹⁰	10^{11}	_	Ω
teristics	Turn-on time	t _{on}	$V_D = 6V, R_L = 100\Omega, I_F = 20mA$	-	-	100	μs

^{*1 40} to 60%RH, AC for 1minute, f=60Hz

^{*2} For 10s

^{*3} Refer to Fig.1, Fig.2

*4 f=50Hz sine wave

*5 Lead solder plating models: 260°C



■ Model Line-up (1) (Lead-free components)

Lead Form	Through-Hole	SMT Gullwing	37	I _{FT} [mA]	
Chimmin a Doolsooo	Sleeve	Taping	V _{DRM}	$(V_D=6V,$	
Shipping Package	50pcs/sleeve	1 000pcs/reel	[V]	$R_L \!\!=\!\! 100\Omega)$	
Model No.	PR22MA11NTZF	PR22MA11NXPF	400	MAX.10	
Wiodel No.	PR32MA11NTZF	PR32MA11NXPF	600	MAX.10	

■ Model Line-up (2) (Lead solder plating components)

Lead Form	Through-Hole	SMT Gullwing	37	$I_{FT}[mA]$ $(V_D=6V,$ $R_L=100\Omega)$	
Chimnin a Doolsooo	Sleeve	Taping	V _{DRM}		
Shipping Package	50pcs/sleeve	1 000pcs/reel	[V]		
Model No.	PR22MA11NTZ	_	400	MAX.10	
Wiodel No.	PR32MA11NTZ	_	600	IVIAA.1U	

Please contact a local SHARP sales representative to see the actual status of the production.



Fig.1 Forward Current vs. Ambient Temperature




Fig.3 Forward Current vs. Forward Voltage




Fig.5 ON-state Voltage vs.
Ambient Temperature




Fig.2 RMS ON-state Current vs.
Ambient Temperature




Fig.4 Minimum Trigger Current vs.
Ambient Temperature




Fig.6 Holding Current vs.

Ambient Temperature








Fig.7 ON-state Current vs. ON-state Voltage

Fig.8 Turn-on Time vs. Forward Current





Remarks: Please be aware that all data in the graph are just for reference.



■ Design Considerations

Recommended Operating Conditions

Parameter		Symbol	Conditions	MIN.	MAX.	Unit	
T4	Input signal current at ON state		$I_F(ON)$	-	20	25	mA
Input	Input signal current at OFF state		I _F (OFF)	-	0	0.1	mA
	Lood symply voltage	PR22MA11NTZ	V _{OUT} (rms)	-	_	120	V
	Load supply voltage	PR32MA11NTZ				240	
Output	Load supply current		I _{OUT} (rms)	Locate snubber circuit between output terminals (Cs= $0.01\mu F$, Rs= 100Ω)	-	I _T (rms)×80%(*)	mA
	Frequency		f	-	50	60	Hz
Operating temperature			T_{opr}	-	-20	70	°C

^(*) See Fig.2 about derating curve ($I_T(rms)$ vs. ambient temperature).

Design guide

In order for the SSR to turn off, the triggering current (I_F) must be 0.1mA or less.

In phase control applications or where the SSR is being by a pulse signal, please ensure that the pulse width is a minimum of 1ms.

When the input current (I_F) is below 0.1mA, the output Triac will be in the open circuit mode. However, if the voltage across the Triac, V_D , increases faster than rated dV/dt, the Triac may turn on. To avoid this situation, please incorporate a snubber circuit. Due to the many different types of load that can be driven, we can merely recommend some circuit values to start with : $Cs=0.01\mu F$ and $Rs=100\Omega$. The operation of the SSR and snubber circuit should be tested and if unintentional switching occurs, please adjust the snubber circuit component values accordingly.

When making the transition from On to Off state, a snubber circuit should be used ensure that sudden drops in current are not accompanied by large instantaneous changes in voltage across the Triac.

This fast change in voltage is brought about by the phase difference between current and voltage.

Primarily, this is experienced in driving loads which are inductive such as motors and solenods.

Following the procedure outlined above should provide sufficient results.

Any snubber or Varistor used for the above mentioned scenarios should be located as close to the main output triac as possible.

All pins shall be used by soldering on the board. (Socket and others shall not be used.)

Degradation

In general, the emission of the IRED used in SSR will degrade over time.


In the case where long term operation and / or constant extreme temperature fluctuations will be applied to the devices, please allow for a worst case scenario of 50% degradation over 5years.

Therefore in order to maintain proper operation, a design implementing these SSRs should provide at least twice the minimum required triggering current from initial operation.




Recommended Foot Print (reference)

SMT Gullwing Lead-form



(Unit:mm)

Standard Circuit



[☆] For additional design assistance, please review our corresponding Optoelectronic Application Notes.



■ Manufacturing Guidelines


Soldering Method

Reflow Soldering:

Reflow soldering should follow the temperature profile shown below.

Soldering should not exceed the curve of temperature profile and time.

Please don't solder more than twice.



Flow Soldering:

Due to SHARP's double transfer mold construction submersion in flow solder bath is allowed under the below listed guidelines.

Flow soldering should be completed below 270°C and within 10s.

Preheating is within the bounds of 100 to 150°C and 30 to 80s.

Please don't solder more than twice.

Hand soldering

Hand soldering should be completed within 3s when the point of solder iron is below 400°C.

Please don't solder more than twice.

Other notices

Please test the soldering method in actual condition and make sure the soldering works fine, since the impact on the junction between the device and PCB varies depending on the tooling and soldering conditions.



Cleaning instructions

Solvent cleaning:

Solvent temperature should be 45°C or below. Immersion time should be 3minutes or less.

Ultrasonic cleaning:

The impact on the device varies depending on the size of the cleaning bath, ultrasonic output, cleaning time, size of PCB and mounting method of the device.

Therefore, please make sure the device withstands the ultrasonic cleaning in actual conditions in advance of mass production.

Recommended solvent materials:

Ethyl alcohol, Methyl alcohol and Isopropyl alcohol.

In case the other type of solvent materials are intended to be used, please make sure they work fine in actual using conditions since some materials may erode the packaging resin.

Presence of ODC

This product shall not contain the following materials.

And they are not used in the production process for this device.

Regulation substances: CFCs, Halon, Carbon tetrachloride, 1.1.1-Trichloroethane (Methylchloroform)

Specific brominated flame retardants such as the PBBOs and PBBs are not used in this product at all.



■ Package specification

● Sleeve package Through-Hole

Package materials

Sleeve: HIPS (with anti-static material)

Stopper: Styrene-Elastomer

Package method


MAX. 50pcs of products shall be packaged in a sleeve.


Both ends shall be closed by tabbed and tabless stoppers.

The product shall be arranged in the sleeve with its anode mark on the tabless stopper side.

MAX. 20 sleeves in one case.

Sleeve outline dimensions







● Tape and Reel package SMT Gullwing


Package materials

Carrier tape: A-PET (with anti-static material)

Cover tape: PET (three layer system)


Reel: PS

Carrier tape structure and Dimensions




Dimensions List						
A	В	С	D	Е	F	G
16.0±0.3	7.5 ^{±0.1}	1.75 ^{±0.1}	12.0 ^{±0.1}	2.0 ^{±0.1}	4.0 ^{±0.1}	φ1.5 ^{+0.1}
Н	I	J	K			
10.4 ^{±0.1}	0.4±0.05	4.2 ^{±0.1}	7.8 ^{±0.1}			

Reel structure and Dimensions



Dimensio	ns List	(Unit: mm)		
a	b	С	d	
330	330 17.5 ^{±1.5}		13±0.5	
e	f	g		
23 ^{±1.0}	2.0 ^{±0.5}	2.0±0.5		

Direction of product insertion



[Packing: 1 000pcs/reel]



■ Important Notices

- · The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- · Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- · Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:
- (i) The devices in this publication are designed for use in general electronic equipment designs such as:
 - --- Personal computers
 - --- Office automation equipment
 - --- Telecommunication equipment [terminal]
 - --- Test and measurement equipment
 - --- Industrial control
 - --- Audio visual equipment
 - --- Consumer electronics
- (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection

with equipment that requires higher reliability such as:

- --- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
- --- Traffic signals
- --- Gas leakage sensor breakers
- --- Alarm equipment
- --- Various safety devices, etc.
- (iii) SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:
 - --- Space applications
 - --- Telecommunication equipment [trunk lines]
 - --- Nuclear power control equipment
 - --- Medical and other life support equipment (e.g., scuba).
- · If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- · This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- · Contact and consult with a SHARP representative if there are any questions about the contents of this publication.