


BM25 Series

Small Hybrid Board to FPC Connectors up to 9 Amps



Connection Examples



Battery Connection

USB Connection

Features

- 1. Low-profile design with the capability of high current power supply, suitable to connecting battery for a mobile device
 - •Rated current: 9 Amps for power contact, 1 Amp for signal contact
 - Stacking height: 0.7 mm, Depth: 2.6 mm
- 2. Minimized contact resistance to facilitate power saving
- 3. Multipoint contact with clipping contacts for high reliability
- 4. Original metal guide structure for high robustness
- 5. Wide self alignment range to realize smooth mating operation
- 6. Integrally molded header and receptacle to prevent solder wicking
- 7. RoHS compliant, Halogen-free* product * This product satisfies

Specifications

* This product satisfies halogen free requirements defined
as 900 ppm maximum chlorine, 900 ppm maximum bromine,
and 1500 ppm maximum total of chlorine and bromine.

Component	Material	Finish
Housing	LCP*1	UL94V-0, Black
Contact	Copper Alloy	Gold plated over Nickel under plating
Metal Fitting	Copper Alloy	Gold plated over Nickel under plating


Rated Current	Power Contact: 9 Amps, Signal Contact: 1 Amp
Rated Voltage	30 V AC/DC
Operating Temperature Range	-40 °C to +85 °C*2
Contact Resistance	Power Contact: $5~\text{m}\Omega$, Signal Contact: $30~\text{m}\Omega$ (20 mV AC, 1 kHz, 1 mA)
Withstanding Voltage	150V AC, for one minute
Insulation Resistance	1000 MΩ or above (100 V DC)
Durability	10 cycles


4 pos. (2 pos. for power + 4 pos. for signal)


◆ Power up to 9 Amps

30 °C or less temperature rising while 9 Amps power being applied.

* Apply 1 Amp to each signal contact.







Receptacle

Specifications herein are subject to change without notice. Contact Hirose for latest specifications, drawings, or availabilities.

Variations

^{*}Include the temperature rising by current flow.