SHARP


GM1BC55250AC

Under development
New product
Chin LED

High-Luminosity Blue Chip LED

Features


- (1) High-luminosity Blue chip LED
- (2) Wide viewing angle ($2\theta \ 1/2$): 120°
- (3) Surface-mount, leadless chip LED device
- (4) Outline dimensions: $1.6 \times 0.8 \times 0.55$ t mm
- (5) Taped product (5 000 pcs/reel)



 $(T_{\rm T} - 10_{\rm m} \wedge T_{\rm c} - 25^{\circ} C)$

Applications

- (1) LCD backlight for cellular phone
- (2) LCD backlight for various portable equipment
- (3) Backlight for membrane switch



*1 Duty ratio=1/10, Pulse width=0.1ms

*2 For 3s or less at the temperature of hand soldering.

Electro-optical Characteristics

(IF=10mA,1a=25 C)										
Lens type	Model No.	Forward voltage $V_F(V)$		Peak emission wavelength λp (nm)	Dominant wavelength λd(nm)	Luminous intensity Iv(mcd)	Spectrum radiation bandwidth $\Delta\lambda(nm)$	Reverse Ir(µA)	Reverse current (μA) V _R	
		TYP	MAX	TYP	TYP	TYP	TYP	MAX	(V)	
Colorless transparency	GM1BC55250AC	3.2	3.9	470	472	35	26	100	4	

(Notice)

•In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc. Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.

•Specifications are subject to change without notice for improvement.

(Internet)

•Data for Sharp's optoelectronic is provided on internet. (Address http://sharp-world.com/ecg/)

As of July 2002