



## General ordering data

Order No. Part designation Version

EAN Qty.

## System parameters

Fitted to PCB Outgoing elbow Pitch Pitch in inch No. of poles Solder pin length Can be coded No. of rows No. of solder pins per pole Dia. of fitting hole Fitting hole tolerance L1 in mm L1 in inch Insulation resistance 1633800000 SLD 3.5/48/90G3.2SN OR PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 48, 90°, Box 4008190258252 10 pc(s).

Soldered connection
90°
3.5 mm
0.138 inch
48
3.2 mm
Yes
2
1
1.3 mm
+ 0.1 mm
80.5 mm
3.169 inch
1 ΜΩ



Custom novemetors	
System parameters	
Electric shock protection to DIN VDE 0470	IP 10
Electric shock protection to DIN VDE 0470	Safe from back-of-hand touch
Material data	
Insulating material	PBT
Colour	orange
colour chart	Similar to RAL 2000
Insulating material group	Illa
Flammability class UL 94	V-0
CTI	>= 200
Contact base material	CuSn
Contact surface	tinned
Constant operating temp., min.	-25 °C
Constant operating temp., max.	100
Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C
Max. relative humidity during storage	80 %
DIN IEC rating data	
Rated current, min. No. pins (Tu=20°C)	10.5 A
Rated current, max. No. pins (Tu=20°C)	8 A
Rated current, min. No. pins(Tu=40°C)	9 A
Rated current, max. No. pins (Tu=40°C)	7 A
Rated voltage for overvoltage class/pollution	160 V
severity III/3	
Rated impulse withstand voltage for overvoltage	2.5 kV
class/pollution severity III/3	
Rated voltage for overvoltage class/pollution	160 V
severity III/2	
Rated impulse withstand voltage for overvoltage	2.5 kV
class/pollution severity III/2	
Rated voltage for overvoltage class/pollution	200 V
severity II/2	0.511/
Rated impulse withstand voltage for overvoltage	2.5 kV
class/pollution severity II/2	
Short-time withstand current resistance	3 x 1s with 80 A
CSA rating data	
Rated voltage (Use group D)	300 V
Rated current (Use group D)	8 A
Rated current (Ose group D)	
UL 1059 rating data	
Rated voltage (Use group D)	300 V
Rated current (Use group D)	8 A
(	

Approvals

Approvals institutes





## Approvals

Downloads					
CAD Library (P-CAD Format - Standard)	SLD.LIB				
ETIM 2.0	NK				
ETIM 3.0	EC001284				
eClass 4.1	27-26-07-01				
eClass 5.0	27-26-07-01				
eClass 5.1	27-26-07-04				

## Similar products

1633580000	SLD 3.5/4/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 4, 90°, Box
1633590000	SLD 3.5/6/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 6, 90°, Box
1633600000	SLD 3.5/8/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 8, 90°, Box
1633610000	SLD 3.5/10/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 10, 90°, Box
1633620000	SLD 3.5/12/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 12, 90°, Box
1633630000	SLD 3.5/14/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 14, 90°, Box
1633640000	SLD 3.5/16/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 16, 90°, Box
1633650000	SLD 3.5/18/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 18, 90°, Box
1633660000	SLD 3.5/20/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 20, 90°, Box
1633670000	SLD 3.5/22/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 22, 90°, Box
1633680000	SLD 3.5/24/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 24, 90°, Box
1633690000	SLD 3.5/26/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 26, 90°, Box
1633700000	SLD 3.5/28/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 28, 90°, Box
1633710000	SLD 3.5/30/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 30, 90°, Box
1633720000	SLD 3.5/32/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 32, 90°, Box
1633730000	SLD 3.5/34/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 34, 90°, Box
1633740000	SLD 3.5/36/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 36, 90°, Box



Product catalogue | PCB connection systems | PCB plug-in connectors | Pitch 3.50 mm (0.138 inch) | Plug connectors, solder connection, pitch 3.5 | SLD 3.5/90 | SLD 3.5/90G

1633750000	SLD 3.5/38/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 38, 90°, Box
1633760000	SLD 3.5/40/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 40, 90°, Box
1633770000	SLD 3.5/42/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 42, 90°, Box
1633780000	SLD 3.5/44/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 44, 90°, Box
1633790000	SLD 3.5/46/90G3.2SN OR	PCB plug-in connector, Male connectors, Soldered connection, Pitch: 3.50 mm, No. of poles: 46, 90°, Box

