# WWW.PHIHONG.COM



# 40W Constant Voltage LED Driver PDA041B Waterproof LED Driver Non-Dimming





### **Features**

- Class 2 per UL1310
- OVP, OCP, Over-Load and Short-Circuit Protection
- >0.9 Power Factor Correction
- 5 Year Warranty

- IP67 Rating waterproof
- THD < 20%
- UL 8750 Compliant
- Brownout/Brownout Recovery

# Applications

- Down lights
- Area Lights

• Architectural lighting

### **Safety Approvals**

• cUL/UL

# **Mechanical Characteristics**

Length: 95mm (3.74in)Width: 71mm (2.79in)

Height: 32mm (1.26in)Weight: 340g (11.99oz)

# **Output Specifications**

Model	Output Current Range			DC Output	Output
	Min.	Typ.	Max.	Voltage	Power
PDA041B-24VB	0A	-	1.67A	24V	40W
PDA041B-48VB	0A	-	0.83A	48V	40W

Phihong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.

# PDA041B Characteristics

# WWW.PHIHONG.COM

### **INPUT:**

**AC Input Voltage Rating** 

120VAC to 277VAC

**AC Input Frequency** 

47~63Hz

**Maximum Input Current** 

 $\leq 0.8A$ 

**Leakage Current** 

0.5mA maximum

**Power Factor** 

 $\geq 0.9$ 

**THD** 

Less than 20%

**OUTPUT:** 

**Output Voltage Ripple** 

≤8% (p-p)

**Efficiency** 

87% at 277VAC

**Environmental:** 

**Temperature** 

Operation case\* -40 to +80°C
Non-operation -40 to +82°C
Operating Humidity 20 to 95%

Dimension Diagram unit: mm

### **EMC**

FCC 47 Part 18 Class B

### **Immunity**

IEC61000-4-2

IEC61000-4-4

IEC61000-4-5

IEC61000-4-11

### Dielectric Withstand (Hi-pot) Test

Primary to secondary: 3000VAC for 1 minute, 10mA

### **Insulation Resistance**

Primary to secondary: >10M Ohm 500VDC, 1 Minute

### **Features**

### **Short-Circuit Protection**

The PSU will withstand a short circuit across the outputs without damage

### **Input Over Current Protection**

The input power line will be fused with a 2A/300V fuse

### **Output Over-voltage Protection**

Auto shutdown

### **Input / Output Connections**


Position	Terminal Color	Specification
Input	Black	AWG16 Solid Wire
•	White Red	AWG16 Solid Wire AWG18 Solid Wire
Output	Black	AWG18 Solid Wire


### Warranty


5 Years


# WHITE BLACK (N) BLACK (N) STREE (N)

<sup>\*</sup>Output derates from 50°C to 70°C Ta









### Temperature Rating

