Note: This datasheet may be out of date

Please download the latest datasheet of SFECF10M7DA0001-R0 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=SFECF10M7DA0001-R0

# SFECF10M7DA0001-R0










### Appearance & Shape







#### **Features**

SFECF10M7 series for FM receivers are small, high-performance and super thin (1.4mm max.) filters. The piezoelectric element is sandwiched by the ceramics substrate. They have 1.4mm max. thickness and a small mounting area (3.45x3.1mm). SFECF series and CDSCB series (MHz Discriminator) enable customers to make VICS/RKE/TPMS set very thin and small.

#### Features

- 1. The filters are mountable by automatic placers.
- 2. They are slim, at only 1.4mm max. thickness, and have a small mounting area (3.45x3.1mm) enabling flexible PCB design.
- 3. Various bandwidths are available. Select a suitable type in accordance with the desired selectivity.
- 4. Operating Temperature Range: -20 to +80 (degrees C), Storage Temperature Range: -40 to +85 (degrees C)



### **Applications**

Other Usage

Communication Equipment/Audio Visual Equipment



## Packaging Information

Packaging	Specifications	Minimum Order Quantity
R0	180mm Embossed Tape	2000

1 of 3

#### Attentior

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



Note: This datasheet may be out of date.

Please download the latest datasheet of SFECF10M7DA0001-R0 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=SFECF10M7DA0001-R0

# SFECF10M7DA0001-R0



## **Specifications**

	,	
Operating Temperature Range	-20°C to 80°C	
Shape	SMD	
Elements	2	
Center Frequency	10.700MHz	
Center Frequency Tolerance	±30kHz	
Nominal Center Value	No	
3dB Bandwidth	420kHzmin.	
Stop Bandwidth	950kHz	
Area of Stop Bandwidth	[within 20dB]	
Spurious Attenuation	35dB[within 9MHz to fo]	
Insertion Loss	3.0dB±2.0dB(at minimum loss point)	
Ripple	3.0dBmax.(at minimum loss point)	
Input/Output Impedance	330Ω	
Mass	65mg	

2 of 3

#### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.




Please download the latest datasheet of SFECF10M7DA0001-R0 from the official website of Murata Manufacturing Co., Ltd.


http://www.murata.com/en-us/products/productdetail?partno=SFECF10M7DA0001-R0

Note: This datasheet may be out of date.

# SFECF10M7DA0001-R0








#### Frequency Characteristics

Spurious Response



Measurement Circuit

3 of 3

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

