

Printed-circuit board connector - BCVP-508WF- 3 GN - 5451624

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)

Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 3, Pitch: 5.08 mm, Connection method: Screw connection, Color: pastel green, Contact surface: Tin



The figure shows a 5-pos. version of the product in gray



Key commercial data

Packing unit	1 pc
Minimum order quantity	100 pc
Custom tariff number	85366990
Country of origin	Germany

Technical data

Dimensions

Pitch	5.08 mm
Dimension a	10.16 mm

General

Range of articles	BCVP-WF
Insulating material group	
Rated surge voltage (III/3)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (II/2)	4 kV
Rated voltage (III/3)	250 V
Rated voltage (III/2)	320 V
Rated voltage (II/2)	630 V
Nominal current I _N	12 A
Nominal cross section	2.5 mm ²
Maximum load current	12 A (with 2.5 mm ² conductor cross section)



Printed-circuit board connector - BCVP-508WF- 3 GN - 5451624

Technical data

General

Insulating material	PA	
Inflammability class according to UL 94	V0	
Number of positions	3	
Connection data		
Conductor cross section solid min.	0.2 mm ²	
Conductor cross section solid max.	2.5 mm ²	
Conductor cross section stranded min.	0.2 mm ²	
Conductor cross section stranded max.	2.5 mm ²	
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²	
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²	
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²	
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²	
Conductor cross section AWG/kcmil min.	24	
Conductor cross section AWG/kcmil max	12	
2 conductors with same cross section, solid min.	0.2 mm ²	
2 conductors with same cross section, solid max.	1 mm ²	
2 conductors with same cross section, stranded min.	0.2 mm ²	
2 conductors with same cross section, stranded max.	1.5 mm ²	
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm²	
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1 mm ²	
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm²	

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27261101
eCl@ss 7.0	27440401
eCl@ss 8.0	27440401

ETIM

ETIM 3.0	EC001121
----------	----------



Printed-circuit board connector - BCVP-508WF- 3 GN - 5451624

Classifications


ETIM

ETIM 4.0	EC002638
ETIM 5.0	EC002638

UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	39121432
UNSPSC 12.01	39121409
UNSPSC 13.2	39121432

Drawings



Phoenix Contact 2014 $\ensuremath{\mathbb{C}}$ - all rights reserved http://www.phoenixcontact.com