

BC214LB

PNP General Purpose Amplifier

- This device is deisgned for use as general purpose amplifiers and switches requiring collector currents to 300mA.
- Sourced from process 68.



1. Emitter 2. Collector 3. Base

Absolute Maximum Ratings* T_a=25°C unless otherwise noted

Symbol	Parameter	Value	Units
V _{CEO}	Collector-Emitter Voltage	-30	V
V _{CBO}	Collector-Base Voltage	-45	V
V _{EBO}	Emitter-Base Voltage	-5.0	V
I _C	Collector Current (DC) Continuous	-500	mA
T _J , T _{STG}	Operating and Storage Junction Temperature Range	- 55 ~ 150	°C

^{*} These ratings are limiting values above which the serviceability of any semiconductor device may be impaired.

- These ratings are based on a maximum junction temperature of 150 degrees C.
 These are steady state limits. The factory should be consulted on applications involving pulsed or low duty cycle operations

Electrical Characteristics T_a=25°C unless otherwise noted


Symbol	Parameter	Test Condition	Min.	Max.	Units
Off Characte	eristics	•	•		•
V _{(BR)CEO}	Collector-Emitter Voltage	I _C = -2mA, I _B = 0	-30		V
V _{(BR)CBO}	Collector-Base Voltage	$I_{C} = -10\mu A, I_{E} = 0$	-45		V
V _{(BR)EBO}	Emitter-Base Voltage	$I_E = -10\mu A, I_C = 0$	-5.0		V
I _{CBO}	Collector Cut-off Current	V _{CB} = -30V, I _E = 0		-15	nA
I _{EBO}	Emitter Cut-off Current	V _{EB} = -4V, I _C = 0		-15	nA
On Characte	eristics *	•	•		•
h _{FE}	DC Current Gain	$V_{CE} = -5V, I_{C} = -2mA$	140	400	
V _{CE} (sat)	Collector-Emitter Saturation Voltage	I _C = -10mA, I _B = -0.5mA I _C = -100mA, I _B = -5mA		-0.25 -0.6	V
V _{BE} (sat)	Base-Emitter Saturation Voltage	I _C = -100mA, I _B = -5mA		-1.1	V
V _{BE} (on)	Base-Emitter On Voltage	$V_{CE} = -5V, I_{C} = -2mA$	-0.6	-0.72	V
Small Signa	I Characteristics			•	•
f _T	Current gain Bandwidth Product	V _{CE} = -5V, I _C = -10mA f = 100MHz	200		MHz
NF	Noise Figure	V_{CE} = -5V, I_{C} = -200μA R_{G} = 2k Ω , f = 15.7KHz		2.0	dB
h _{fe}	Small Signal Current Gain	$I_{C} = -2mA, V_{CE} = -5V$ f = 1KHz	200	400	
C _{OB}	Output Capacitance	V _{CB} = -10V, f = 1MHz		10	pF


* Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2.0%


Thermal Characteristics T _A =25°C unless otherwise noted			
Symbol	Parameter	Max.	Units
P _D	Total Device Dissipation Derate above 25°C	625 5.0	mW mW/°C
$R_{\theta JC}$	Thermal Resistance, Junction to Case	83.3	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	200	°C/W

Package Dimensions

TO-92







TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACEx™	FACT Quiet Series™	LittleFET™	Power247™	SuperSOT™-6
ActiveArray™	FAST [®]	MICROCOUPLER™	PowerTrench [®]	SuperSOT™-8
Bottomless™	FASTr™	MicroFET™	QFET [®]	SyncFET™
CoolFET™	FRFET™	MicroPak™	QS™	TinyLogic [®]
$CROSSVOLT^{\text{TM}}$	GlobalOptoisolator™	MICROWIRE™	QT Optoelectronics™	TINYOPTO™
DOME™	GTO™	MSX™	Quiet Series™	TruTranslation™
EcoSPARK™	HiSeC™	MSXPro™	RapidConfigure™	UHC™
E ² CMOS™	I ² C™	OCX™	RapidConnect™	UltraFET [®]
EnSigna™	ImpliedDisconnect™	OCXPro™	SILENT SWITCHER®	VCX™
FACT™	ISOPLANAR™	OPTOLOGIC®	SMART START™	
Across the board.	Around the world.™	OPTOPLANAR™	SPM™	
The Power Franci	hise™	PACMAN™	Stealth™	
Programmable Ad	ctive Droop™	POP™	SuperSOT™-3	

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.
- 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.

©2003 Fairchild Semiconductor Corporation Rev. II