

# 「 SERIES **CURRENT CONTROL RELAY**

UL listed CSA recognized

- **Automatic or Manual Control**
- Start-up Inhibit
- Adjustable Hysteresis
- Multiple Voltages
- **LED Relay Status Indicator**



#### 1. AC Current Control Without Latching:

The output relay is energized when the current (peak current on AC) overshoots the level selected on the potentiometer. It de-energizes when the current falls below the normal current by 5 to 50% or when input power breaks. The hysteresis is controlled by a top mounted potentiometer and its selection does not change the chosen current level.

2. AC Current Control With Latching:

The output relay is energized when the current reaches the selected value and stays latched. The contact between terminal B1 and B2 (or 11 and 9) should be opened or input power to the device interrupted to reset. In this case, it is preferable to reduce the hysteresis 5%.

## SPECIFICATIONS:

-	±15%, 50/60 Hz				
Power consumption		3 VA maximum			
CONTROL RANGE			PERMITTED	OVERLOAD	
DC	AC	INPUT		LESS THAN	
CURRENT	CURRENT	RESISTANCE	PERMANENTLY	1 sec Peak	
5 to 100 mA	3.5 to 70.7 mA	1 ohm	1.5 V	5 A	
0.05 to 1 A	0.035 to 0.707 A	0.1 ohm	5 A	17 A	
0.5 to 10 A	0.35 to 7.07 A	0.01 ohm	15 A	55 A	
Hysteresis selection 5 to 50% of input current					
Repeat accuracy ±2% at a constant ambient					
Response time 100 ms On Make					
		200 ms	s On Break		
Output Relay		SPDT Relay			
Contact mat	erial				
			10 A AC resistive 1 A DC inductive		
Maximum switching voltage 250 VAC or DC					

Input ...... 24 VDC, 24, 48, 110, 220 VAC

Relay maximum power rating .... 2500 VA 30W

Mechanical life of relay ..... 30 x 10<sup>4</sup> operations

Electrical life of relay ...... 2 x 10<sup>5</sup> at 2500 VA resistive load Operating temperature ...... +14°F to + 140°F -10°C to +60°C


Weight . . . . . . . . . . . . . . . . 7 oz. (200g)

Option: 24 VDC power - the voltage and the measured current must be


from separate sources.

Note: It is recommended that the unit be adequately fused.






# WIRING DIAGRAM:



Note: Upon energization of the current control IR.T Series Relay, the time delay, which is adjustable from .1 to 10 seconds, inhibits the output relay during start-up periods. The delay time is adjustable via a potentiometer located on the side of the case. Applies to both versions, with and without latching.



Products and specifications subject to change without notice.






# IAR.T SERIES CURRENT CONTROL RELAY

UL listed CSA recognized

- Automatic or Manual Control
- Start-up Inhibit
- Adjustable Hysteresis
- Multiple Voltages
- 5 to 100 Amp RMS



1. AC Current Control Without Latching:

The output relay is energized when the AC current overshoots the level selected on the potentiometer. It de-energizes when the current falls below the selected current by 5 to 50% or when input power breaks. The hysteresis is controlled by a top mounted potentiometer and its selection does not change the chosen current level.

2. AC Current Control With Latching:

The output relay is energized when the current reaches the selected value and stays latched. The contact between terminal B1 and B2 (or 11 and 9) should be opened or input power to the device interrupted to reset. In this case, it is preferable to reduce the hysteresis 5%.

# **SPECIFICATIONS:**


±15%, 50/60 Hz Power consumption . . . . . . . . . 3 VA maximum **Hysteresis selection** . . . . . . . . . 5 to 50% of input current Repeat accuracy ..... ±2% at a constant ambient ±5% with temperature variation **VDE 0435** Response time ...... 100 ms On Make 200 ms On Break Output Relay Contact material . . . . . . . . AgCdO 1 A DC inductive Maximum switching voltage ..... 250 VAC 30 VDC 30 W Relay maximum power rating ..... 2500 VA Mechanical life of relay ..... 30 x 10<sup>4</sup> operations Electrical life of relay ...... 2 x 10<sup>5</sup> at 2500 VA resistive load

Input ..... 24 VDC, 24, 48, 110, 220 VAC

# TRANSFORMER: (Part Number 74 525 305)

Operating temperature ......+14°F to +140°F


Weight . . . . . . . . . . . . . . . . . 7 oz. (200g)









-10°C to +60°C



## **WIRING DIAGRAM:**



**Note:** Upon energization of the current control IAR.T Series Relay, the time delay, which is adjustable from .1 to 10 seconds, inhibits the output relay during start-up periods. The delay time is adjustable via a potentiometer located on the side of the case. For additional current transformer see "Accessories" section: L595 Series. Page 2/99



Products and specifications subject to change without notice.

