
## **Spec Sheet**

Metal Core Wire-wound Chip Power Inductors (MCOIL(TM) MA series H (High Spec.) type)

# MAKK2016H1R0M



#### Features

- Item Summary
  - 1.0 μH(±20%), 0806
- Lifecycle Stage Mass Production
- Standard packaging quantity (minimum)

Taping 3000pcs

#### Products characteristics table


CaseSize (EIA/JIS)	0806/2016
Inductance	1.0 µH(±20%)
Inductance Measuring Frequency	2MHz
Rated Current -Saturation Current	2700mA
Rated Current -Temperature Rise Current	2300mA
DC Resistance (max)	0.07Ω
DC Resistance (typ)	0.06Ω
Temperature Range	-40 to +125 ℃
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

#### External Dimensions

L	2mm ±0.1
W	1.6mm ±0.1
Т	1mm max
е	0.5mm ±0.3

### **Recommended Land Patterns**





Metal Core wire	-wound Chip Fox	rer maactors (inc	OILM, MA Series.
Type	A	В	С
2016	0.7	0.8	1.8
2520	0.8	1.2	2.0

2015.10.14