



2N5961



NPN General Purpose Amplifier

This device is designed for use as low noise, high gain, general purpose amplifiers requiring collector currents to 50 mA. Sourced from Process 07. See 2N5088 for characteristics.

Absolute Maximum Ratings* TA = 25°C unless otherwise noted

Symbol	Parameter	Val60ue	Units
V_{CEO}	Collector-Emitter Voltage	60	V
V _{CBO}	Collector-Base Voltage	60	V
V_{EBO}	Emitter-Base Voltage 8.0		V
I _C	Collector Current - Continuous 100		mA
T _J , T _{stg}	Operating and Storage Junction Temperature Range	-55 to +150	°C

*These ratings are limiting values above which the serviceability of any semiconductor device may be impaired.

NOTES:

1) These ratings are based on a maximum junction temperature of 150 degrees C.
2) These are steady state limits. The factory should be consulted on applications involving pulsed or low duty cycle operations.

Thermal Characteristics

Thermal Characteristics TA = 25°C unless otherwise noted				
Symbol	Characteristic	Max	Units	
		2N5961		
P _D	Total Device Dissipation Derate above 25°C	625 5.0	mW mW/°C	
$R_{\theta JC}$	Thermal Resistance, Junction to Case	83.3	°C/W	
R _{θJA}	Thermal Resistance, Junction to Ambient	200	°C/W	

© 1997 Fairchild Semiconductor Corporation

NPN General Purpose Amplifier (continued)

Symbol	Parameter	Test Conditions	Min	Мах	Units
OFF CHA	RACTERISTICS				
V _{(BR)CEO}	Collector-Emitter Breakdown Voltage*	$I_{\rm C} = 5.0 \text{ mA}, I_{\rm B} = 0$	60		V
V _{(BR)CBO}	Collector-Base Breakdown Voltage	$I_{\rm C} = 10 \ \mu {\rm A}, \ I_{\rm E} = 0$	60		V
V _{(BR)EBO}	Emitter-Base Breakdown Voltage	$I_{\rm E} = 10 \mu {\rm A}, I_{\rm C} = 0$	8.0		V
I _{сво}	Collector Cutoff Current	$V_{CB} = 45 V, I_E = 0$ $V_{CB} = 45 V, I_E = 0, T_A = 65 ^{\circ}C$		2.0 50	nA nA
EBO	Emitter Cutoff Current	$V_{EB} = 5.0 \text{ V}, I_{C} = 0$		1.0	nA
/ _{CE(sat)}	Collector-Emitter Saturation Voltage	$V_{CE} = 5.0 \text{ V}, I_C = 1.0 \text{ mA}$ $V_{CE} = 5.0 \text{ V}, I_C = 10 \text{ mA}$ $I_C = 10 \text{ mA}, I_B = 0.5 \text{ mA}$	135 150	700	V
		$V_{CE} = 5.0 \text{ V}, I_{C} = 100 \mu\text{A}$ $V_{CE} = 5.0 V, I_{C} = 1.0 \text{m}\text{A}$	120 135		
,	Collector Emitter Seturation Voltage		150		V
VCE(sat)		$I_{\rm C} = 10$ mA, $I_{\rm B} = 0.5$ mA $I_{\rm C} = 10$ mA, $I_{\rm B} = 1.0$ mA		0.2	V
V _{BE(on)}	Base-Emitter On Voltage	$V_{CE} = 5.0 \text{ V}, I_{C} = 1.0 \text{ mA}$	0.5	0.7	V
SMALL S C _{cb} C _{eb} n _{fe}	IGNAL CHARACTERISTICS Collector-Base Capacitance Emitter-Base Capacitance Small-Signal Current Gain	$V_{CB} = 5.0 \text{ V}, \text{ f} = 1.0 \text{ MHz}$ $V_{EB} = 0.5 \text{ V}, \text{ f} = 1.0 \text{ MHz}$ $I_{C} = 10 \text{ mA}, V_{CE} = 5.0 \text{ V},$ $f = 1.0 \text{ kHz}$ $I_{C} = 10 \text{ mA}, V_{CE} = 5.0 \text{ V},$	150	4.0 6.0 1000	pF pF
NF	Noise Figure	$\begin{array}{l} f = 100 \text{ MHz} \\ V_{CE} = 5.0 \text{ V}, I_C = 10 \ \mu\text{A}, \\ R_S = 10 \ k\Omega, \ f = 1.0 \ \text{kHz}, \\ B_W = 400 \ \text{Hz} \\ V_{CE} = 5.0 \ \text{V}, I_C = 10 \ \mu\text{A}, \\ R_S = 10 \ k\Omega, \ f = 10 \ \text{Hz} - 10 \ \text{kHz} \\ B_W = 15.7 \ \text{kHz} \\ V_{CE} = 5.0 \ \text{V}, I_C = 100 \ \mu\text{A}, \\ R_S = 1.0 \ k\Omega, \ f = 1.0 \ \text{kHz} \\ B_W = 400 \ \text{Hz} \end{array}$	1.0	3.0 3.0 6.0	dB dB dB

2N5961



©2001 Fairchild Semiconductor Corporation

March 2001, Rev. B1





July 1999, Rev. A



TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACEx™ Bottomless™ CoolFET™ CROSSVOLT™ DOME™ E²CMOS[™] EnSigna™ FACT™ FACT Quiet Series[™] FAST[®]

FASTr™ GlobalOptoisolator™ GTO™ HiSeC™ **ISOPLANAR™** MICROWIRE™ OPTOLOGIC™ **OPTOPLANAR™** PACMAN™ POP™

PowerTrench[®] QFET™ QS™ QT Optoelectronics[™] Quiet Series[™] SILENT SWITCHER® SMART START™ SuperSOT[™]-3 SuperSOT[™]-6 SuperSOT[™]-8

SyncFET™ TinyLogic™ UHC™ VCX™

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.
	1	Rev G