International IOR Rectifier

50WQ06FN

SCHOTTKY RECTIFIER

5.5 Amp

 $I_{F(AV)} = 5.5Amp$ $V_R = 60V$


Major Ratings and Characteristics

Characteristics	Values	Units
I _{F(AV)} Rectangular waveform	5.5	А
V _{RRM}	60	V
I _{FSM} @tp=5 µs sine	320	Α
V _F @5 Apk, T _J = 125°C	0.54	V
T _J range	-40 to 150	°C

Description/ Features

The 50WQ06FN surface mount Schottky rectifier has been designed for applications requiring low forward drop and small foot prints on PC board. Typical applications are in disk drives, switching power supplies, converters, free-wheeling diodes, battery charging, and reverse battery protection.

- Popular D-PAK outline
- Small foot print, surface moutable
- Low forward voltage drop
- · High frequency operation
- Guard ring for enhanced ruggedness and long term reliability



Document Number: 93360 www.vishay.com

Voltage Ratings

Part number	50WQ06FN			
V _R Max. DC Reverse Voltage (V)	60			
V _{RWM} Max. Working Peak Reverse Voltage (V)	60			

Absolute Maximum Ratings

	Parameters	50WQ	Units	Conditions		
I _{F(AV)}	Max. Average Forward Current	5.5	Α	50% duty cycle @ T _C = 132°C, r	ectangular wave form	
	* See Fig. 5					
I _{FSM}	Max. Peak One Cycle Non-Repetitive	320	Α	5μs Sine or 3μs Rect. pulse	Following any rated load condition and with rated V _{RRM} applied	
	Surge Current *See Fig. 7	105		10ms Sine or 6ms Rect. pulse		
E _{AS}	Non-Repetitive Avalanche Energy	7	mJ	$T_J = 25 ^{\circ}\text{C}, I_{AS} = 1.2 \text{Amps}, L = 1.2 ^{\circ}$	10 mH	
I _{AR}	Repetitive Avalanche Current			Current decaying linearly to zero in 1 µsec		
				Frequency limited by T_J max. V_J	_A =1.5 x V _R typical	

Electrical Specifications

	Parameters		50WQ	Units		Conditions		
V _{FM}	Max. Forward Voltage D	rop	0.57	V	@	5A	T = 25 °C	
	* See Fig. 1	(1)	0.74	V	@	10A	$T_J = 25 ^{\circ}\text{C}$	
			0.54	V	@	5A	T ₁ = 125 °C	
			0.68	V	@	10A	1 _J = 125 C	
I _{RM}	Max. Reverse Leakage	Current	3	mA	T _J =	= 25 °C	\/ = rated \/	
	* See Fig. 2	(1)	35	mA	T _J =	= 125 °C	$V_R = \text{rated } V_R$	
V _{F(TO}	Threshold Voltage		0.35	V	$T_J = T_J \text{ max.}$			
r _t	Forward Slope Resistan	nce	25.5	mΩ				
C _T	Typical Junction Capacit	tance	360	pF	$V_R = 5V_{DC}$, (test signal range 100Khz to 1Mhz) 25 °C			
L _S	Typical Series Inductano	ce	5.0	nH	Measured lead to lead 5mm from package body			
dv/dt	Max. Voltage Rate of Ch	nange	10000	V/µs	(Rated V _R)			

⁽¹⁾ Pulse Width < 300µs, Duty Cycle < 2%

Thermal-Mechanical Specifications

	Parameters	50WQ	Units	Conditions
T _J	Max. Junction Temperature Range(*)	-40 to 150	°C	
T _{stg}	Max. Storage Temperature Range	-40 to 150	°C	
R _{thJC}	Max. Thermal Resistance Junction	3.0	°C/W	DC operation *See Fig. 4
	to Case			
wt	Approximate Weight	0.3 (0.01)	g (oz.)	
	Case Style	D-PAK		Similar to TO-252AA
	Device Marking	50WQ06FN		

 $[\]frac{\text{(*)}}{\text{dTj}} < \frac{1}{\text{Rth(j-a)}} \quad \text{thermal runaway condition for a diode on its own heatsink}$

Bulletin PD-20525 rev. G 05/06




Fig. 1 - Maximum Forward Voltage Drop Characteristics

Fig. 3-Typical Junction Capacitance Vs. Reverse Voltage




Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics




Fig. 5 - Maximum Allowable Case Temperature Vs. Average Forward Current




Fig. 6 - Forward Power Loss Characteristics






Fig. 7 - Maximum Non-Repetitive Surge Current

(2) Formula used: $T_C = T_J - (Pd + Pd_{REV})xR_{thJC}$; $Pd = Forward PowerLoss = I_{F(AV)}xV_{FM} @ (I_{F(AV)}/D)$ (see Fig. 6); $Pd_{REV} = Inverse PowerLoss = V_{R1}xI_R(1-D); I_R @ V_{R1} = 80\%$ rated V_R

Outline Table




Part Marking Information




Document Number: 93360 www.vishay.com

Tape & Reel Information



Ordering Information Table





- Current Rating (5.5A)
- Package Identifier

W = D-Pak

- Schottky "Q" Series
- Voltage Rating (06 = 60V)
- 5 FN = TO-252AA
- none = Tube (50 pieces)
 - TR = Tape & Reel
 - TRL = Tape & Reel (Left Oriented)
 - TRR = Tape & Reel (Right Oriented)
- o none = Standard Production
 - PbF = Lead-Free

Data and specifications subject to change without notice. This product has been designed and qualified for AEC Q101 Level.

Qualification Standards can be found on IR's Web site.



IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7309



Vishay

Notice

The products described herein were acquired by Vishay Intertechnology, Inc., as part of its acquisition of International Rectifier's Power Control Systems (PCS) business, which closed in April 2007. Specifications of the products displayed herein are pending review by Vishay and are subject to the terms and conditions shown below.

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products. Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

International Rectifier®, IR®, the IR logo, HEXFET®, HEXSense®, HEXDIP®, DOL®, INTERO®, and POWIRTRAIN® are registered trademarks of International Rectifier Corporation in the U.S. and other countries. All other product names noted herein may be trademarks of their respective owners.

Document Number: 99901 www.vishay.com Revision: 12-Mar-07