
Spec Sheet

Metal Core Wire-wound Chip Power Inductors (MCOIL(TM) MA series H (High Spec.) type)

MAKK2016HR68M



Features

- Item Summary
 0.68 μH(±20%), 0806
- Lifecycle Stage
 - Mass Production
- Standard packaging quantity (minimum)
 Taping 3000pcs

Products characteristics table


CaseSize (EIA/JIS)	0806/2016
Inductance	0.68 μH(±20%)
Inductance Measuring Frequency	2MHz
Rated Current -Saturation Current	3200mA
Rated Current -Temperature Rise Current	2700mA
DC Resistance (max)	0.05Ω
DC Resistance (typ)	0.041Ω
Temperature Range	-40 to +125 ℃
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

External Dimensions

L	2mm ±0.1
W	1.6mm ±0.1
Т	1mm max
е	0.5mm ±0.3

Recommended Land Patterns





Metal Core Wire	-wound Chip Pov	er Inductors (MC	:UlLn⊌, MA series	,	
Type	A	В	С		
2016	0.7	0.8	1.8		
2520	0.8	1.2	2.0		
unit* mm					

2015.10.14