EXQ60D Series

Dual positive output



DC/DC CONVERTERS 60 W High Efficiency DC/DC Converters

- Two positive outputs
- Output voltage tracking
- High efficiency
- Approved to EN60950 (TÜV Rheinland), UL/cUL1950
- Operating baseplate temperature of -40 °C to +100 °C
- Up to 100% load imbalance
- Trim function
- No minimum load
- Complies with ETS 300 019-1-3/2-3
- Fully compliant with ETS 300 386-1
- Available RoHS compliant

The EXQ60 is a new high efficiency, open frame, isolated 60 Watt converter series in an industry standard quarter-brick footprint. The EXQ60 delivers very high output current at low voltages, and excellent useable power density for today's high end applications. The first two models in the series feature an input voltage range of 33 V to 75 V and are available in output voltages of 5/3.3 V and 3.3/2.5 V. The output voltage on each model is adjustable from 90% to 110% of the nominal value. Typical efficiencies for the models are 91% for the 5/3.3 V and 90% for the 3.3/2.5 V version. The EXQ60 series also has a remote on/off capability. Overcurrent and overvoltage protection features are included as standard. With full international safety approval including EN60950, (TÜV Rheinland) and UL/cUL1950, the EXQ60 reduces compliance costs and time to market.



2 YEAR WARRANT

SPECIFICATIONS

All specifications are typical at nominal inpu	t, full load at 25 °C unless otherwise stated
--	---

OUTPUT SPECIFICATIONS

Voltage adjustability	Both outputs	±10%
Setpoint accuracy	Both outputs (See I	Note 1) ±1% max.
Output voltage		4.75 V < Vo1 < 5.23 V 3.20 V < Vo2 < 3.43 V
(over all line and load conditions)		8.18 V < Vo1 < 3.48 V 2.39 V < Vo2 < 2.60 V
Minimum load	Both outputs	0%
Ripple and noise	20 MHz bandwidth	60 mV pk-pk max., 20 mV rms max.
Transient response peak dev. settling time	50% to 75% and b to 1.0%, no externa	
Short circuit protection		Both outputs
Tracking	st	Outputs track art-up and shutdown

INPUT SPECIFICATIONS

Input voltage range	48 Vin nomin	al 33-75 Vdc
Input current	No load Remote OFF	60 mA max. 20 mA max.
UVLO turn ON voltage UVLO turn OFF voltage		33 V (typ) 30 V (typ)
Start-up time	Nominal line	8 ms (typ)
Active high remote ON/O Logic compatibility ON OFF		(See Note 4) Open Collector ref. to -input Open circuit or >4 Vdc <1.2 Vdc

EMC CHARACTERISTICS

ETS 300 386-1 table 5			
Conducted emissions	EN55022 with e		Level A
	EN55022 with e	xternal filter	Level B
Radiated emissions	EN55022		Level B
Immunity:			
ESD air	EN61000-4-2	8 kV (NP), 1	5 kV (RP)
ESD contact	EN61000-4-2	6 kV (NP),	8 kV (RP)
Radiated field enclosure	EN61000-4-3	10	V/m (NP)
Conducted (DC power)	EN61000-4-6		10 V (NP)
Conducted (signal)	EN61000-4-6		10 V (NP)
Input transients	ETS 300 132-2,	ETR 283	

GENERAL SPECIFICATIONS

Efficiency		See table
Operational insulation	Input/output Input/baseplate	1500 Vdc 1500 Vdc
Input fuse		5 A slow blow
Switching frequency	Fixed	400 kHz (5/3.3 V) 325 kHz (3.3/2.5 V)
Approvals and standards (See Notes 2 and 3)	ι	JL/cUL1950, EN60950 TÜV Rheinland
Weight		45 g (1.6 oz)
MTBF	Telcordia SR-332 @ 25 °C, 100% lo ground benign	3,080,891 hours ad
ENVIRONMENTAL SPE	CIFICATIONS	
Thermal performance	Operating baseplatemperature	ate -40 °C to +100 °C
	Non-operating	-40 °C to +125 °C

EXQ60D Series



CAUTION: Hazardous internal voltages and high temperatures.

Ensure that unit is not user accessible.

Dual positive output

DC/DC CONVERTERS

60 W High Efficiency DC/DC Converters

For the most current data and application support visit www.artesyn.com/powergroup/products.htm

INPUT	OUTPUT	VOLTAGE	OUTPUT C	URRENT	٥V	/P	TYPICAL	MODEL
VOLTAGE	OP1	OP2	1	2	1	2	EFFICIENCY	NUMBER (4,5,6)
33-75 Vdc	5 V	3.3 V	12 A	15 A	5.9 V	4.0 V	91.5%	EXQ60-48D05-3V3J
33-75 Vdc	3.3 V	2.5 V	12 A	16 A	4.0 V	3.0 V	90.5%	EXQ60-48D3V3-2V5J

Notes

1 lo1 = 6 A, lo2 = 9 A

PIN NUMBER

1

2

3

4 5

> 6 7

- 2 User must provide recommended fuses in order to comply with safety approvals.
- 3 Maximum continuous output power.

PIN CONNECTIONS

- 60 Watts for D05-3V3 models
- 40 Watts for D3V3-2V5 models.
- 4 The EXQ60D features 'Active High' Remote ON/OFF as standard. An 'Active Low' Remote ON/OFF version is also available. To order the 'Active Low' version of the EXQ60-48D05-3V3J please add the suffix '-R' towards the end of the part number, i.e. EXQ60-48D05-3V3-RJ. As our part numbers cannot exceed 18 characters when ordering the 'Active Low' version of the EXQ60-48D3V3-2V5J please add the suffix 'R' towards the end of the part number, i.e. EXQ60-48D3V3-2V5RJ.
- 5 When ordering 0.110" pin lengths designate with suffix '-K'. If the product is already a '-R' suffix product then the suffix will be '-RK'.
- 6 The 'J' suffix indicates that these parts are Pb-free (RoHS 6/6) compliant. TSE RoHS 5/6 (non Pb-free) compliant versions may be available on special request, please contact your local sales representative for details.

FUNCTION

+Vin

Remote On/Off

-Vin

Output Return Trim

OP1

	→	2.000 [50.80]	-	0.50 [12.70]
	0.250 [6.35] 1 0.000 [0.00] - @	Bottom View	6 0.975 [24.77] 5 0.725 [18.42] 6 0.475 [12.07] 7 0.225 [5.72] 6 0.000 [0.00]	
	,	PLSj 🖉 M	M3 x 0.5 Threaded Fhrough (4 PLS)	→ → + *0.145 [3.68] *Standard available pin length. 0.110 (2.79) option also available. See Note 5 for ordering details
	1.200 [30.48] ↓ •	Top View	● ↑ 1.500 [38.10] ● ↓	ALL DIMENSIONS IN INCHES [mm]
	1.200 [30.48]	2.000 [50.80] -	→ (4 F	128 [Ø3.25] PLS)
	$\begin{array}{c} 0.950 \ [24.13] - \cdot \cdot 1 \\ 0.600 \ [15.24] - \cdot \cdot 2 \\ 0.250 \ [6.35] - \cdot \cdot 3 \\ 0.000 \ [0.00] - \circ \end{array}$		$\begin{array}{c} 7 & \cdot & - 0.975 \ [24.77] \\ 6 & \cdot & 0.725 \ [18.42] \\ 5 & \cdot & 0.475 \ [12.07] \\ 4 & \cdot & 0.225 \ [5.72] \\ \bullet & - 0.000 \ [0.00] \end{array}$	
5	Becom	Ø0.054 (7 PLS) nended Hole	·	
	necomi	lended Hole	Fallelli	

International Safety Standard Approvals



UL/cUL : UL1950 File No. E135734 TÜV Rheinland Certificate No. 40013415

TÜV Rheinland Certificate No. 40013415 File No. 10401-3336-0208 CB Scheme No. DE1-32228

Datasheet © Artesyn Technologies® 2006

The information and specifications contained in this datasheet are believed to be correct at time of publication. However, Artesyn Technologies accepts no responsibility for consequences arising from printing errors or inaccuracies. Specifications are subject to change without notice. No rights under any patent accompany the sale of any such product(s) or information contained herein.

Please consult our website for the following items: V Application Note V Longform Data Sheet