



Vishay General Semiconductor

Dual High-Voltage Trench MOS Barrier Schottky Rectifier

Ultra Low $V_F = 0.54 \text{ V}$ at $I_F = 5 \text{ A}$



PRIMARY CHARACTERISTICS					
I _{F(AV)}	2 x 30 A				
V _{RRM}	200 V				
I _{FSM}	300 A				
E _{AS} at L = 60 mH	150 mJ				
V _F at I _F = 30 A	0.77 V				
T _J max.	150 °C				

FEATURES

- Trench MOS Schottky technology
- Low forward voltage drop, low power losses

• High efficiency operation

HALOGEN • Solder dip 275 °C max. 10 s, per JESD 22-B106 FREE

• Compliant to RoHS directive 2002/95/EC and in

accordance to WEEE 2002/96/EC Halogen-free according to IEC 61249-2-21 definition

TYPICAL APPLICATIONS

For use in high frequency converters, switching power supplies, freewheeling diodes, OR-ing diode, dc-to-dc converters and reverse battery protection.

MECHANICAL DATA

Case: TO-3PW

Molding compound meets UL 94 V-0 flammability rating Base P/N-M3 - halogen-free and RoHS compliant, commercial grade

Terminals: Matte tin plated leads, solderable per

J-STD-002 and JESD 22-B102

M3 suffix meets JESD 201 class 1A whisker test

Polarity: As marked

Mounting Torque: 10 in-lbs maximum

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)					
PARAMETER		SYMBOL	V60200PGW	UNIT	
Maximum repetitive peak reverse voltage		V_{RRM}	200	V	
Maximum average forward rectified curret (fig. 1)	per device	I _{F(AV)}	60	А	
	per diode		30		
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load per diode		I _{FSM}	300	А	
Non-repetitive avalanche energy at $T_J = 25$ °C, $L = 60$ m	E _{AS}	150	mJ		
Peak repetitive reverse current at t_p = 2 μ s, 1 kHz, T_J = 38 °C \pm 2 °C per diode		I _{RRM}	0.5	А	
Voltage rate of change (rated V _R)	dV/dt	10 000	V/µs		
Operating junction and storage temperature range		T _J , T _{STG}	- 40 to + 150	°C	

V60200PGW

Vishay General Semiconductor



ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)								
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT		
Breakdown voltage	I _R = 1.0 mA	T _A = 25 °C	V_{BR}	200 (minimum)	-	V		
Instantaneous forward voltage per diode	I _F = 10 A	T _A = 25 °C	- V _F ⁽¹⁾	0.69	-	V		
	I _F = 15 A			0.90	-			
	I _F = 30 A			1.28	1.48			
	I _F = 10 A	T _A = 125 °C		0.54	-			
	I _F = 15 A			0.66	-			
	I _F = 30 A			0.77	0.85			
Reverse current per diode	V _R = 180 V	T _A = 25 °C	I _R ⁽²⁾	3.4	-	μΑ		
		T _A = 125 °C		4.6	-	mA		
	V _R = 200 V	T _A = 25 °C		-	210	μΑ		
		T _A = 125 °C		7.5	27	mA		

Notes

 $^{(1)}$ Pulse test: 300 μ s pulse width, 1 % duty cycle

(2) Pulse test: Pulse width ≤ 40 ms

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER		SYMBOL	V60200PGW	UNIT		
Typical thermal resistance	per diode	- R _{θJC}	1.5	°C/W		
	per device		0.8			

ORDERING INFORMATION (Example)						
PACKAGE	AGE PREFERRED P/N UN		PACKAGE CODE	BASE QUANTITY	DELIVERY MODE	
TO-3PW	V60200PGW-M3/4W	4.5	4W	30/tube	Tube	

RATINGS AND CHARACTERISTICS CURVES

 $(T_A = 25 \, ^{\circ}C \text{ unless otherwise noted})$




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Forward Power Loss Characteristics Per Diode



Vishay General Semiconductor




Fig. 3 - Typical Instantaneous Forward Characteristics Per Diode




Fig. 5 - Typical Junction Capacitance Per Diode




Fig. 4 - Typical Reverse Characteristics Per Diode





Fig. 6 - Typical Transient Thermal Impedance Per Diode

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000