| SPE  | <b>CIFICATION CO</b>   | NTROL I             | DRAW                       | <b>ING</b>   | SCD                                 | 55A7564  |
|--|--|---------------------|----------------------------|--------------|-------------------------------------|--|
| Title  | TWO CONDUCTOR CABLE,   |                     | JACKETED,                  |              | Date<br>9-8-14                      | Revision<br>B  |
| GENERAL PURPOSE, 600 VOLT 9-8-14 B   This specification sheet forms a part of the latest issue of Raychem Specification 55A. B   |  |                     |                            |              |                                     |  |
| COM  | IPONENT WIRES - 55A7556  |                     |                            |              |                                     |  |
| CABLE CONSTRUCTION DETAILS   |  |                     |                            |              |                                     |  |
|  | PART NUMBER<br><u>1</u> /<br>CONDUCTOR<br>SIZE<br>(AWG)  |                     | OUTSIDE DIAMETER<br>(inch) |              | MAXIMUM<br>WEIGHT<br>(lbs/1000 ft.) |  |
|  |  |                     | NOMINAL                    | MAXIMUM      |                                     |  |
|  | 55A7564-22-*   | 22                  | .102                       | .107         | 6.9                                 |  |
|  | 55A7564-20-*<br>55A7564-18-*   | 20<br>18            | .120<br>.144               | .125<br>.150 | 9.8<br>15.5                         |  |
|  | 55A7564-16-*   | 16                  | .144                       | .130         | 22.4                                |  |
| CABLE RATINGS AND ADDITIONAL REQUIREMENTS     TEMPERATURE RATING: 200°C     Maximum continuous conductor temperature   1/ PART NUMBER:     VOLTAGE RATING: 600 volts (rms) at sea level   1/ PART NUMBER:     INSULATION FLAWS:   The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors.     Impulse Dielectric Test, 8.0 kV (peak)   Example: AWG 20, black and brown component wires: 55A7564-20-0/1 |  |                     |                            |              |                                     |  |
| NOT  | E: Nominal values are for information o  | only. Nominal value | es are not requ            | irements.    |                                     |  |
| Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.<br>Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.  |  |                     |                            |              |                                     |  |
| 1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER,<br>AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902" MAY BE REPLACED BY "Axxx".) OTHER CODES AND<br>SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.   |  |                     |                            |              |                                     |  |
| Page 1 of 1  | Raychem, TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks.  |                     |                            |              |                                     | aychem Wire & Cable  |
|  | DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL<br>THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.<br>REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID. |                     |                            | D HEREIN.    |                                     | 01 Oakside Avenue<br>Redwood City, CA 94063-3800<br>Phone: 1-800-227-8816<br>Fax: 1-650-361-6297 |
|  |  |                     |                            |              | © 2010-2014 Tyco Electr             | onics Corporation. All rights reserved.  |