

High Efficiency Off-Line CC/CV Switch

FEATURES

- Constant-Current (CC) and
 Constant-Voltage (CV) with Primary Side
 Control
- Proprietary technology enabling high efficiency and fast dynamic response
- Satisfy DoE Level 6 requirements from 5V/1A to 5V/2.4A applications
- No audible noise over entire operating range
- > Optimization for capacitive loading
- Built-in power NPN/MOS
- > Built-in Cable Compensation
- > Built-in Line Compensation
- Primary-side feedback eliminates opto-coupler and TL431
- > Cycle-by-Cycle Current Limiting
- > Over Temperature Protection
- VCC Over Voltage Protection
- > CV Open-loop Protection
- Excellent capacitive loading start-up performance

TYPICAL APPLICATION

- Adapter/Charger for Cell/Cordless Phones,
 PDAs, MP3 and Other Portable Apparatus
- Standby and Auxiliary Power Supplies
 Set Top Boxes (STB)
- > Adapter for ADSL / WiFi Wireless
- AC/DC LED Driver applications

DESCRIPTION

The FT839NX/FT839MX controller device is optimized for high-performance, low power switching mode power supply applications. The FT839NX/FT839MX facilitates CC/CV charger design by eliminating an opto-coupler and TL431. Its highly integrated functions such as Under Voltage Lockout (UVLO), Leading Edge Blanking (LEB) and built-in cable compensation offer the users a high efficiency and low cost solution for AC/DC power applications.

Power supplies built with FT839NX/FT839MX can achieve both highest average efficiency, fast dynamic load response and super low standby power. FT839NX and FT839MX satisfy DoE Level 6 requirements with production margin from 5V/1A to 5V/2.4A applications, respectively.

Furthermore, FT839NX/FT839MX features fruitful protections like Open Circuit Protection and Over Temperature Protection to eliminate the external protection circuits and provide reliable operations. FT839NX is available in SOP8/DIP8 package. FT839MX is available in SOP8 package.

TYPICAL APPLICATION CIRCUIT




Figure 1.1: FT839NX Typical Application Circuit




Figure 1.2: FT839MX Typical Application Circuit

Preliminary FT839NX/839MX

ABSOLUTE MAXIMUM RATINGS

FB to GND	0.3V to +7V
CS to GND	0.3V to +7V
VCC to GND	0.3V to +30V
C to GND	0.3V to +700V
D to GND	0.3V to +650V
Operating Temperature Range	40℃ to +125℃
Junction Temperature	40℃ to +150℃
Storage Temperature Range	60°C to +150°C
ESD Protection HBM	2000\
ESD Protection MM	200\

*Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

PIN CONFIGURATION





Figure 2: Pin Assignments

TERMINAL DEFINITION

Pin	Name	Description		
1	CS	Primary current sense		
2	FB	Output voltage feedback pin		
3	GND	Ground.		
4	VCC	Supply voltage		
5	NC	No connection		
6	INC	No connection		
7	CorD	C: the Collector of the power NPN for FT839NX; D: the Drain of the power MOS for		
8	CorD	FT839MX. This pin is connected to the primary lead of the transformer		

Table 1

ORDERING INFORMATION



FT839NX1/FT839MX1

Device	DESIGNATOR	SYMBOL	Options
FT839NA①		0	Cable Comp = 0%
FT839NB① FT839ND①	①	1	Cable Comp = 3%
FT839NDD①		2	Cable Comp = 6%
FT839MB①	\	3	Cable Comp = 9%

Table 2

MARKING RULE




Figure 3: Marking Rule

- 1): Represents Version (0, 1, 2 or 3)
- (2)(3)(4)(5)(6)(7): for internal reference

Block Diagram




Figure 4.1: FT839NX Block Diagram




Figure 4.2: FT839MX Block Diagram



ELECTRICAL CHARACTERISTICS

(For typical values Tj=25 °C, Vcc=12V, unless otherwise noted)

Characte	eristic	Symbol		Min	Тур	Max	Unit
Current Sense				Į.			
Maximum Current Th	reshold	Vcs_max		541	552	563	mV
Leading Edge Blanki	ng Duration	Tleb		350	400	450	ns
Propagation Delay		Tod				200	
(OUT=1.0nF to GND))	Tpd				200	ns
Secondary Dutycycle							_
Secondary Maximum	Dutycycle	Ds_max			47		%
Feedback Section					•		
Feedback Voltage Th	reshold	Vfb		2.856	2.9	2.944	V
CCM protection Thre	shold Level	Vcp			100		mV
Supply Section			•				
Start Up Threshold V	oltage	Vcc_on		15.5	16.2	17.5	V
Under Voltage Locko	ut Voltage	Vcc_off		5.2	5.5	6.0	V
VCC Start Up Curren	t	lstart_up			2	5	uA
Operating Current		lop		0.4	0.5	0.7	mA
Protection Section						•	
Feedback Loop Oper	n Protection	lfb_open		90	115	140	uA
VCC Over Voltage Protection		Vcc_OVP		26	27	28	V
Over Temperature Pr	rotection	T_OTP			145		°C
Compensation				Į.			
Line Compensation (Ifb=1mA)	Vline		25	33	40	mV
	0				0		
Cable	1		Ī		3		1
compensation	2	Kcab	Ī		6		%
	3		Ī		9		
Power NPN Section	(FT839NX)	I				I.	
Characteristic	Test condition	Symbol		Min	Тур	Max	Unit
Collector-Base	I = 0 4 = = A) / - l		700			
breakdown voltage	Ic=0.1mA	Vcbo		700			V
Collector-Emitter	lo=4 A	1/225		400			
breakdown voltage	Ic=1mA	Vceo		400			V
Emitter-Base	IE-0.4mA	Vaha		0			W
breakdown voltage	IE=0.1mA	Vebo		9			V
Collector-Emitter	IB=0.25A,IC=1A	VCEact			0.3	0.9	V
saturation voltage	1B-0.23A,1C-1A	VCEsat			0.3	0.9	v
Base-Emitter	IB=0.25A,IC=1A	VBEsat			0.9	1.2	V
saturation voltage	15-0.257,10-17	V DESAL			0.9	1.2	v
Maximum collector		FT839NA	Icm	0.39			Α



Preliminary FT839NX/839MX

current		FT839NB		0.40			
		FT839ND		0.70			
		FT839NDD		0.80			
Power MOS Section	(FT839MB)						
Static drain-source on-resistance	R _{DS_ON}	V _{GS} =10 I _{DS} =0.5			4.5		Ω
Drain-source breakdown voltage	BV _{DSS}	V _{GS} =0' I _{DS} =250		650			V
Drain-source leakage current	I _{DSS}	V _{GS} =0' V _{DS} =65	•			10	uA
Maximum Drain Current	I _{DMAX}			0.65			Α

Table 3



FUNCTIONAL DESCRIPTION

Operating Description

FT839NX/FT839MX is a cost effective and high-performance AC-DC power supply controller for off-line low power AC-DC applications including battery chargers, adaptors and LED lighting. The constant voltage (CV) and constant current (CC) control are achieved accurately without the secondary feedback circuit.

Start up Control

Start-up current of FT838NX/FT839MX is very low so that a start-up resistor with high resistance and low-wattage is allowed to supply the start-up power for the controller. The large value startup resistor minimizes the power loss in operations and allows quick start up. With a special fast startup technology, FT839NX/FT839MX starts up easily in capacitive loading applications.

Operating current

The operating current of FT839NX/FT839MX is as low as 500uA. Good efficiency is achieved with the low operating current. Low operating current also reduces the Vcc hold-up capacitance requirement.

Constant voltage (CV) and constant current (CC) Operation

The FT839NX/FT839MX can accurately achieve CV/CC characteristic output without secondary side voltage and current-feedback circuits. It operates in CV mode to regulate the output voltage by capturing the auxiliary winding feedback voltage at FB pin. The auxiliary winding feedback voltage is proportional to secondary winding, so it provides controller the feedback signal from secondary side and achieves constant-voltage output. In CC mode, the controller detects the secondary discharger peak current and the discharger time, which determines the off-time of the base driver to make the output average current constant.

Primary peak current modulation

Primary peak current is constant at constant current mode. And primary peak current is modulated at constant voltage mode for the purposes of good dynamic load response and no audible noise over entire operating range. According to the output loading current the current threshold voltage is modulated from 0.55V to 0.27V. The current threshold voltage is 0.55V at rated load and 0.27V at light load.

Leading edge blanking

Each time the power NPN or MOS transistor is switched on, a turn-on spike occurs at the sense resistor. To avoid premature termination of the switching pulse, a 400ns leading edge blanking time is built in. Conventional RC filtering can therefore be omitted. During this blanking period, the current limit comparator is disabling and cannot switch off the base driver.

Under voltage lockout (UVLO)

FT839NX/FT839MX turn-on Vcc_on and turn-off Vcc_off are 16.2 V and 5.5 V, respectively. During start-up, the hold-up capacitor must be charged to 16.2V through the start-up resistor. The hold-up capacitor continues to supply Vcc until power can be delivered from the auxiliary winding of the

Preliminary FT839NX/839MX

transformer. Vcc must not drop below 5.5 V during this start-up process. This UVLO hysteresis window ensures that hold-up capacitor is sufficient to supply Vcc during start-up.

Protection control

With rich protection features of FT839NX/FT839MX, excellent power supply system reliability can be achieved. The protection features include cycle by cycle current limiting, Vcc over voltage protection and clamp, over temperature protection, feedback loop open circuit protection and Vcc under voltage lockout, etc.

Integrated NPN/MOS

Power NPN/MOS is integrated in FT839NX/FT839MX for low cost and/or space limited applications, respectively.


Output cable compensation

The output cable compensation provides a constant output voltage at the end of the cable over the entire load range in constant voltage mode. As the converter load increases from no-load to the peak current load, the voltage drop introduced across the output cable is compensated by increasing the feedback pin reference voltage.



SOP8 PACKAGE OUTLINE DIMENSIONS


SOP8 Package



Cumahad	Dimensions In Millimeters		Dimension	s In Inches
Symbol	Min	Max	Min	Max
Α	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
С	0.170	0.250	0.006	0.010
D	4.700	5.100	0.185	0.200
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
е	1.270	1.270 (BSC) 0.050 (BSC)		(BSC)
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°



DIP8 PACKAGE OUTLINE DIMENSIONS



Complete	Dimensions i	in Millimeters	Dimensions in Inches		
Symbol	Min	Max	Min	Max	
Α	3.710	4.310	0.146	0.170	
A1	0.510	. () -	0.020		
A2	3.200	3.600	0.126	0.142	
В	0.380	0.570	0.015	0.022	
B1	1.524 (BSC)		0.060 (BSC)		
С	0.204	0.360	0.008	0.014	
D	9.000	9.400	0.354	0.370	
E	6.200	6.600	0.244	0.260	
E1	7.320	7.920	0.288	0.312	
e	2.540 (BSC)		0.100	(BSC)	
Ľ	3.000	3.600	0.118		
E2	8.400	9.000	0.331	0.354	



Fremont Micro Devices (SZ) Limited

#5-8, 10/F, Changhong Building, Ke-Ji Nan 12 Road, Nanshan District, Shenzhen, Guangdong 518057

Tel: (86 755) 86117811 Fax: (86 755) 86117810

Fremont Micro Devices (Hong Kong) Limited

#16, 16/F, Blk B, Veristrong Industrial Centre, 34-36 Au Pui Wan Street, Fotan, Shatin, Hong Kong

Tel: (852) 27811186 Fax: (852) 27811144

Fremont Micro Devices (USA), Inc.

42982 Osgood Road Fremont, CA 94539

Tel: (1-510) 668-1321 Fax: (1-510) 226-9918

Web Site: http://www.fremontmicro.com/

^{*} Information furnished is believed to be accurate and reliable. However, Fremont Micro Devices, Incorporated (BVI) assumes no responsibility for the consequences of use of such information or for any infringement of patents of other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent rights of Fremont Micro Devices, Incorporated (BVI). Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. Fremont Micro Devices, Incorporated (BVI) products are not authorized for use as critical components in life support devices or systems without express written approval of Fremont Micro Devices, Incorporated (BVI). The FMD logo is a registered trademark of Fremont Micro Devices, Incorporated (BVI). All other names are the property of their respective owners.