

# Cable connector - CA-17P1N8A80DN - 1619753

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Cable connector, straight, shielded: yes, Screw locking, M23, Number of positions: 17, Type of contact: Male connector, Crimp connection, Cable diameter: 3 mm ... 14.5 mm

The figure shows the 12-pos. product version

#### **Product Features**

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly



## **Key Commercial Data**

Packing unit	1 pc
Custom tariff number	85366990
Country of origin	Germany

#### Technical data

#### Temperature range

Ambient temperature (operation)	-40 °C 125 °C

#### Data of the insulating body

Note	Order information Order crimp contacts Ø 1 mm separately
Coding	N
Insulator material	PA 66
Contact connection method	Crimp connection
Type of contacts	Male connector
Number of positions	17
Contact diameter of power contacts	1 mm
Nominal current per power contact at 25°C	8 A



# Cable connector - CA-17P1N8A80DN - 1619753

## Technical data

### Data of the insulating body

Nominal voltage, power contact	150 V
Overvoltage category	II
Degree of pollution	3

### Housing data

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	Screw locking
Degree of protection (when plugged in)	IP67
Thread type	M23

#### Cable seal data

Min. cable diameter	3 mm
Max. cable diameter	14.5 mm
Sealing material	NBR

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	272607xx
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260702
eCl@ss 7.0	27440102
eCl@ss 8.0	27440102

#### **ETIM**

ETIM 3.0	EC001121
ETIM 4.0	EC002635
ETIM 5.0	EC002635

#### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404



# Cable connector - CA-17P1N8A80DN - 1619753

Approvals	
Approvals	
Approvals	
UL Recognized / cUL Recognized / EAC	
Ex Approvals	
Approvals submitted	
Approval details	
UL Recognized <b>3</b>	
cUL Recognized	
EAC	
Drawings	
Schematic diagram	Dimensional drawing
X 110 01 Y	≈ 58,2

Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com