


PRODUCT DATA SHEET

Part Number: 1909XM5XWE

Туре	Size	Rating	Description
LED	M8	8 - 32Vdc	LED Recessed Panel Indicator with leads

Dimensions (mm)



Part #	Colour	Current (mA) nom.	Intensity (mcd) nom.
1909XM50WE	Red	2.9	250
1909XM51WE	Green	2.9	400
1909XM52WE	Yellow	2.9	140
1909XM57WE	Blue	2.9	140

Bezel finish: X = 0 Satin chrome: X = 1 Black chrome: X = 2 Matt chrome

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 LED Luminous intensity without lens
- 3 Storage temperature -25°C to +80°C
- 4 Application temperature -20°C to +60°C
- 5 Due to component tolerances, slight colour variations may be observed
- 6 Sealed to IP67 above panel when supplied gasket used
- 7 The plastic (polycarbonate) has limited chemical resistance
- 8 Lead wires are internally soldered
- 9 Lead wires: 7/0.2 stranded copper, tinned annealed copper wire, PVC insulation
- 10 Marking: Part number, voltage rating and date code
- 11 This product contains free-machining brass and is RoHS compliant via exemption clause 2011/65/EU Directive Annex III 6 (c) [Copper alloy containing lead (Pb) up to 4% by weight]
- 12 This product contains lead (Pb) as a constituent of free-machining brass. Lead (Pb) is present in the bezel at less than 4% by weight

Page 1 of 1 Issue 2: 22Nov18