IRE J:K007





The Most Powerful M5Stack Kit!

utorial&Quick-Start

se the development platform you want to use, view the corresponding tutorial&quick-Start.

low Arduino

)escription

tack FIRE Kit, as one of the M5Stack developing kit series, is an upgrade from the Gray kits. Providing 9-Axis IMU sensor(6-Axis posture acceleratio ;urement + 3-Axis magnetic measurement), it equips with more hardware resources : 16M Flash + 8M PSRAM , enhanced Base (M5GO Base and M⁴. Base), larger battery, etc. For those developers who ask for hardware performance, Fire will be a good choice.

a IMU posture sensor, there are a lot of situations which you can apply this kit to: detecting acceleration, angulation, and trajectory. You can make

ve products like sports data collector, 3D remote gesture controller and more base on the above functions.

is M5 Core device. Its modular, stackable, scalable, and portable device is powered with an ESP-32 core, which makes it open source, low cost, fullion, and easy for developers to handle new product development on all stages include circuit design, PCB design, software, mold design and uction.

tack Fire comes with three separable parts. The top part ,just like Basic and Gray Kit, has all kinds of processors, chips ,sockets, 2.4G antenna, ESP32, er management IC , a LCD screen and some other interface components. The middle part is called M5GO base which provides a lithium battery, M-F et , LED bar and three more GROVE Ports. The bottom part is a charge table, which can be connected to the M5GO base via POGO pins.

ortive development platforms and programming languages: Arduino, Blockly language with UIFlow, Micropython. Regardless of what level ramming skill you have, M5Stack would guide you in every step of the way to realize your idea as well as to the final productlization.

J ever played with ESP8266, you would realize that ESP32 is a perfect upgrade out of ESP8266. In comparison, ESP32 has more GPIOs, more analog ts and two analog outputs, multiple extra peripherals(like a spare UART). Official developing platform ESP-IDF has transplanted with FreeRTOS. Wi -core and real time OS you can get more organized code and much high speed processor.

Notice:

The GPIO 16 / 17 in Fire is connected to the PSRAM by default, so when you connect or stack other function modules, you

need to avoid conflicts with these two pins to prevent the device from working improperly and causing instability.

Power on/off:

Power on: click the red power button on the left Power off: Quickly double-click the red power button on the left Note: By default, when USB is powered, it cannot be shut down**

roduct Features

SP32-based

peaker, 3 Buttons, LCD(320*240)

F card slot (16G Maximum size)

attery Socket & Lipo Battery

xtendable Pins & Holes

/I-Bus Socket & Pins

lude

x FIRE

x M5GO CHG Base

x LEGO block

x LEGO connector

x M3 HEX KEY

x Type-C USB(100cm)

x User Manual

pplications

nternet of things terminal controller

tem education product

pecification

Resources	Parameter	
ESP32	240MHz dual core, 600 DMIPS, 520KB SRAM, Wi-Fi, dual mode Bluetooth	
Flash Memory	16MB	
PSRAM	8MB	
Power Input	5V @ 500mA	
Port	TypeC x 1, GROVE(I2C+I/0+UART) x 1	
IPS Screen	2 inch, 320x240 Colorful TFT LCD, ILI9342C, max brightness 853nit	
Snoakor	1\\/_0028	

Speaker		
Button	Custom button x 3	
MEMS	BMM150 + MPU6886	
Battery	500 mAh @ 3.7V	
Antenna	2.4G 3D Antenna	
Operating Temperature	0°C to 60°C	
Net weight	62.3g	
Gross weight	162g	
Product Size	54mm x 54mm x 30.5mm	
Package Size	105mm x 65mm x 40mm	
Case Material	Plastic (PC)	

GO Bottom

to view details parameters

asyLoader

EasyLoader is a concise and fast program writer, which has a built-in case program related to the product. It can be burned to the main control by simple steps to perform a series of function verification.

wnload Windows Version Easyloader

Description:

Load UIFlow firmware, built-in demo program supports testing of accelerometer, LED BAR, microphone, buttons and some peripheral sensors. The firmware can be used for UIFlow graphical programming.

eripherals Pin Map

& TF card

: 320x240 TF card Maximum size 16GB

SP32 Chip	GPIO23	GPIO19	GPIO18	GPIO14	GPIO27	GPIO33	GPIO32
ILI9342C	MOSI/MISO	/	CLK	CS	DC	RST	BL
TF Card	MOSI	MISO	CLK				

on & Speaker

GFIUSS GFIUSS GFIUSS GFIUSS	ESP32 Chip	GPIO39	GPIO38	GPIO37	GPIO25
-----------------------------	------------	--------	--------	--------	--------

ESP32 Chip	GPIO39	GPIO38	GPIO37	GPIO25
Button Pin	BUTTON A	BUTTON B	BUTTON C	/
Speaker				Speaker Pin

VE Port A & IP5306

e use the customized I2C version of IP5306, on power management.

C address is 0x75. Click here to check its datasheet

ESP32 Chip	GPIO22	GPIO21	5 V	GND
GROVE A	SCL	SDA	5V	GND
IP5306	SCL	SDA	5V	GND

06 charging/discharging,Voltage parameter

charging

0.00 ~ 3.40V -> 0%	4.20 ~ 4.07V -> 100%
3.40 ~ 3.61V -> 25%	4.07 ~ 3.81V -> 75%
3.61 ~ 3.88V -> 50%	3.81 ~ 3.55V -> 50%
3.88 ~ 4.12V -> 75%	3.55 ~ 3.33V -> 25%
4.12 ~ / -> 100%	3.33 ~ 0.00V -> 0%

discharging

is MotionTracking Sensor MPU6886

6886 I2C address 0x68

ESP32 Chip	GPIO22	GPIO21	5 V	GND
MPU6886	SCL	SDA	5V	GND

is Geomagnetic Sensor BMM150

1150 I2C address 0x10

ESP32 Chip	GPIO22	GPIO21	5V	GND
BMM150	SCL	SDA	5V	GND



15GO Base Port

VE Port B

ESP32 Chip	GPIO36	GPIO26	5V	GND
GROVE B	GPIO36	GPIO26	5V	GND

VE Port C

ESP32 Chip	GPIO16	GPIO17	5V	GND
GROVE C	RXD	TXD	5V	GND

Bar & Micphone & Speaker

ESP32 Chip	GPIO15	GPIO34	GPIO25
Hardwares	SIG Pin	MIC Pin	Speaker Pin

15PORT EXPLAIN

PORT-A(Red)	G21/22	I2C
PORT-B(Black)	G26/36	DAC/ADC
PORT-C(Blue)	G16/17	UART

SP32 ADC/DAC

ADC1	ADC2	DAC1	DAC2
8 channels	10 channels	2 channels	2 channels
G32-39	G0/2/4/12-15/25-27	G25	G26

Analog Function					Analog Function	GPIO TYPE
	GND		ADC	G35	ADC1_CH7	I
	GND GND		ADC	G36	ADC1_CH0	I
			RST	EN		
	G23	MOSI	DAC/SPK	G25	ADC2_CH8	I/0/T
	G19	MISO	DAC	G26	ADC2_CH9	I/0/T
	G18	SCK	3.3V			
	G3	RXD1	TXD1	G1		I/0/T
	G16	RXD2	TXD2	G17		I/0/T
	G21	SDA	SCL	G22		I/0/T
ADC2_CH2/T2	G2	GPIO	GPIO	G5		I/0/T
ADC2_CH5	G12	IIS_SK	IIS_WS	G13	ADC2_CH4/T4	I/0/T
ADC2_CH3/T3	G15	IIS_OUT	IIS_MK	G0	ADC2_CH1/T1	I/0/T
	HPWR		IIS_IN	G34	ADC1_CH6	I
		HPWR	5V			
	HPWR		BATTE	RY		

n using the RGB LED of gpio15, it is recommended to initialize,pinMode(15, OUTPUT_OPEN_DRAIN); For more information about Pin assignment ar temapping, Please refer to ESP32 Datasheet

chematic

chematic

elated Link

atasheet			
• ESP32			
 MPU6886 			
· BMM150			
○ SH200Q			
○ IP5306			
PI			
 Arduino API 			

earn



M5Stack Christmas Snow Globe

Modern times make modern solutions possible. Therefore, the step to a digital snow globe is not that far.



Q-Bot

We aim to build a robot that is effective in sanitizing surfaces without putting cleaners in harm's way.



Office M5Stack Assistant

An IoT office assistant with "free, busy and lunch" indicators, Pomodoro timers and quick meetings with IFTTT and your calendar integration.



Audio Spectrum Display with M5Stack

An audio spectrum visualiser using the M5Stack internal mic or FC-04 sound sensor with the M5Stack core. Translated from a guide by macsbug





M5Stack COM.LoRaWAN Using UIFlow

M5Stack recently released an updated LoRaWAN module. This tutorial teaches you how to connect it to The Things Network using UIFlow.



RTC Modules with M5Stack

Out of the M5Stack family only the M5StickC has an inbuilt RTC. Here's how to add one to your other M5Stac devices



luino

lickhereto get Arduino code



tack instroduce

'ersion Change

elease Date	Product Change	Note:				
2018.6	Initial public release					
2010 7	MPU9250 changed to SH200Q+BMM150, TN	before use . pls upgrade your M5Stack lib to the latest version (after 0.2.8				
2019.7	screen changed to IPS screen	to solve screen reverse color problem.				
2019.8	SH200Q changed to MPU6886					
2010 11	Battery capacity changed from 600mAh to					
2019.11	500mAh					

2020.4 PSRAM Size changed from 4MB to 8MB