



FD-33S



Applications	For Distribution Lines
Feature	SF6 Gas Insulated SF6 Gas (Insulation Type)
Series	FD
Status	 Production



Size	
D	34.00mm +/-1.00mm
L	39.00mm +/-1.00mm
T	35.00mm +1.00,-2.00mm
d	10.00mm +/-0.50mm
Screw Thread	ISO M4

Electrical Characteristics	
Capacitance	250pF +/-10%
Rated Voltage	25kVAC
Withstanding Voltage (Nom.)	40kVAC
AC Corona Starting Voltage [3PC] (Min.)	32kVAC
Lightning Impulse Withstand Voltage (Min.)	90kV
Temperature Characteristic	Y5P(+/-10%)
Dissipation Factor (Max.)	0.3%
Insulation Resistance (Min.)	10000MΩ

Other	
Operating Temperature Range	-30 to 85°C
Storage Temperature Range	-30 to 85°C
Packing	Box
Weight	123g