

Product data sheet

1. General description

Planar passivated three quadrant high commutation triac in a SOT223 surface mountable plastic package for use in motor control circuits or with other highly inductive loads. This triac balances the requirements of commutation performance and gate sensitivity.

2. Features and benefits

3Q technology for improved noise immunity

High commutation capability

High immunity to false turn-on by dV/dt

Less sensitivite gate for high noise immunity

Planar passivated for voltage ruggedness and reliability

Surface mountable package

3. Applications

- General purpose motor controls
- Small loads in washing machines
- Rectifier-fed DC inductive loads e.g. DC motors and solenoids

4. Quick reference data

Table 1. Quid	ck reference data					
Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V _{DRM}	repetitive peak off- state voltage		-	-	600	V
I _{TSM}	non-repetitive peak on- state current	full sine wave; $T_{j(init)} = 25 \text{ °C};$ $t_p = 20 \text{ ms}; \text{ Fig. 4}; \text{ Fig. 5}$	-	-	10	A
I _{T(RMS)}	RMS on-state current	full sine wave; T _{sp} ≤ 108 °C; <u>Fig. 1;</u> <u>Fig. 2; Fig. 3</u>	-	-	1	A





BTA204W-600F

3Q Hi-Com Triac

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
Static char	Static characteristics						
I _{GT}	gate trigger current	$V_D = 12 \text{ V}; \text{ I}_T = 0.1 \text{ A}; \text{ T2+ G+};$ T _j = 25 °C; <u>Fig. 9</u>		-	-	25	mA
		V _D = 12 V; I _T = 0.1 A; T2+ G-; T _j = 25 °C; <u>Fig. 9</u>		-	-	25	mA
		V _D = 12 V; I _T = 0.1 A; T2- G-; T _j = 25 °C; <u>Fig. 9</u>		-	-	25	mA

5. Pinning information

Table 2.	Pinning	information		
Pin	Symbol	Description	Simplified outline	Graphic symbol
1	T1	main terminal 1	4	T2
2	T2	main terminal 2		sym051
3	G	gate		
4	mb	mounting base; connected to main terminal 2	⊟1 ⊟2 ⊟3 SC-73 (SOT223)	

6. Ordering information


Table 3. Ordering information							
Type number	Package						
	Name	Description	Version				
BTA204W-600F	SC-73	plastic surface-mounted package with increased heatsink; 4 leads	SOT223				


7. Limiting values


Table 4.Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).


Symbol	Parameter	Conditions	Min	Max	Unit
V _{DRM}	repetitive peak off-state voltage		-	600	V
I _{T(RMS)}	RMS on-state current	full sine wave; T _{sp} ≤ 108 °C; <u>Fig. 1;</u> <u>Fig. 2; Fig. 3</u>	-	1	A
I _{TSM}	non-repetitive peak on-state	full sine wave; $T_{j(init)}$ = 25 °C; t_p 16.7 ms	-	11	А
	current	full sine wave; T _{j(init)} = 25 °C; t _p = 20 ms; <u>Fig. 4</u> ; <u>Fig. 5</u>	-	10	А
l ² t	I ² t for fusing	t _p = 10 ms; SIN	-	0.5	A ² s
dI _T /dt	rate of rise of on-state current	I_{T} = 1.5 A; I_{G} = 0.2 A; dI_{G}/dt = 0.2 A/µs	-	100	A/µs
I _{GM}	peak gate current		-	2	А
P _{GM}	peak gate power		-	5	W
P _{G(AV)}	average gate power	over any 20ms period	-	0.5	W
T _{stg}	storage temperature		-40	150	°C
Tj	junction temperature		-	125	°C








3Q Hi-Com Triac



BTA204W-600F


3Q Hi-Com Triac



3Q Hi-Com Triac


8. Thermal characteristics

Table 5.	Thermal characteristics					
Symbol	Parameter	Conditions	Min	Тур	Max	Unit
R _{th(j-sp)}	thermal resistance from junction to solder point	full cycle or half cycle; Fig. 6	-	-	15	K/W
R _{th(j-a)} thermal resistance from junction to	-	in free air; printed circuit board mounted: minimum pad area; <u>Fig. 7</u>	-	70	-	K/W
	ambient	in free air; printed circuit board mounted: minimum footprint; Fig. 8	-	156	-	K/W



BTA204W-600F

3Q Hi-Com Triac






3Q Hi-Com Triac

9. Characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Static char	acteristics		Ì			
I _{GT}	gate trigger current	$V_D = 12 V; I_T = 0.1 A; T2+G+;$ $T_j = 25 °C; Fig. 9$	-	-	25	mA
		$V_D = 12 V; I_T = 0.1 A; T2+G-;$ $T_j = 25 °C; Fig. 9$	-	-	25	mA
		V _D = 12 V; I _T = 0.1 A; T2- G-; T _j = 25 °C; <u>Fig. 9</u>	-	-	25	mA
I _L latchin	latching current	V _D = 12 V; I _G = 0.1 A; T2+ G-; T _j = 25 °C; <u>Fig. 10</u>	-	-	20	mA
		V _D = 12 V; I _G = 0.1 A; T2+ G+; T _j = 25 °C; <u>Fig. 10</u>	-	-	30	mA
		$V_D = 12 \text{ V}; \text{ I}_G = 0.1 \text{ A}; \text{ T2- G-};$ T _j = 25 °C; Fig. 10	-	-	20	mA
I _H	holding current	V _D = 12 V; T _j = 25 °C; <u>Fig. 11</u>	-	-	30	mA
V _T	on-state voltage	I _T = 2 A; T _j = 25 °C; <u>Fig. 12</u>	-	1.2	1.5	V
V _{GT}	gate trigger voltage	V _D = 12 V; I _T = 0.1 A; T _j = 25 °C; Fig. 13	-	0.7	1	V
		V _D = 400 V; I _T = 0.1 A; T _j = 125 °C; Fig. 13	0.25	0.4	-	V
I _D	off-state current	V _D = 600 V; T _j = 125 °C	-	0.1	0.5	mA
Dynamic cl	haracteristics	· · · · ·	ł	1		
dV _D /dt	rate of rise of off-state voltage	V_{DM} = 402 V; T _j = 125 °C; (67% of V_{DRM}); exponential waveform; gate open circuit	50	-	-	V/µs
dl _{com} /dt	rate of change of commutating current	V_D = 400 V; T_j = 125 °C; $I_{T(RMS)}$ = 1 A; dV _{com} /dt = 20 V/µs; (snubberless condition); gate open circuit	2.5	-	-	A/ms

BTA204W-600F

3Q Hi-Com Triac




All information provided in this document is subject to legal disclaimers.

BTA204W-600F

BTA204W-600F

3Q Hi-Com Triac





3Q Hi-Com Triac

10. Package outline





 Fig. 14. Package Outline SC-75 (SO1225)

 BTA204W-600F

 All information provided in this document is subject to legal disclaimers.

3Q Hi-Com Triac

11. Soldering



BTA204W-600F

All information provided in this document is subject to legal disclaimers.

3Q Hi-Com Triac

12. Legal information

12.1 Data sheet status

Document status [1][2]	Product status [<u>3]</u>	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <u>http://www.nxp.com</u>.

12.2 Definitions

Preview — The document is a preview version only. The document is still subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

12.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the

BTA204W-600F

3Q Hi-Com Triac

grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

12.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Adelante, Bitport, Bitsound, CoolFlux, CoReUse, DESFire, EZ-HV, FabKey, GreenChip, HiPerSmart, HITAG, I²C-bus logo, ICODE, I-CODE, ITEC, Labelution, MIFARE, MIFARE Plus, MIFARE Ultralight, MoReUse, QLPAK, Silicon Tuner, SiliconMAX, SmartXA, STARplug, TOPFET, TrenchMOS, TriMedia and UCODE — are trademarks of NXP Semiconductors N.V.

HD Radio and **HD Radio** logo — are trademarks of iBiquity Digital Corporation.

3Q Hi-Com Triac

13. Contents

1	General description	1
2	Features and benefits	1
3	Applications	1
4	Quick reference data	1
5	Pinning information	2
6	Ordering information	2
7	Limiting values	3
8	Thermal characteristics	6
9	Characteristics	8
10	Package outline	11
11	Soldering	12
12	Legal information	13
12.1	Data sheet status	13
12.2	Definitions	13
12.3	Disclaimers	13
12.4	Trademarks	14

© NXP Semiconductors N.V. 2014. All rights reserved

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com Date of release: 15 August 2014