

Skin:

Inhalation:

some sensitive individuals.

nose and respiratory tract.

SAFETY DATA SHEET

Page 1 of 6

SDS-E-CL-WBC Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, 2001/58 & 1272/2008/EC Standards SDS Revision Date: 3/14/2018 1. PRODUCT & COMPANY IDENTIFICATION 1.1 Product Name: WHITE BOARD CLEANER (Part No. CL-WBC-8), 8 ounce Bottle 12 Chemical Name: Aqueous solution 1.3 Synonyms: NA 14 Trade Names CAIG White Board Cleaner, CL-WBC 1.5 Product Uses & Restrictions: Cleaner for Dry Erase Board 1.6 Distributor's Name: CAIG Laboratories. Inc. 1.7 Distributor's Address: 12200 Thatcher Court, Poway, CA 92064-6876 USA CHEMTREC: +1 (703) 527-3887 / +1 (800) 424-9300 (CCN205206) 1.8 Emergency Phone: 19 Business Phone / Fax: +1 (800) 224-4123 2. HAZARDS IDENTIFICATION Hazard Identification: This product is classified as a HAZARDOUS SUBSTANCE but not as DANGEROUS GOODS according to the classification criteria of NOHSC: 1088 (2004) and ADG Code (Australia). WARNING! CAUSES EYE IRRITATION. CAUSES MILD SKIN IRRITATION. Classification: Eye Irrit. 2B; Skin Irrit. 2 Hazard Statements (H): H316 – Causes mild skin irritation. H320 – Causes eye irritation. 22 Label Elements: Precautionary Statements (P): P264 - Wash thoroughly with soap and water after handling. P332+P313 - IF skin irritation occurs: Get medical advice/attention. P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P337+P313 - If eye irritation persists: Get medical advice/attention. 2.3 Other Warnings: KEEP OUT OF REACH OF CHILDREN 3. COMPOSITION & INGREDIENT INFORMATION EXPOSURE LIMITS IN AIR (mg/m³) ACGIH NOHSC **OSHA** ppm ppm ppm FS-FS-FS-RTECS No. EINECS No. STEI PEL STEL IDLH OTHER CHEMICAL NAME(S) CAS No. TWA STE PEAK 7732-18-5 ZC0110000 231-191-2 60-100 NA NA NF NF NF NA NA NA WATER (AQUA/EAU) 5131-66-8 UA7700000 225-878-4 1-5 NA NA NF NF NF NA NA NA BUTOXYPROPANOL Eye Irrit. 2B; Skin Irrit. 2; H320, H315 NT8050000 200-661-7 1-5 400 500 400 500 NF 400 | 500 | 2000 | 400 TWA ISOPROPYL ALCOHOL Flam. Liq. 2; Skin Irrit. 3; Eye Irrit. 2; STOT SE 3; H225, H316, H319 4. FIRST AID MEASURES If ingested, do not induce vomiting. If product has been swallowed, drink plenty of water or milk First Aid: Ingestion: IMMEDIATELY. If the patient is vomiting, continue to offer water or milk. Never give water or milk to an unconscious person. Contact the nearest Poison Control Center or local emergency number. Provide an estimate of the time at which the material was ingested and the amount of the substance that was swallowed. Eyes: Splashes are not likely; however, if product gets in the eyes, flush with copious amounts of lukewarm water for at least 15 minutes lifting upper and lower lids, occasionally. Skin: Wash thoroughly with soap and water. In case of contact, immediately flush skin with plenty of water for at least 15 minutes. Inhalation: Remove victim to fresh air at once. If breathing difficult, administer oxygen. If breathing stops give artificial respiration. Keep person warm, quiet and get medical attention. 4.2 Effects of Exposure: If product is swallowed, may cause nausea, temporary gastrointestinal irritation, vomiting and/or diarrhea. Ingestion: Moderately irritating to the eyes. Symptoms of overexposure may include redness, itching, irritation and Eyes: Skin: May be irritating to skin. The product can cause allergic skin reactions (e.g., rashes, welts, dermatitis) in some sensitive individuals. Coughing, wheezing, shortness of breath, impaired pulmonary function. Irritation or soreness in throat, Inhalation: nose and respiratory tract. 43 Symptoms of Overexposure: If product is swallowed, may cause gastrointestinal disturbance. Ingestion: Exposure may cause eye irritation. Symptoms of overexposure may include redness, itching, irritation and Eyes:

May be irritating to skin. The product can cause allergic skin reactions (e.g., rashes, welts, dermatitis) in

Coughing, wheezing, shortness of breath, impaired pulmonary function. Irritation or soreness in throat,



Page 2 of 6 SDS-E-CL-WBC

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, 2001/58 & 1272/2008/EC Standards SDS Revision Date: 3/14/2018 4. FIRST AID MEASURES - cont'd 4 4 Acute Health Effects: Non-irritating when used as directed. Moderate irritation to eyes and skin near affected areas. Additionally, high concentrations can cause iirritation or soreness in throat, nose and respiratory tract 4.5 Chronic Health Effects: Non-irritating when used as directed. Possible allergic dermatitis in some sensitive individuals 4.6 Target Organs: Eyes, Skin Medical Conditions 4.7 Pre-existing dermatitis, other skin conditions, and disorders of the **HEALTH** 1 Aggravated by Exposure: target organs (eves. skin) or impaired kidney function may be more **FLAMMABILITY** 1 susceptible to the effects of this substance. 0 **PHYSICAL HAZARDS** PROTECTIVE EQUIPMENT В EYES SKIN 5. FIREFIGHTING MEASURES Fire & Explosion Hazards: Cool uninvolved containers to prevent possible bursting. If involved in a fire, this product may decompose at high temperatures to form toxic gases (e.g., CO, CO_X, hydrocarbons). 52 Extinguishing Methods: CO₂, Dry Chemical, Alcohol foam, Dry Chemical. Use water spray to cool containers. 5.3 Firefighting Procedures: Keep containers cool until well after the fire is out. Fight fires as for surrounding materials. As in any fire, wear MSHA/NIOSH approved self-contained breathing apparatus (pressure-demand) and full protective gear. Keep containers cool until well after the fire is out. Use water spray to cool fire-exposed surfaces and to protect personal. Fight fire upwind. Avoid spraying water directly into storage containers because of danger of boil-over. Prevent runoff from fire control or dilution from entering sewers, drains, drinking water supply, or any natural waterway. Firefighters must use full bunker gear including NIOSH-approved positive pressure self-contained breathing apparatus to protect against potential hazardous combustion or decomposition products and oxygen deficiencies 6. ACCIDENTAL RELEASE MEASURES Spills Before cleaning any spill or leak, individuals involved in spill cleanup must wear appropriate Personal Protective Equipment. For small spills (e.g., < 1 gallon (3.8 L)) wear appropriate personal protective equipment (e.g., goggles, gloves). Maximize ventilation (open doors and windows). Remove spilled material with absorbent material and place into appropriate closed container(s) for disposal. Dispose of properly in accordance with local, state and federal regulations. Wash all affected areas and outside of container with plenty of warm water and soap. Remove any contaminated clothing and wash thoroughly before reuse. For large spills (e.g., ≥ 1 gallon (3.8 L)), deny entry to all unprotected individuals. Dike and contain spill with inert material (e.g., sand or earth). Transfer product to containers for recovery or disposal and solid diking material to separate containers for proper disposal. Remove contaminated clothing promptly and wash affected skin areas with soap and water. Keep spills and cleaning runoffs out of municipal sewers and open bodies of water. 7. HANDLING & STORAGE INFORMATION 7 1 Work & Hygiene Practices: Do not eat, drink or smoke when handling this product. Handle as to avoid puncturing container(s). Wash unintentional residues with soap and warm water. Keep tightly closed when not in use. Avoid contact with skin and clothing. 7.2 Storage & Handling: Use and store in a cool, dry, well-ventilated location (e.g., local exhaust ventilation, fans) away from heat and direct sunlight. Keep away from incompatible substances. Protect containers from physical damage. Avoid breathing vapor. 7.3 Special Precautions: Spilled material may present a slipping hazard if left unattended. Clean all spills promptly. Empty containers may contain product residues. Avoid contaminating soil or releasing this material into sewage and drainage systems and bodies of water. 8. EXPOSURE CONTROLS & PERSONAL PROTECTION Exposure Limits: NOHSC OSHA OTHER ppm (mg/m³) ES-ES-CHEMICAL NAME(S) TLV STEL ES-STEL STEL IDLH ISOPROPYL ALCOHOL 400 TWA 8.2 Ventilation & Engineering When working with large quantities of product, provide adequate ventilation (e.g., local exhaust ventilation, fans). Ensure that an eyewash station, sink or washbasin is available in case of exposure to eyes. 8.3 Respiratory Protection: No special respiratory protection is required under typical circumstances of use or handling. If necessary, use only respiratory protection authorized per U.S. OSHA's requirement in 29 CFR §1910.134, or applicable U.S. state regulations, or the appropriate standards of Canada, its provinces, E.C. member states, or Australia. 8.4 Eye Protection: Avoid eye contact due to irritation potential. Wear protective eyewear (e.g., safety glasses with side-shield) when handling large amounts (≥1L) of this product. Always use protective evewear when cleaning spills or leaks. Contact lenses pose a special hazard; soft lenses may absorb and concentrate irritants.



Page 3 of 6 SDS-E-CL-WBC

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, 2001/58 & 1272/2008/EC Standards

SDS Revision: 3.1

SDS Revision Date: 3/14/2018

	8.	EXPOSURE CONTROLS & PERSONAL PROTECTION – cont'd		
8.5	Hand Protection:	Avoid skin contact due to irritation potential. Use gloves constructed of chemical resistant materials such as neoprene or heavy nitrile rubber if frequent or prolonged contact is expected.		
8.6	Body Protection:	No apron required when handling small quantities. When handling large quantities (e.g., ≥ 1 gallon), eye wash stations and deluge showers should be available. Upon completion of work activities involving large quantities of this product, wash any exposed areas thoroughly with soap and water.		
		9. PHYSICAL & CHEMICAL PROPERTIES		
9.1	Appearance:	Clear, colorless liquid		
9.2	Odor:	Slight alcohol odor		
9.3	Odor Threshold:	NA NA		
9.4	pH:	NA NA		
9.5	Melting Point/Freezing Point:	NA NA		
9.6	Initial Boiling Point/Boiling Range:	NA NA		
9.7	Flashpoint:	NA NA		
9.8	Upper/Lower Flammability Limits:	NA NA		
9.9	Vapor Pressure:	NA		
9.10	Vapor Density:	NA		
9.11	Relative Density:	NA NA		
9.12	Solubility:	Soluble		
9.13	Partition Coefficient (log Pow):	NA		
9.14	Autoignition Temperature:	NA		
9.15	Decomposition Temperature:	NA		
9.16	Viscosity: Other Information:	NA		
9.17	Other information:	NA		
		10. STABILITY & REACTIVITY		
10.1	Stability:	Stable under normal conditions; unstable with heat or contamination.		
10.2	Hazardous Decomposition Products:	Will not degrade to unstable products. Discard solution.		
10.3	Hazardous Polymerization:	Will not occur.		
10.4	Conditions to Avoid:	Open flames, sparks, high heat, incompatible substances and direct sunlight.		
10.5	Incompatible Substances:	Avoid extreme heat and store away from oxidizers.		
		11. TOXICOLOGICAL INFORMATION		
11.1	Routes of Entry:	Inhalation: YES Absorption: YES Ingestion: YES		
11.2	Toxicity Data:	1 125		
	,	This product has not been tested on animals to obtain toxicological data. Toxicology data for some of the components in this mixture, found in scientific literature.		
	Acute Toxicity:	See section 4.4		
11.4	Chronic Toxicity:	This material may aggravate any pre-existing skin condition (e.g., dermatitis).		
11.5	Suspected Carcinogen:	This product contains <u>Isopropyl Alcohol</u> , which is not carcinogenic to humans, but is listed as a Group 3 carcinogen by the IARC. This product does not contain any chemicals known to the State of California to cause cancer or other reproductive harm. For more information go to <u>www.P65Warnings.ca.gov</u> .		
11.6	Reproductive Toxicity:	This product is not reported to produce reproductive toxicity in humans.		
	Mutagenicity:	This product is not reported to produce mutagenic effects in humans.		
	Embryotoxicity:	This product is not reported to produce embryotoxic effects in humans.		
	Teratogenicity:	This product is not reported to cause teratogenic effects in humans.		
	Reproductive Toxicity:	This product is not reported to cause reproductive effects in humans.		
11.7	Irritancy of Product:	The product can cause allergic skin reactions (e.g., rashes, welts, dermatitis) upon prolonged or repeated exposure.		
11.8	Biological Exposure Indices:	NE NE		
11.9	Physician Recommendations:	Treat symptomatically.		



Page 4 of 6 SDS-E-CL-WBC

SDS Revision Date: 3/14/2018

12. ECOLOGICAL INFORMATION The components of this product will slowly degrade over time into a variety of organic compounds. 12 1 Environmental Stability: environmental data available for the components of this product are as follows: Isopropyl Alcohol: Log Kow = 0.05-0.14. Isopropyl alcohol occurs naturally; it is generated during microbial degradation of plant and animal wastes. When released on land or water, it is apt to volatilize and biodegrade. The estimated halflife in water is 5.4 days. Isopropyl alcohol is not expected to bioconcentrate. Effects on Plants & Animals: 12.2 There are no specific data available for this product. 12.3 Effects on Aquatic Life: This material should be kept out of sewage and drainage systems and all bodies of water. Releases of large volumes of this product are expected to be harmful or fatal to overexposed aquatic life. 13. DISPOSAL CONSIDERATIONS 13.1 Waste Disposal: Products covered by this SDS, in their original form, when disposed as waste, are considered non hazardous waste according to Federal RCRA regulations (40 CFR 261). Disposal should be in accordance with local, state and federal regulations. Dispose of in accordance with federal, state and local regulations. 13.2 Special Considerations: Contact the federal, state or provincial environmental authority to determine suitability for recycling and or proper disposal requirements. 14. TRANSPORTATION INFORMATION The basic description (ID Number, proper shipping name, hazard class & division, packing group) is shown for each mode of transportation. Additional descriptive information may be required by 49 CFR, IATA/ICAO, IMDG and the CTDGR. 49 CFR (GND): **NOT REGUALTED** IATA (AIR): 14.2 **NOT REGUALTED** IMDG (OCN): 14.3 NOT REGUALTED TDGR (Canadian GND): 14.4 NOT REGUALTED 14.5 ADR/RID (EU): **NOT REGUALTED** 14 6 SCT (MEXICO): **NOT REGUALTED** 14.7 ADGR (AUS): **NOT REGUALTED** 15. REGULATORY INFORMATION SARA Reporting 15.1 This product does not contain any substances subject to SARA Title III, Section 313 reporting requirements. Requirements SARA Threshold Planning 15.2 There are no specific Threshold Planning Quantities for the components of this product. Quantity: 15.3 TSCA Inventory Status: The components of this product are listed on the TSCA Inventory. 15.4 CERCLA Reportable Quantity NA (RQ): 15.5 Other Federal Requirements: NA 15.6 Other Canadian Regulations: This product has been classified according to the hazard criteria of the CPR and the SDS contains all of the information required by the CPR. The components of this product are listed on the DSL/NDSL. None of the components of this product are listed on the Priorities Substances List. WHMIS Class D2B (Other Toxic Effects). <u>Isopropanol</u> is listed on the following state criteria lists: Florida Toxic Substances List (FL), Massachusetts Hazardous 15.7 State Regulatory Information: Substances List (MA), New Jersey Right-to-Know List (NJ), Pennsylvania Right-to-Know List (PA), and Washington Permissible Exposures List (WA). No other ingredients in this product, present in a concentration of 1.0% or greater, are listed on any of the following state criteria lists: California Proposition 65 (CA65), Delaware Air Quality Management List (DE), Florida Toxic Substances List (FL), Massachusetts Hazardous Substances List (MA), Michigan Critical Substances List (MI), Minnesota Hazardous Substances List (MN), New Jersey Right-to-Know List (NJ), New York Hazardous Substances List (NY), Pennsylvania Right-to-Know List (PA), Washington Permissible Exposures List (WA), Wisconsin Hazardous Substances List (WI). Other Requirements: 15.8 This product does not contain any chemicals known to the State of California to cause cancer or other

reproductive harm. For more information go to www.P65Warnings.ca.gov



Page 5 of 6 SDS-E-CL-WBC

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, GHS & 1272/2008/EC Standards SDS Revision: 3.1 SDS Revision Date: 3/14/2018

		·		
	16. OTHER INFORMATION			
16.1	Other Information:	WARNING! CAUSES EYE IRRITATION. CAUSES MILD SKIN IRRIATION. Use only as directed. Wash thoroughly with soap and water after handling. IF ON SKIN: Wash with plenty of water. IF skin irritation occurs: Get medical advice/attention. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. KEEP LOCKED UP AND OUT OF REACH OF CHILDREN.		
16.2	Terms & Definitions:	See last page of this Safety Data Sheet.		
16.3	Disclaimer:	This Safety Data Sheet is offered pursuant to OSHA's Hazard Communication Standard, 29 CFR §1910.1200. Other government regulations must be reviewed for applicability to this product. To the best of ShipMate's & CAIG Laboratories, Inc.'s knowledge, the information contained herein is reliable and accurate as of this date; however, accuracy, suitability or completeness is not guaranteed and no warranties of any type, either expressed or implied, are provided. The information contained herein relates only to the specific product(s). If this product(s) is combined with other materials, all component properties must be considered. Data may be changed from time to time. Be sure to consult the latest edition.		
16.4	Prepared for:	CAIG Laboratories, Inc. 12200 Thatcher Court Poway, CA 92064-6876 Tel: +1 (800) CAIG-123 (244-4123) Fax: +1 (858) 486-8398 fax http://www.caig.com/		
16.5	Prepared by:	ShipMate, Inc. P.O. Box 787 Sisters, Oregon 97759-0787 USA Tel: +1 (310) 370-3600 Fax: +1 (310) 370-5700 http://www.shipmate.com		



Page 6 of 6 SDS-E-CL-WBC

Prepared to OSHA, ACC, ANSI, NOHSC, WHMIS, GHS & 1272/2008/EC Standards

SDS Revision: 3.1

SDS Revision Date: 3/14/2018

DEFINITION OF TERMS

A large number of abbreviations and acronyms appear on a SDS. Some of these that are commonly used include the following:

GENERAL INFORMATION:

CAS No.	CAS No. Chemical Abstract Service Number	
RTECS No. Registry of Toxic Effects of Chemical Substances Number		
EINECS No.	European Inventory of Existing Commercial Chemical Substances Number	

EXPOSURE LIMITS IN AIR:

ACGIH	American Conference on Governmental Industrial Hygienists	
IDLH	Immediately Dangerous to Life and Health	
NOHSC	ISC National Occupational Health and Safety Commission (Australia)	
OSHA	HA U.S. Occupational Safety and Health Administration	
PEL	Permissible Exposure Limit	
STEL	STEL Short Term Exposure Limit	
TLV	TLV Threshold Limit Value	
TWA	Time Weighted Average	

FIRST AID MEASURES:

CPR	Cardiopulmonary resuscitation - method in which a person whose heart has
	stopped receives manual chest compressions and breathing to circulate blood

HAZARDOUS MATERIALS IDENTIFICATION SYSTEM: HMIS


HEALTH, FLAMMABILITY & REACTIVITY RATINGS:

0	Minimal Hazard
1	Slight Hazard
2	Moderate Hazard
3	Severe Hazard
4	Extreme Hazard



PERSONAL PROTECTION RATINGS:

Α			
В			
С		THE STATE OF THE S	
D		THE STATE OF THE S	
Е			
F		THE SECOND	





OTHER STANDARD ABBREVIATIONS:

Carc	Carcinogenic
Irrit	Irritant
NA	Not Available
NR	No Results
ND	Not Determined
NE	Not Established
NF	Not Found
SCBA	Self-Contained Breathing Apparatus
Sens	Sensitization
STOT RE	Specific Target Organ Toxicity – Repeat Exposure
STOT SE	Specific Target Organ Toxicity – Single Exposure

NATIONAL FIRE PROTECTION ASSOCIATION: NFPA

FLAMMABILITY LIMITS IN AIR:		
Autoignition Temperature	Minimum temperature required to initiate combustion in air with no other source of ignition	
LEL	Lower Explosive Limit - lowest percent of vapor in air, by volume, that will explode or ignite in the presence of an ignition source	
UEL	Upper Explosive Limit - highest percent of vapor in air, by volume, that will explode or ignite in the presence of an ignition source	

HAZARD RATINGS:

0	Minimal Hazard	FLAMMABILITY
1	Slight Hazard	\
2	Moderate Hazard	REACTIVITY
3	Severe Hazard	
4	Extreme Hazard	
ACD	Acidic	
ALK	Alkaline	
COR	Corrosive	/ \ \ \ \
₩	Use No Water	HEALTH
ОХ	Oxidizer	SPECIAL
TREFOIL	Radioactive	PRECAUTIONS

TOXICOLOGICAL INFORMATION:

Lethal Dose (solids & liquids) which kills 50% of the exposed animals
Lethal concentration (gases) which kills 50% of the exposed animal
Concentration expressed in parts of material per million parts
Lowest dose to cause a symptom
Lowest concentration to cause a symptom
Lowest dose (or concentration) to cause lethal or toxic effects
International Agency for Research on Cancer
National Toxicology Program
Registry of Toxic Effects of Chemical Substances
Bioconcentration Factor
Median threshold limit
Coefficient of Oil/Water Distribution

REGULATORY INFORMATION:

WHMIS	Canadian Workplace Hazardous Material Information System	
DOT	U.S. Department of Transportation	
TC	Transport Canada	
EPA	U.S. Environmental Protection Agency	
DSL	Canadian Domestic Substance List	
NDSL	Canadian Non-Domestic Substance List	
PSL	Canadian Priority Substances List	
TSCA	U.S. Toxic Substance Control Act	
EU	EU European Union (European Union Directive 67/548/EEC)	
WGK	Wassergefährdungsklassen (German Water Hazard Class)	

WORKPLACE HAZARDOUS MATERIALS IDENTIFICATION (WHMIS) SYSTEM:

0	*	(2)		\odot	(4)		
Class A	Class B	Class C	Class D1	Class D2	Class D3	Class E	Class F
Compressed	Flammable	Oxidizing	Toxic	Irritation	Infectious	Corrosive	Reactive

CLP/GHS (1272/2008/EC) PICTOGRAMS:

	®		\Diamond	N. C.		\Diamond		*
GHS01	GHS02	GHS03	GHS04	GHS05	GHS06	GHS07	GHS08	GHS09
Explosive	Flammable	Oxidizer	Pressurized	Corrosive	Toxic	Harmful Irritating	Health Hazard	Environment