WISE-4610

LoRa Outdoor Wireless I/O Module



Features

- For North America, Europe, and Japan
- Longer communication range
- Better penetration through concrete and steel
- Less interference than 2.4GHz spectrum
- Application-ready I/O combination with IP65 enclosure
- Powered by solar rechargeable battery or 10~50V_{DC} input
- Global Positioning System (GPS) support



Introduction

LPWAN is a type of wireless telecommunication wide area network designed to allow long range communications at a low data rate among IoT applications, such as sensors operated on a battery. Its benefits is to offer multi-year battery lifetime for sensors/applications to send small amounts of data over long distances a few times per hour suitable for different environments.

LoRa and LoRaWAN are one of category of LPWAN which belong to the non-cellular LPWAN wireless communication network protocols enables very long range transmissions with low power consumption, operating in the non-licensed spectrum. What is the difference between LoRa and LoraWAN? LoRa (Long Range) is a patented wireless data communication of IoT technology and acquired by Semtech in 2012 which holds the IP for LoRa transmission methodology.










Star Topology

The LoRaWAN networks in a star topology have gateway relaying the data between the sensor nodes and the network server.

Communication between the sensor nodes and the gateway goes over the wireless channel utilizing the LoRa physical layer, whilst the connection between the gateways and the central server are handled over a backbone IP-based network.

The LoRaWAN end nodes(sensors) typically use Low Power and are battery powered (Class A and Class B). LoRa embedded sensors that run on batteries that lasts from 2–5 years typically. The LoRa sensors can transmit signals over distances from 1km—10km.





Common Specification

Wireless Communication

IEEE 802.15.4g EU 863-870 (MHz) ■ IEEE Standard Frequency Band US 902-928 (MHz) AU (JP) 915-928 (MHz)

Spreading Factor Outdoor Range 7~12

5km with line of sight (with 2 dBi Antenna) Transmit Power Up to +18dBm Up to -136dBm at SF = 12 / 125KHz **Receiver Sensitivity**

50 kbps at FSK mode EU868 21.9 kbps at SF7 mode US915 Data Rate 5.47 kbps at SF7 mode JP923

TopologyFunction End Node Function

GPS¹

GNSS Systems GPS, GLONASS, Galileo, BeiDou, QZSS and SBAS signals Max. Update Rate

Single GNSS: up to 18 Hz
Concurrent GNSS: up to 10 Hz
Position: 2.5 m CEP (50% confidence)
With SBAS: 2.0 m CEP (50% confidence) Accuracy

Acquisition Cold starts: 57 s Aided starts: 7 s

General

Built-in 4000mA Lithium rechargeable battery pack 2 or $10{\sim}50V_{\text{DC}}$ external power Power Input

6 months (1 hour data update and 1 day GPS update)

Configuration Interface Micro-B USB

Power: M12 4-pin code-A male x 1 I/O: M12 8-pin code-D female x 2 Connector LED Indicator Status, Error, Tx, Rx, Battery/Signal Level DIN 35 rail, wall, pole, and stack Mounting Dimension (W x H x D) 82 x 122 x 49 mm (without antenna)

Environment

 Operating Temperature² 0~60°C

No Battery Version: -20~70°C

Operating Humidity ¹ No GPS version, can be order by request

² No battery version, can be order by request

WISE-S672

Serial Port

Port Number Type Port 1: RS-485 Port 2: RS-485/232

RS-485: DATA+, DATA-RS-232: Tx, Rx, GND Serial Signal Data Bits 7, 8

Stop Bits Parity None, Odd, Even

Baud Rate (bps) 1200, 2400, 4800, 9600, 19200, 38400, 57600, 115200

Protection

Modbus/RTU (Total 32 address) Protocol

Digital Input

Channels

Dry Contact (Wet Contact by request) Input Type

0: Open Logic Level 1: Close to DCOM Isolation Voltage

Isolation Voltage 3,000V_{rms} Supports 200Hz Counter Input (16-bit + 1-bit overflow)

Keep/Discard Counter Value when Power-off

Supports 200Hz Frequency Input

Supports Inverted DI Status

WISE-4610-S614

Analog Input

Channels Resolution Sampling Rate 1Hz per channel Accuracy ±0.1% of FSR (Voltage) +0.2% of FSR (Current)

±5V, ±10V, 0~5V, 0~10V, 0~20mA, 4~20mA, ±20mA Input Range

 Input Impedance $> 2M \Omega$ (Voltage)

120 Ω (External resistor for current)

Isolation Voltage $3000 V_{\text{rms}}$ ±35 V_{DC} Over Voltage Protection Burn-out Detection Yes (4~20mA only)

Supports Data Scaling and Averaging

Digital Input

Channels **Input Type** Dry Contact (Wet Contact by request)


0: Open 1: Close to DCOM Logic Level 3,000V_{rms}

Isolation Voltage Supports 200Hz Counter Input (16-bit + 1-bit overflow)

Keep/Discard Counter Value when Power-off Supports 200Hz Frequency Input

Supports Inverted DI Status

Pin Assignment



	Model Name Pin Number	WISE-S672	WISE-S614
A	1	DI0	DI0
	2	DI1	DI1
	3	DI2	DI2
	4	DI3	DI3
	5	DI4	NC
	6	DI5	NC
	7	NC	NC
	8	DICOM	DI COM
В	1	DATA1-	IAO+
	2	DATA1+	IAO-
	3	TX	IA1+
	4	RX	IA1-
	5	DATA2-	IA2+
	6	DATA2+	IA2-
	7	NC	IA3+
	8	GND	IA3-
PWR	1	+VS	+VS
	2	-VS	-VS
	3	SP+	SP+
	4	SP-	SP-

Ordering Information

Wireless Sensor Node

LoRa Outdoor WSN with 6DI & 2COM - NA915 LoRa Outdoor WSN with 6DI & 2COM - EU868 WISE-4610-S672NA WISE-4610-S672EA WISE-4610-S672JA LoRa Outdoor WSN with 6DI & 2COM - JP923 WISE-4610-S614NA LoRa Outdoor WSN with 4AI & 4DI - NA915 LoRa Outdoor WSN with 4AI & 4DI - EU868 LoRa Outdoor WSN with 4AI & 4DI - JP923 WISE-4610-S614EA

