

KGF20N05D

N-Channel 5.5V Dual Power MOSFET

FN8963
Rev.0.00
Feb 1, 2018

The KGF20N05D is a dual 5.5V, 1.6mΩ, chip-scale, N-channel power MOSFET. The device uses technology that uniquely integrates low cost CMOS and WLCSP fabrication processes. The chip-scale package offers small area, low vertical profile, and is fully compatible with standard SMT assembly processes. The KGF20N05D offers unprecedented low ON-resistance and total gate charge, outperforming conventional trench MOSFETs and enabling high frequency, low voltage switching. The device offers extremely high power density, reducing the board size of DC/DC converters and other power management systems.

Features

- Industry leading figures of merit: $r_{DS(ON)} \times Q_g$ and $r_{DS(ON)} \times Q_{gd}$
- Low profile/small footprint chip-scale WLCSP package
- High frequency switching
- Known Good FET (KGF) quality assurance process
- Low thermal resistance

Applications

- Point-of-load DC/DC converters
- Portable electronics
- OR'ing diodes




Figure 1. Equivalent Circuit




Figure 2. WLCSP, Die Size 2.475mmx1.170mm

1. Overview

1.1 Ordering Information


Part Number (Notes 1, 2, 3)	Part Marking	Temp Range (°C)	Tape and Reel (Units)	Package (RoHS Compliant)
KGF20N05D	AO	-55°C to +150°C	4k	20 Bump WLCSP

Notes:

1. Refer to [TB347](#) for details about reel specifications.
2. For more information about MSL, refer to [TB363](#).
3. The part marking is located on the bottom of the part.

1.2 Pin Configuration

KGF20N05D
(20 Bump WLCSP)
Bottom View



1.3 Pin Descriptions

Pin Number	Pin Name	Description
1	G1	MOSFET 1 gate
2, 3, 4, 5	D1	MOSFET 1 drain
6, 7, 8, 9, 10, 11, 12, 13, 14, 15	S	Source of both MOSFETs
16, 17, 18, 19	D2	MOSFET 2 drain
20	G2	MOSFET 2 gate

2. Specifications

2.1 Absolute Maximum Ratings

$T_J = +25^\circ\text{C}$ unless otherwise noted.

Parameter	Minimum	Maximum	Unit
Drain-to-Source Voltage (V_{DS})		5.5	V
Gate-to-Source Voltage (V_{GS})		± 5.5	V
Drain Current ($I_{D1} + I_{D2}$)			
Continuous (I_D)		20	A
Pulsed (I_{DM})		40	A
Single Pulse Avalanche Current (I_{AS}), ($I_{D1} + I_{D2}$)			
$L \leq 50\mu\text{H}$, $R_G \leq 25\Omega$		10	A

CAUTION: Do not operate at or near the maximum ratings listed for extended periods of time. Exposure to such conditions may adversely impact product reliability and result in failures not covered by warranty.

2.2 Thermal Information

Thermal Resistance (Typical)	θ_{JA} ($^\circ\text{C}/\text{W}$)	θ_{JC} ($^\circ\text{C}/\text{W}$)
WLCSP Package (Note 4)	50	10

Note:

- When mounted on 1 inch square 2oz copper clad FR-4.

Parameter	Minimum	Maximum	Unit
Maximum Power Dissipation (P_D) (Note 4)			
$T_A = +25^\circ\text{C}$		2.5	W
$T_A = +70^\circ\text{C}$		1.6	W
Junction and Storage Temperature Range (T_J , T_{stg})	-55	+150	$^\circ\text{C}$
Pb-Free Reflow Profile	Refer to TB493		

2.3 Electrical Specifications

Specifications are for single MOSFET unless otherwise specified. $T_J = +25^\circ\text{C}$ unless otherwise noted

Parameter	Symbol	Test Condition	Min (Note 5)	Typ	Max (Note 5)	Units
Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0\text{ V}, I_D = 5\text{ mA}$	5.5			V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 4\text{ V}, V_{GS} = 0\text{ V}, T_J = +25^\circ\text{C}$			0.01	mA
		$V_{DS} = 5\text{ V}, V_{GS} = 0\text{ V}, T_J = +25^\circ\text{C}$			0.1	mA
		$V_{DS} = 5\text{ V}, V_{GS} = 0\text{ V}, T_J = +125^\circ\text{C}$			1	mA
Gate-Body Leakage	I_{GSS}	$V_{GS} = 5.5\text{ V}, V_{DS} = 0\text{ V}$			75	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = 250\mu\text{A}$	0.55	0.73	0.90	V
Drain-to-Source On-State Resistance (per MOSFET)	$r_{DS(ON)}$	$V_{GS} = 3.5\text{ V}, I_D = 10\text{ A}$		1.70		m Ω
		$V_{GS} = 4.5\text{ V}, I_D = 10\text{ A}$		1.60		m Ω
Drain-to-Source On-State Resistance (in Parallel)	$r_{DS(ON)}$	$V_{GS} = 3.5\text{ V}, I_D = 10\text{ A}$		0.85		m Ω
		$V_{GS} = 4.5\text{ V}, I_D = 10\text{ A}$		0.80		m Ω
Input Capacitance	C_{iss}	$V_{DS} = 5\text{ V}, V_{GS} = 0\text{ V}, f = 1\text{ MHz}$		865		pF
Output Capacitance	C_{oss}			270		pF
Reverse Transfer Capacitance	C_{rss}			1100		pF
Input Capacitance	C_{iss}	$V_{DS} = 0\text{ V}, V_{GS} = 0\text{ V}, f = 1\text{ MHz}$		890		pF
Output Capacitance	C_{oss}			295		pF
Reverse Transfer Capacitance	C_{rss}			1390		pF
Gate Resistance	R_g	$V_{DS} = 0\text{ V}, f = 1\text{ MHz}$		1.2		Ω
Total Gate Charge	Q_g	$V_{GS} = 3.5\text{ V}, I_D = 4\text{ A}, V_{DS} = 4\text{ V}$		5.3		nC
Gate-to-Source Charge	Q_{gs}			1.1		nC
Gate-to-Drain Charge	Q_{gd}			1.3		nC
Total Gate Charge	Q_g	$V_{GS} = 4.5\text{ V}, I_D = 4\text{ A}, V_{DS} = 4\text{ V}$		6.7		nC
Source-to-Drain Reverse Recovery Time	t_{rr}	$I_S = 10\text{ A}, di/dt = 33\text{ A}/\mu\text{s}$		69		ns
Diode Forward Voltage	V_{SD}	$I_S = 10\text{ A}, V_{GS} = 0\text{ V}$		0.7	1.0	V

Note:

- Compliance to datasheet limits is assured by one or more methods: production test, characterization, and/or design.

3. Typical Performance Curves




Figure 3. Output Characteristics




Figure 4. Transfer Characteristics




Figure 5. Drain-to-Source On-State Resistance vs Drain Current




Figure 6. Drain-to-Source On-State Resistance vs Junction Temperature




Figure 7. Drain-to-Source On-State Resistance vs Gate-to-Source Voltage




Figure 8. Gate Threshold Voltage vs Junction Temperature




Figure 9. Source-to-Drain Diode Forward Voltage




Figure 10. Drain-to-Source Breakdown Voltage vs Junction Temperature




Figure 11. Gate Charge




Figure 12. Capacitance




Figure 13. Maximum Rated Forward Biased Safe Operating Area (in Parallel)




Figure 14. Transient Thermal Response, Junction-to-Ambient (in Parallel)




Figure 15. Transient Thermal Response, Junction-to-Ball

4. Revision History

Rev.	Date	Description
0.00	Feb 1, 2018	Initial release.


5. Package Outline Drawing

Dimensional Outline and Pad Layout

Side View



Pad-up View



Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.

1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited

9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.

Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.

Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited

Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852 2886-9022

Renesas Electronics Taiwan Co., Ltd.

13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd.

80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.

Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.

No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.

17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338