# PRODUCT SPECIFICATION

PRODUCT NAME: FAN MOTOR

MODEL: 9GA0412P6G023

SPECIFICATION No.: S5269094

#### Signature

We would kindly like you to check all specifications, make your signature on one copy, and return it to us by  $\underline{14\text{-September-2019}}$  When you have corrections, please write them in red. If this is not returned by the due date, we will deliver the products following this product specification.



### Caution

- To ensure that this product is used safely, be sure that you read and understand the following precautions fully and use the product only as directed.
- Be sure to read the Safety Precautions carefully before installing, connecting, operating, maintaining, or inspecting this product. Follow all the precautions and directions given here.
- This product has been designed and manufactured for use as a device to be used in general industrial machinery, and may not be used as a standalone product.
- The product of our company (hereinafter called the product) falls into the category of the products specified in the Attached List 1, Item 16 (Class 84, Item 14) of the Export Trade Control Ordinance. To export the product as an individual part or to export a product into which the product is assembled, the "Informing Requirements" and "Objective Requirements" that the Ministry of Economy, Trade and Industry of Japan established based on the "Catchall Controls" must be studied for applicability. Accordingly, appropriate export formalities must be performed.
- When disposing the product, treat it as industrial waste. Please contact your local government office for further details about disposal.
- To prevent any possible bodily injury or damage to property or equipment, the following precautions for ensuring safety are displayed according to the following two ranks of importance:

$oldsymbol{\hat{I}}_{ ext{Danger}}$	Handling or using the product improperly and in disregard of the instructions with this mark may result in serious bodily injury or death.	
<b>A</b> Caution	Handling or using the product improperly and in disregard of the instructions with this	
	mark may result in bodily injury or physical damage.	

Note: Items marked 'Caution' might also result in serious bodily injury or death in some circumstances.

Always follow the instructions the same as for items marked 'Danger.'

# SANYO DENKI CO., LTD.

APPROVED BY	CHECKED BY	DESIGNED BY
August 14, 2019	August 14, 2019	August 07, 2019



## Safety Precautions (1/2)

### $\hat{\mathbb{T}}_{Danger}$

- When using the product in the following environments, use it at your own discretion only after deploying sufficient safety measures and making prior evaluations.
- Equipment such as medical equipment related to human life, facilities that have serious social and public effects, or
  environments with vibrations such as in-automobiles or ships.
- Ensure that wiring has been correctly done. Failure to do so may result in fire, burns, or electrical shock.
- If there are any grounding taps or wires, ground them securely. There is danger of electrical shock.
- Never use in explosive atmospheres, as doing so might result in fires, burns, or bodily injury.
- Do not operate the product when electronic components are exposed. There is danger of electric shock.
- Never allow any persons or objects to approach or come into contact with the rotor while in operation, as doing so might result in damage or personal injury.
- Turn off the power and stop using the product immediately if you notice any sparks, smoke, odd odors, sounds, or anything unusual during operation. There is danger of electrical shock, fires, or bodily injury.
- Never allow the product to fall, topple over, or otherwise be subjected to excessive shocks when moving it, as doing so
  might result in product breakdown or substandard operation.
- The product should be handled only by personnel with sufficient training and knowledge and under the responsibility of the end user
- Never attempt to disassemble, repair, or alter this product in any way, as doing so might result in electrical shock, fires, or bodily injury.

### **A**Caution

#### **Handling**

- Installation, placement, connections, wiring, or relocation of the product should be performed by knowledgeable or correctly licensed personnel. Never perform such work while the product is on, as this might lead to injury, electrical shock, burns, or fire.
- · Do not use the fan if it is not fixed, nor while held in hand.
- Never allow yourself to come into contact with the ends of wires or plugs when measuring insulation resistance or dielectric strength voltage. There is danger of electrical shock.
- Never attempt to disassemble or alter this product in any way. Doing so may invalidate any warranties concerning the
  functions or performance of the product, and may also result in fire, burns, bodily injury, or electrical shock.

#### Cautions for operation

- Give proper consideration to the device for its protection in case the fan stops during operation.
- Never use the product at voltages, temperatures, or any other settings which exceed those given in the product specifications. This might result in substandard operation, breakdown, fire, bodily injury, or electrical shock.
- The fan may fail to operate properly if there is insufficient power capacity, because a starting current several times larger than the rated current will flow at the moment voltage is supplied to the fan. Be sure to inquire about starting current levels for individual models.
- · Do not control the speed of the fan by changing power voltage using PWM. It may cause fan failure.
- Start all fans at the same time when two or more fans whose wind creates interference are installed in the device. If the fan is exposed to wind from other fans at startup, it may cause fan failure or the fan may not start up correctly.
- Never insert or remove any lead wires, plug cords, or connectors while the power is turned on. When inserting or removing plugs or connectors, always be sure to first check that the power has been turned off, and hold the fan frame of the plug or connector when doing so. Failure to do so might result in damage or electrical shock.
- Do not remove the lead wire of the fan from the frame hook. Doing so may scratch and damage the surface of the lead wire
- Do not remove the nameplate. There is danger of electrical shock or failure.
- Do not push the nameplate of the fan with strong force. The nameplate may break or come in contact with the shaft.
- · The product might become damaged if foreign objects or external forces interfere with normal fan operation.
- Do not implement ON-OFF on the negative power supply line. That might damage the fan.

## Safety Precautions (2/2)

### **A** Caution

#### Installation


- When fixing this product into place, be sure to take the product's weight, vibrations generated during operation, and all other relevant factors into consideration. Failure to do so may result in the product or its parts falling, resulting in bodily injury or device failure.
- Be sure to check the installation direction (i.e., the fan), as failing to do so might result in bodily injury or mechanical breakdown.
- To ensure that the product operates properly, allow spaces for ventilation and take necessary steps to prevent the entry of foreign objects. Failure to do so might result in bodily injury or mechanical breakdown.
- When fixing the fan with screws, ensure the screwing torque. If the screwing torque exceeds the recommended torque, the fan frame may be deformed or damaged. Use a ribbed frame when using through-screws to affix fans with plastic frames. To prevent loose screws, use plain washers or spring lock washers. For the screwing torque of each fan type, contact SANYO DENKI or a SANYO DENKI distributor.
- When fixing the fan with self-tapping screws, the fan frame may be damaged.
- When excessive shock is applied to the fan, the impeller may protrude from the surface of the fan frame. Make sure that the impeller does not touch covers, such as finger guards or mounting plates.
- Do not subject fans to excessive shock to avoid fan failure and performance deterioration.
- Pulling or pinching lead wires could result in damage to the wire; avoid placing excessive stress on wires. The device should be installed so that the lead wires do not come into contact with the rotor or blades. Failure to do so might result in damage or electrical shock.
- Take proper precautions against static electricity when making electrical connections. Failure to do so might cause the breakdown of the fan or device.
- Install a finger guard or other cover if there is any danger of fingers, hands, or objects coming into contact with the rotor or blades. Failure to do so might result in bodily injury or mechanical breakdown.
- Install finger guards, filters, and plates in the correct position while avoiding touching the rotor blade. Avoiding this will prevent device failure. Please use only genuine SANYO DENKI finger guards and filter kits.
- Make electrical connections properly. If not there is a possibility that the device might break, or that the product might malfunction, breakdown, or have degraded performance.

#### Operating environment

- Avoid using or storing the product in the following areas and environments. There is the possibility that a fire may
  occur, the product may malfunction, or its performance may deteriorate.
- Flammable or corrosive gas atmospheres, in places where water or oil splashes (not applicable to Splash Proof or Oil Proof Fans), in places where there is much dust or humidity, in places where condensation occurs, in places where the product is exposed to radioactive rays or is in direct sunlight, in places where a salty sea breeze blows or seawater splashes, or in an environment where the product may be contaminated by such corrosive materials as sulfurous water, sulfurous volcanic ash, organic solvents, acidic chemicals, alkali chemicals, etc., or such hazardous substances as nuclear fuel materials, etc.
- Avoid using or storing the product in the following areas and environments. Doing so might result in product breakdown or substandard operation.
- Environments where it could be constantly exposed to vibrations, strong shocks, centrifugal force, acceleration (excluding G Proof Fans) magnetic or electromagnetic noise, areas in which the electromagnetic noise overlaps into power voltage, or areas subjected to rapid environmental fluctuations (temperature, humidity, etc.)

#### Maintenance

- Maintenance and inspections should always be performed by personnel with sufficient training and knowledge.
   Otherwise, it may result in fire, burns, bodily injury, or electrical shock.
- Never perform any maintenance or inspections while the product is in operation. Also note that the blades continue to rotate for some time immediately after operation ceases. Always confirm that all rotating parts have come to a stop before beginning work. There is danger of electrical shock, fires, or bodily injury.
- Never use gasoline, paint thinner, benzene, or other organic solvents to clean the product, as this could result in deformation or substandard operation.



PWM DUTY CYCLE (BETWEEN CONTROL LEAD AND ⊝LEAD) - SPEED CHARACTERISTIC (REFERENCE) PWMデューティサイクル (コントロールー ○問) - 回転速度特性例 PWM INPUT SIGNAL PWM入力信号 FAN INPUT VOLTAGE: 12 V DC ファン入力電圧 : DC12 V PWM FREQUENCY: 25 kHz  $\times 100 = PWM DUTY CYCLE(%)$ PWMデューティサイクル (AT ROOM TEMPERATURE, NORMAL HUMIDITY) (常温、常湿にて) 16000 15000 T1 | T2 V<sub>IH</sub> 4.75V~5.25V V IL 0V~0.4V NOMINAL 10000 中心値 5000 3800 1 # sec MAX. 1 # sec MAX. 以下 以下 0 10 100 PWM DUTY CYCLE (%) CONNECTION PWM デューティサイクル NOTE: 注 FAN MOTOR INPUT\_VOLTAGE ⊕ DC FAN ファンモータ電源 DCファン内部 1. WHEN PWM DUTY CYCLE IS 100%, REFER TO PAGE 1 FOR THE SPEED. PWMデューティサイクルが 100%の時、回転速度は1頁を参照のこと。 2. WHEN PWM DUTY CYCLE IS 0%, REFER TO PAGE 1 FOR THE SPEED. PWMデューティサイクルが ○%の時、回転速度は1頁を参照のこと。  $_{\rm PWM~SIGNAL}~{\rm CTL}$ 3. WHEN THE CONTROL LEAD WIRE IS NOT CONNECTED. PWM信号 🛫 THE SPEED IS THE SAME SPEED AS AT 100% OF PWM DUTY CYCLE. PWM入力端子がオープン状態の時、回転速度はPWMデューティサイクル100%と 同じであること。 4. INPUT PWM FREQUENCY IS 25 kHz. 入力PWM周波数は、25 kHzであること。 5. THIS FAN SPEED SHOULD BE CONTROLLED BY PWM INPUT SIGNAL 承認 APPROVED BY 12 V PWM SIGNAL VARIABLE SPEED TE.YAMAZAKI OF EITHER TTL INPUT OR OPEN COLLECTOR, DRAIN INPUT. PWM信号 可変速ファン 19-08-14 AND IN CASE OF OPEN COLLECTOR, DRAIN INPUT, THE PWM DUTY 単位 UNIT 審査 CHECKED BY 名称 TITLE CYCLE SHOULD BE  $\frac{T-T2}{T} \times 100$ . TE.YAMAZAKI San Ace 40(9GA) m m 19-08-14 PWM入力信号はTTL入力又は、オープンコレクタ、ドレイン入力にて使用可能であること。 尺度 SCALE 設計 DESIGNED BY A |新規作成 N.QUIROZ | 19-08-07 N.QUIROZ 但し、オープンコレクタ、ドレイン入力の場合、 記号 記 事 DESCRIPTION サンエース40 9GAタイプ リブ付 日 付 DATE 19-08-07 SANYO DENKI 図番 DWG NO. PWM $\vec{r}_1 - \vec{r}_7 = \frac{T - T2}{T} \times 100$  oze. 山洋雷気株式会社 2019-08-17 SANYO DENKI CO., LTD. D12.E0 01035273.0002

┙

