# **Specification**

Drawing No.	TKY1D-H1-19557-00[44]	[1/9]
Issued Date.	Dec-11-2019	

# TO: Digi-Key

Note: In case of specification change, KYOCERA Part Number also will be changed.

Product Name	Crystal Oscillator
Product Model	
Frequency	**.*** MHz
Customer Part Number	
Customer Specification Number	
KYOCERA Part Number	KC2520Z**.****C1KX00
Remarks RoHS Compliant / MS	_1/

**Customer Acceptance** 

Accept Signature	Accept Date	
	Department	
	Person in charge	

Seller
KYOCERA Corporation
Corporate Electronic Components Group

Electronic Components Sales Division

6 Takeda Tobadono-cho, Fushimi-ku, Kyoto 612-8501 Japan

TEL. No. 075-604-3500 FAX. No. 075-604-3501

Manufacturer
KYOCERA Corporation
Corporate Electronic Components Group
Crystal Components Division
Yamagata higashine Plant
5850, Higashine-koh, Higashine-shi, Yamagata
999-3701 Japan
TEL. No. 0237-43-5611
FAX. No. 0237-43-5615

Design Department	Quality Assurance	Approved by	Checked by	Issued by	
KYOCERA Corporation Crystal Components Division	Y.Kakuta	Koyanagi	K.Jikhara	Y.Kato 藤	

Drawing No.

TKY1D-H2-19557-00[44] [2/9]

# **Revision History**

Rev. No.	Description of revise	Date	Approved by	Checked by	Issued by
00	First Edition	Dec-11-2019	T.Koyanagi	K.Jikuhara	Y.Kato
			0		
	~46)				

Drawing No. TKY1D-H2-19557-00[44] [3/9]

## 1. Scope

This specification shall be defined of the Clock Oscillator for the integrated circuits (ICs).

#### 2. Customer Part Number

#### 3. KYOCERA Part Number

## KC2520Z\*\*.\*\*\*\*C1KX00

#### 4. Electrical Characteristics

#### 4-1. Absolute Maximum Rating

Item	Symbol	Rated Value	Units
Power Supply Voltage	$V_{CC}$	-0.3 to +4.5	V
Input Voltage	V <sub>IN</sub>	-0.3 to V <sub>CC</sub> +0.3	V
Storage Temperature	T <sub>STG</sub>	-55 to +150	°C

#### Note:

If the part is used beyond absolute maximum ratings, it may cause internal destruction. The part should be used under the recommended operating conditions the reliability of this part may be damaged if those conditions are exceeded.

# 4-2. Recommended Operating Conditions

Item	Symbol	Min	Тур	Max	Units	Remarks
Power Supply Voltage	V <sub>cc</sub>	1.71	3.3	3.63	V	
Input Voltage	$V_{IN}$	0		$V_{CC}$	V	
Operating Temperature	T <sub>OPR</sub>	-40	+25	+85	°C	

#### 4-3. Electrical Characteristics

Item	Symbol	Min	Тур	Max	Units	Remarks
Output Frequency	Fo	0.5	** ****	170	MHz	
Frequency Tolerance*	F_tol	-20		+20	ppm	
				5.2		0.5≤ f <sub>0</sub> <5MHz
				5.8		5≤ f <sub>0</sub> <15MHz
				6.2		15≤ f <sub>O</sub> <30MHz
Current Consumption				6.8		30≤ f <sub>O</sub> <50MHz
				6.8		50≤ f <sub>O</sub> ≤60MHz
(No Load/ 1.71≤V <sub>CC</sub> ≤2.25V)				9		60< f <sub>0</sub> <75MHz
(NO LOAG/ 1.713VCC32.23V)		-		10		75≤ f <sub>O</sub> <105MHz
				10.5		105≤ f <sub>0</sub> <130MHz
				11.5		130≤ f <sub>O</sub> <160MHz
				12.5		160≤ f <sub>0</sub> ≤170MHz
				5.5		0.5≤ f <sub>o</sub> <5MHz
				6		5≤ f <sub>0</sub> <15MHz
	lcc			6.5		15≤ f <sub>O</sub> <30MHz
		-		7.2		30≤ f <sub>0</sub> <50MHz
Current Consumption				7.4	Л	50≤ f <sub>0</sub> ≤60MHz
(No Load/ 2.25 <v<sub>CC≤2.8V)</v<sub>				10	mA	60< f <sub>0</sub> <75MHz
				11.5		75≤ f <sub>O</sub> <105MHz
				12.5		105≤ f <sub>O</sub> <130MHz
				14		130≤ f <sub>O</sub> <160MHz
				15		160≤ f <sub>O</sub> ≤170MHz
				5.8		0.5≤ f <sub>o</sub> <5MHz
				6.5		5≤ f <sub>0</sub> <15MHz
				7.3		15≤ f <sub>O</sub> <30MHz
				8		30≤ f <sub>O</sub> <50MHz
Current Consumption				8.5		50≤ f <sub>O</sub> ≤60MHz
(No Load/ 2.8 <v<sub>CC≤3.63V)</v<sub>				12.5		60< f <sub>0</sub> <75MHz
				14.5		75≤ f <sub>0</sub> <105MHz
				15.5		105≤ f <sub>O</sub> <130MHz
				18		130≤ f <sub>O</sub> <160MHz
				19.5		160≤ f <sub>0</sub> ≤170MHz
Standby Current	I <sub>ST</sub>			5	μA	
Symmetry (Duty Ratio)	SYM	45	50	55	%	@ 50% V <sub>CC</sub>

Drawing No. T	KY1D-H2-19557-00[44] [4/9]
---------------	----------------------------

Item	Symbol	Min	Тур	Max	Units	Ren	narks	
				4			1.71≤V <sub>CC</sub> ≤2.25V	
				3		0.5≤ f <sub>O</sub> ≤60MHz	2.25 <v<sub>CC≤2.8V</v<sub>	
Rise Time/ Fall Time	T., / T.			2.5			2.8 <v<sub>CC≤3.63V</v<sub>	
(20% $V_{CC}$ to 80% $V_{CC}$ ) Loaded	Tr/ Tf			1.5	ns		1.71≤V <sub>CC</sub> ≤2.25V	
Loaded				1.3		60< f <sub>0</sub> ≤170MHz	2.25 <v<sub>CC≤2.8V</v<sub>	
				1			2.8 <v<sub>CC≤3.63V</v<sub>	
Output Voltage-"L"	V <sub>OL</sub>			10% V <sub>CC</sub>	V	I <sub>OL</sub> = 4mA		
Output Voltage-"H"	V <sub>OH</sub>	90% V <sub>CC</sub>			V	I <sub>OH</sub> =-4mA		
Output Load	CL			15	pF	CMOS		
Input Voltage-"L"	$V_{IL}$			30% V <sub>CC</sub>	V			
Input Voltage-"H"	$V_{IH}$	70% V <sub>CC</sub>			V			
Output Disable Time	t_dis			200	ns			
Output Enable Time	t_ena			5	ms			
Start-up Time	t_sta			5	ms	@Minimum operating	voltage to be 0sec	
				14		10≤ f0 <25MHz		
				12		25≤ f0 <50MHz		
1 Sigma Jitter**	$J_{Sigma}$			10	ps	50≤ f0 <75MHz		
	•			14		75≤ f0 <125MHz		
				18		125≤ f0 ≤170MHz		
	J <sub>PK-PK</sub>			110	μS	10≤ f0 <25MHz		
				95		25≤ f0 <50MHz		
Peak to Peak Jitter**				80		50≤ f0 <75MHz		
				75		75≤ f0 <125MHz		
				100		125≤ f0 ≤170MHz		
				33		10≤ f0 <25MHz		
				36		25≤ f0 <50MHz		
				45		50≤ f0 <75MHz	V <sub>CC</sub> =1.8V	
				55		75≤ f0 <125MHz	V <sub>CC</sub> =1.6V	
				60		125≤ f0 <150MHz		
				48		150≤ f0 ≤170MHz		
				33		10≤ f0 <25MHz		
				36		25≤ f0 <50MHz		
			A	45		50≤ f0 <75MHz		
Phase Jitter (BW:12kHz to 20MHz)		<u> </u>	7	53	ps	75≤ f0 <125MHz	V <sub>CC</sub> =2.5V	
(DVV.12KI IZ (O 20IVII IZ)				57		125≤ f0 <150MHz		
				48		150≤ f0 ≤170MHz		
				33		10≤ f0 <25MHz		
				36	-	25≤ f0 <50MHz		
				43		50≤ f0 <75MHz	┪	
				49	-	75≤ f0 <125MHz	V <sub>CC</sub> =3.3V	
				52		125≤ f0 <150MHz		
				44	1	150≤ f0 ≤170MHz		
							1	

Table 1

Note: All electrical characteristics have defined on the maximum loaded and recommended operating conditions.

\* Include initial tolerance, operating temperature range, rated power supply voltage change, load change, aging (1year @+25°C), shock and vibration

\*\*Based on Time Interval Analyzer "Wavecrest SIA-3000".

Drawing No. TKY1D-H2-19557-00[44] [5/9]

#### 4-4. Measurement Condition


The reference temperature shall be +25±2°C. The measurement shall be performed at the temperature range of +5 °C to +35 °C unless otherwise the result is doubtful.

#### 4-5. Measurement Circuit

The electrical characteristics shall be measured by test circuit "Fig. 1". Also jitter shall be measured by test circuit "Fig. 3".

#### 4-6. Clock Timing Chart


The clock timing chart is "Fig. 2".



Note: CL includes probe and test fixture capacitance

Fig.1 Test Circuits

Fig.2 Clock Timing Chart (C-MOS Output)




<Measurement Conditions>

- Time Interval Analyzer
  - WaveCrest SIA-3000
  - DTS timer calibration
  - Over 30 minutes warm-up
  - > Extend 30 minutes calibration
  - Jitter histogram conditions (Tail-fit)
    - ➤ More than 50,000cyc Hits
    - Bit Error Ratio (BER) –12 (14sigma)

Fig.3 Jitter Test Circuits

#### 5. Dimensions and Marking



XXXXXX Serial Code

K XX P01 Manufacturing Date Code
Internal Code

Manufacturing Date Code

1) Year Code (2000: "Z", 2001:"A", 2002: "B" ....)

2) Weekly Code

Table 2

Drawing No. TKY1D-H2-19557-00[44] [6/9]

# 6. Parts Numbering Guide

# KC2520Z \*\*.\*\*\* C 1 K X 00 G

A. Series (SMD Oscillator)

B. Output Frequency(MHz)

C. Output C: C-MOS

D. Supply Voltage1: 1.8V/ 2.5V/ 3.3V Compatible

E. Frequency Tolerance\* K:±20ppm F. Symmetry (Duty Ratio) and Enable/Disable Function X: Symmetry: 45% to 55% with Stand-by Function

G. Suffix for Individual Requirements (STD Specification is "00")

Packing (Tape & Reel 2,000pcs/Reel)

\*Over All Conditions:

Include initial tolerance, operating temperature range, rated power supply voltage change, load change, aging (1year @+25°C), shock and vibration.

Ex.

#### 7. Environmental Characteristics


Items	Conditions	Criteria of Acceptance
7-1. Solderability	Soaking: +245±5°C, 5.0±0.5sec	Dipped potion: Minimum 95% coverage
7-2. Soldering Heat Resistance	Reflow soldering: Peak +260°C max, 10sec, Twice max	Without looseness or crack etc.
7-3. Temperature Cycle	10 cycles: -55°C to +125°C (30minuts each/ cycle)	
7-4. Mechanical Shock (Pulse)	5 times 14,750m/sec <sup>2</sup> (1,500G), Duration of pulse 0.5msec (MIL-STD-883D-2002.3 Condition B)	
7-5. Vibration	4 times each axis X, Y, Z: 20 to 2,000Hz and 2,000Hz to 20Hz/cycle Peak acceleration 196m/sec <sup>2</sup> (20G) (MIL-STD-883D-2007.2 Condition A)	Clause 7-10 shall be satisfied.
7-6. High Temperature	1000 hours: Temperature: +85+5/-3°C	
7-7. Low Temperature	1000 hours: Temperature: -40+5/-3°C	
7-8. Humidity Cycle	10 cycles: Based on 1004 specifications (MIL-STD-883D-1004.7)	Clause 7-1 shall be satisfied.
7-9. Hermeticity 1 (Gross leak)	Soaking: +125°C, 5minutes	No bubbles appeared
7-10. Hermeticity 2 (Fine leak)	Measured by Helium Detector Equipment (MIL-STD-883D-1014.10 Condition A1)	5x10 <sup>-9</sup> Pa m <sup>3</sup> /sec max

After each testing, the parts shall be subjected to standard atmospheric conditions more than 2 hours. After that, the electrical characteristics shall be measured. The result of the test shall be satisfied **Table 1**.

Table 3

## Drawing No.

# 8. Recommended Land pattern and Soldering Guide



Note: Since the part doesn't have Bypass Capacitor between  $V_{\rm cc}$  and GND, Please mount high frequency type capacitor  $0.01\mu F$  to the nearest position of oscillator.


Fig.4 Land pattern

#### 10sec max Peak +260 °C max +255±5 ℃ 250 +230 °C Temperature (°C) 200 +150 to +180 °C 150 100 .30 to 40sec 90 to 120 sec. Time (sec)

Available Reflow times: Maximum twice

Fig.5 Reflow profile (Lead Free Available)


# 9. Taping Specifications



Unit: (mm)

				_	
Symbol	$A_0$	$B_0$	W	F	E
Dimensions	2.2±0.1	2.7±0.1	8.0±0.2	3.5±0.05	1.75±0.1
Symbol	$P_1$	P <sub>2</sub>	P <sub>0</sub>	$D_0$	T
Dimensions	4.0±0.1	2.0±0.05	4.0±0.1	1.5+0.1/-0	0.2±0.05
Symbol	K	$D_1$			
Dimensions	1.0±0.1	1.1±0.1			

Fig.6 Emboss Carrier Tape



Std. Max 2,000pcs/Reel

Unit: (mm)

Symbol	Α	N	$W_1$
Dimensions	180 +0/-1.5	60+1/-0	9.0+0.3/-0
Symbol	$W_2$	С	d
Dimensions	11.4±1.0	13.0±0.2	21.0±0.8
Symbol	E		
Dimensions	2.0±0.5		

Option Max 15,000pcs/Reel Unit: (mm)				
Symbol	Α	N	<b>W</b> <sub>1</sub>	
Dimensions	330 +0/-2	100+1/-1	9.4+1/-0.5	
Symbol	$W_2$	С	D	
Dimensions		13.0±0.2	21.0±0.8	
Symbol	E			
Dimensions	2.0±0.5			

Fig.7 Reel


## 9-1. Taping Quantities

- The taping of per reel shall be packed 2,000 pcs.
- The parts shall be contained continuously in the pocket.

Drawing No.	TKY1D-H2-19557-00[44] [8/9]	
-------------	-----------------------------	--

#### 9-2. Leader and Blank Pockets

- The package shall be consisted of leader, blank pockets and loaded pocket as follows "Fig. 8".
- The power of peeling strength between top tape and carrier tape shall be 0.1N(10gf) to 0.7N(70gf) as follows "Fig. 9".



- Load Pocket
- Blank Pocket (160mm minimum)

#### Fig.8 Packing Method

Fig.9 Peeling Strength

#### 9-3. Reel Label

The reel label shall be consisted as below. (Based on EIAJ C-3 format)

- A) Customer Part Number
- Lot No.
- C) Quantities

D) Shipping Date Vender Name

#### 9-4. Exterior Package Label

The oscillator shall be packed properly to avoid defect in transportation. The exterior package label shall be consisted as below.

- A) Name of Customer
- P/O No.
- **Customer Part Number**
- D) Lot No.

- E) Quantities
- Shipping Date
- G) Vender Name

## 10. Production

· KYOCERA Corporation Yamagata Higashine Plant 5850 Higashine-koh ohaza Higashine-shi Yamagata 999-3701, Japan

## 11. The agreement of this specifications

In case there is any obscure point or doubt concerning the contents of the specification, it shall be settled through consultation of both parties.

Drawing No. TKY1D-H2-19557-00[44] [9/9]

#### 12. Remarks on Usages

# A) Storage Conditions

The parts shall be stored in temperature range of -5 to +40°C, humidity 40 to 60% RH, and avoid direct sunlight. Then the parts shall be used within 6 months.

#### B) Handling Conditions

Although the part has protection circuit against static electricity, when excess static electricity is applied, the inside IC may get damaged.

Before mounting on the PCB, please make sure the direction of the part is correct. Otherwise the part of temperature will increase. And also the part will have some damages.

Please do not use the parts under the unfavorable condition such as beyond specified range in this specification.

Please do not use the parts under the condition, in the water or in the salt water also environment of dew or harmful gas.

Frequency drift may occur as a result of application of light such as direct sunlight or LED light etc when operating this oscillator.

Please use in a design and environment that consider light shielding.

Note the frequency drift will not occur if used in a light-shielded environment.

Please make sure the condition of pick and place following pick up nozzle guideline.

Picking Method: Case of Head Unit 1.6 x 1.2mm (Inside Diameter)

The proper condition of pick and place will be different each equipment. Therefore, please check before testing.

C) Rework Condition

Please do not pick up Head Unit. We can't guaranty electrical performance and reliability.

D) Soldering Conditions

This product can respond to the general Pb-free reflow profile. The wave soldering cannot be supported.

E) Soldering in Mounting

In case of Solder paste and conductive glue contact product lid or product side face exception for product terminal it's possible to influence product characteristics.

Please be careful above contents.

F) Washing Conditions

Ultra sonic cleaning is available. However there is a possibility that Crystal in the part may cause damaged under certain condition. Therefore please test before using.

After washing, please dry the parts completely. Otherwise water drops between the parts and PCB may cause migration.

In case of using this part without above precaution, Kyocera is unable to guarantee the specific characteristics.