

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY							
REV	DESCRIPTION	DATE	APPROVED				
-	DCN 43148	02/17	MAL				





MATERIAL:

STAINLESS STEEL PER AMS-5640, ALLOY UNS S30300, TYPE 1 BODY:

CONTACT: BERYLLIUM COPPER PER ASTM B196,

ALLOY No. UNS C17300, TD04

TERMINAL: BRASS PER ASTM B16, ALLOY UNS No. C36000

INSULATORS: PTFE PER ASTM D1710, TYPE I, GRADE 1, CLASS B

FINISH:

BODY, CONTACT &

TERMINAL:

GOLD PER ASTM B 488, TYPE II, CODE C, CLASS .76, OVER NICKEL PER AMS-QQ-N-290, CLASS 1, .00010" MIN.

PERFORMANCE:

IMPEDANCE: 50 OHMS

FREQ. RANGE: DC TO 12.4 GHz

NOTES:

- 1. TO BE TIN DIPPED USING Sn96 SOLDER
- 2. ALL DIMENSIONS APPLY PRIOR TO SOLDER DIPPING

SEE NOTES FINISH: SEE NOTES SURFACE AREA: N/A		DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X* ±1*0' X*X' ±15' DECIMAL: X ±.030	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS] 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63 , MIL-STD-10. 6) DIA: S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS			SV Mic. 2400 Centrep West Pa		
						PROPRIETARY		FER AGINE 114.5W - 1994
THE INFORMATION CONTAINED IN THIS	PROPERTY OF SV MICROWAVE, INC. JCTION IN PART OR AS A WHOLE WRITTEN PERMISSION OF	THIRD ANGLE PROJECTION	DRAWN:	VB	02/28/17	0175	CAGE CODE	DWO I
ANY REPRODUCTION IN PART OR AS A WITHOUT THE WRITTEN PERMISSION OF		+	CHECKED:	MAL	02/28/17	SIZE B	95077	DWG. I
SV MICROWAVE, INC IS PROHIBITED.			APPROVED:	MAL	02/28/17	S	CALE: 4:1	

crowave, Inc.

epark West Drive, Suite 100 Palm Beach, FL 33409

/A JACK FOR CIRCUIT BOARD

2986-6001-TD