Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



9534 Multi-Conductor - Computer Cable for EIA RS-232 Applications



For more Information please call

1-800-Belden1



Description:

24 AWG stranded (7x32) tinned copper conductors, conductors cabled, PVC insulation, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
4	24	7x32	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)		
PVC - Polyvinyl Chloride	.010		

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Outer Shield Material	Coverage (%)
Beldfoil®	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	7x32	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.032

Overall Cable

Overall Cabling Lay Length & Direction:



Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red
4	Green

Overall Nominal Diameter: 0.184 in.

Mechanical Characteristics (Overall) Operating Temperature Range: -30°C To +80°C UL Temperature Rating: 80°C (UL AWM Style 2464) Bulk Cable Weight: 20 lbs/1000 ft. Max. Recommended Pulling Tension: 22 lbs. Min. Bend Radius (Install)/Minor Axis: 1.750 in.

Page 1 of 3 02-24-2012

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



9534 Multi-Conductor - Computer Cable for EIA RS-232 Applications

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
. , ,	
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2464 (300 V 80°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flai

C(UL) Flame Test: FT4

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

Max. Operating Voltage - UL:

Voltage 300 V RMS (UL AWM Style 2464)

Max. Recommended Current:

1.75 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9534 060U1000	1,000 FT	21.000 LB	CHROME		4 #24 PVC FS PVC
9534 060U500	500 FT	11.000 LB	CHROME		4 #24 PVC FS PVC
9534 060100	100 FT	2.700 LB	CHROME		4 #24 PVC FS PVC
9534 0601000	1,000 FT	22.000 LB	CHROME	С	4 #24 PVC FS PVC
9534 060500	500 FT	11.500 LB	CHROME	С	4 #24 PVC FS PVC
9534 0605000	5,000 FT	100.000 LB	CHROME		4 #24 PVC FS PVC

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



9534 Multi-Conductor - Computer Cable for EIA RS-232 Applications

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 02-16-2010

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.