1A, 400V - 1000V Surface Mount Rectifier

FEATURES

- Glass passivated junction chip
- Ideal for automated placement
- Low forward voltage drop
- High surge current capability
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- High frequency rectification
- Freewheeling application
- Switching mode converters and inverters in computer and telecommunication.

MECHANICAL DATA

- Case: SOD-123FL
- Molding compound meets UL 94 V-0 flammability rating
- Moisture sensitivity level: level 1, per J-STD-020
- Packing code with suffix "G" means green compound (halogen-free)
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 1A whisker test
- Polarity: As marked
- Weight: 16 mg (approximately)

KEY PARAMETERS		
PARAMETER	**VALUE**	**UNIT**
$I_{F(AV)}$	1	A
V_{RRM}	400 - 1000	V
I_{FSM}	30	A
$T_{J\ MAX}$	150	°C
Package	SOD-123FL	
Configuration	Single dice	

Pb-Free RoHS COMPLIANT HALOGEN FREE

SOD-123FL

ABSOLUTE MAXIMUM RATINGS (T_A = 25°C unless otherwise noted)					
PARAMETER	**SYMBOL**	**S1GFL**	**S1JFL**	**S1MFL**	**UNIT**
Marking code on the device		SGF	SJF	SMF	
Repetitive peak reverse voltage	V_{RRM}	400	600	1000	V
Reverse voltage, total rms value	V_{RMS}	280	420	700	V
Maximum DC blocking voltage	V_{DC}	400	600	1000	
Forward current	$I_{F(AV)}$	1			A
Surge peak forward current, 8.3 ms single half sine-wave superimposed on rated load per diode	I_{FSM}	30			A
Junction temperature	T_J	- 55 to +150			°C
Storage temperature	T_{STG}	- 55 to +150			°C

THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP	UNIT
Junction to Lead Thermal Resistance	$R_{\Theta JL}$	25	°C/W
Junction to Ambient Thermal Resistance	$R_{\Theta JA}$	85	°C/W

ELECTRICAL SPECIFICATIONS (T_A = 25°C unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage (1)	I_F = 1A, T_J = 25°C	V_F	-	1.1	V
Reverse current @ rated V_R per diode (2)	T_J = 25°C	I_R	-	1	μA
	T_J = 125°C		-	50	μA
Junction capacitance	1 MHz, V_R=4V	C_J	7	-	pF

Notes:

1. Pulse test with PW=0.3 ms
2. Pulse test with PW=30 ms

ORDERING INFORMATION

PART NO.	PACKING CODE	PACKING CODE SUFFIX	PACKAGE	PACKING
S1xFL (Note1, 2)	RV	G	SOD-123FL	3,000 / 7" Plastic reel
	RQ		SOD-123FL	10,000 / 13" Paper reel

Notes:

1. "x" defines voltage from 400V (S1GFL) to 1000V (S1MFL)
2. Whole series with green compound

EXAMPLE

EXAMPLE P/N	PART NO.	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION
S1MFL RVG	S1MFL	RV	G	Green compound

CHARACTERISTICS CURVES

(T_A = 25°C unless otherwise noted)

Fig.1 Forward Current Derating Curve



Fig.2 Typical Junction Capacitance



Fig.3 Typical Reverse Characteristics



Fig.4 Typical Forward Characteristics



CHARACTERISTICS CURVES

(T_A = 25°C unless otherwise noted)

Fig.5 Maximum Non-repetitive Forward Surge Current



Fig.6 Reverse Recovery Time Characteristic And Test Circuit Diagram



PACKAGE OUTLINE DIMENSIONS

SOD-123FL



DIM.	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	0.80	1.15	0.031	0.045
B	1.70	2.10	0.067	0.083
C	2.60	3.10	0.102	0.122
D	0.88	1.35	0.035	0.053
E	0.10	0.30	0.004	0.012
F	0.30	0.90	0.012	0.035
G	3.45	3.95	0.136	0.156

MARKING DIAGRAM

P/N = Marking Code
YW = Date Code
F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.