
# Waterproof Bayonet Lock Connector for 50A Power Supply

# **EM-W Series**





### ■Features

## 1. High current 4 position connector (Three-phase power source + ground)

Compatible with 50A current 3-position connectors and cables. (For the relationship between ambient temperature and current, see the derating curve shown in Fig.2)

### 2. Easy crimp termination

Crimp contact is user-friendly and the easy-to-assemble design allows for uniform termination.

#### 3. Uses a standard crimp tool

The crimp contacts can be terminated by using the JIS C 9711-compliant crimp tool.

#### 4. Sequential ground contact

Sequential mating allows the ground contact to mate first. The ground contact touches the metal shell. (Receptacle)

#### 5. Quick and secure bayonet lock


Easy to operate One-touch Bayonet lock.

#### 6. Waterproof design

IP68 compliant water resistance in mated condition IP68: No water intrusion while submerged in 2m water depth for 14 days in mated condition

#### 7. Safety Standard

TÜV certified



#### Measurement Condition:

3 contacts connected in series with 8mm² wire. Measurement performed with the plug sealed for air tightness (waterproofness).

Comment: 50A current rating assumes the connector is used at maximum of 85°C ambient temperature. The actual current used should be determined individually based on the derating curve. The derating curve is not guaranteed and will change dependent on factors such as the cable used. The values in this diagram are not guaranteed, but should be used as reference values. Actual measurement may vary even when all the measurements are done under the same conditions.

Fig.2

## ■Product Specifications

Datina	Rated current	50A (See the Derating Curve on page 1.)	Operating temperature range	-40 to +125℃
Ratings	Rated voltage	AC 250V, DC 250V	Storage temperature range	-10 to +60℃

Item	Specifications	Conditions	
Contact resistance	1mΩ max.	Measured at DC 1A	
2. Insulation resistance	5000MΩ min.	Measured at DC 500V	
3. Withstanding voltage	No flashover or breakdown	Apply AC 2210V for 1 minute.	
4. Vibration resistance	No electrical discontinuity of 10 $\mu$ s or more	10 to 50 to 10Hz/cycle, half amplitude of 0.75mm, 5 minutes/cycle, 10 cycles in each of the three axial directions	
5. Shock resistance	No electrical discontinuity of 10 $\mu$ s or more	Acceleration: 490m/s², duration: 11ms, 3 directions, 3 cycles for each	
6. Mechanical operation	Contact resistance : 1mΩ max.	500 times	
7. Temperature cycles	Insulation resistance : 5000MΩ min.	-55°C: 30 minutes→Room temperature: 2 to 3 minutes→+125°C 30 minutes→Room temperature: 2 to 3 minutes, 5 cycles	
8. Humidity resistance (Steady state)	Insulation resistance : 50MΩ min. (at high humidity) 500MΩ min. (dry environment)	Left at a temperature of 40°C and in humidity of 90 to 95% for 96 hours.	
9. Waterproofness	No water intrusion inside connector	Submerged in 1.8m water depth for 48 days in mated condition.	

# **■**Materials / Finish

Item	Materials	Finish	Remarks
Outer shell	Aluminum alloy	Nickel plated	
Insulator	PBT resin		UL94V-0
Contact	Copper alloy	Tin plated (over nickel under plating)	
Waterproof packing	Silicon rubber		

### ■Product Number Structure

Refer to the chart below when determining the product specifications from the product number. Please select from the product numbers listed in this catalog when placing orders.

### **●**Connector


#### ●Code clamp

#### ●Crimp contact

Series name : EM	Specifications : When different types of
2 Shell size: 35	specifications are provided, attach
Specialty : W=Waterproof	(01), (02), for identification.
Lock mechanism : B=Bayonet lock	Applicable cable diameter
6 Connector type : P=Plug	Contact shape : 1=Loose piece contact
R=Receptacle	Change in shape/gender:
CC=Code clamp	When contacts of the same size vary in shape/
6 Number of contacts: 4	gender, discriminate them by attaching a serial
Discrimination between contacts : S=Female contact	number (1, 2, 3,) to each.
P=Male contact	Plating : 3=Tin plated
Termination method : C=Crimp	


# **■Plug**






Part No.	HRS No.
EM35WBP-4SC	138-0008-3
EM35WBP-4PC	138-0013-3

# **■**Receptacle





36.5±0.


Diagram indicating panel mounting slot dimension

36.5±0.1 4×M3×0.5

Part No.	HRS No.	Α
EM35WBR-4PC	138-0009-6	61.4
EM35WBR-4SC	138-0014-6	55.8

# **■**Code clamp






Part No.	HRS No.	φA	Applicable cable diameter
EM35WCC-23	138-0007-0	23	φ23±0.5

## Crimp contact

#### ●Male contact






Туре	Part No.	HRS No.	Applicable wire size	Remarks
EM-PC-113(01) 138-0011-8 01		138-0011-8 01	<ul> <li>(1) Conductor area: 5.26 to 5.57mm² (10 AWG equivalent)</li> <li>(2) Conductor outer dia.: Maximum of φ3.1</li> <li>(3) Coating outer dia.: Maximum of φ8.7 (Applicable wire size shall satisfy all of conditions (1) to (3).)</li> </ul>	Retainer : Black
piece contacts	EM-PC-133	138-0019-0	<ul> <li>(1) Conductor area: 8mm²</li> <li>(2) Conductor outer dia.: Maximum of φ3.7</li> <li>(3) Coating outer dia.: Maximum of φ8.7 (Applicable wire size shall satisfy all of conditions (1) to (3).)</li> </ul>	Retainer : White

Note: This product is sold per packages (4 pcs).

#### Female contact





Type	Part No.	HRS No.	Applicable wire size Rema	
Loose	EM-SC-113(01)	138-0010-5 01	<ul> <li>(1) Conductor area: 5.26 to 5.57mm² (10 AWG equivalent)</li> <li>(2) Conductor outer dia.: Maximum of φ3.1</li> <li>(3) Coating outer dia.: Maximum of φ8.7 (Applicable wire size shall satisfy all of conditions (1) to (3).)</li> </ul>	Retainer : Black
piece contacts	EM-SC-133	138-0018-7	<ul> <li>(1) Conductor area: 8mm²</li> <li>(2) Conductor outer dia.: Maximum of φ3.7</li> <li>(3) Coating outer dia.: Maximum of φ8.7 (Applicable wire size shall satisfy all of conditions (1) to (3).)</li> </ul>	Retainer : White

Note: This product is sold per packages (4 pcs).

## **♦**Tool

Туре	Part No.	HRS No.	Applicable contact
Manual crimp tools	Note 1		EM-PC-133, EM-SC-133, EM-PC-113(01), EM-SC-113(01)
Contact removal tool	EM-8-TP	150-0249-3	EM-PC-133, EM-SC-133, EM-PC-113(01), EM-SC-113(01)

Note 1 : About manual crimp tools

Applicable tool is JIS C 9711-compliant wire termination tool for interior wiring (commercially available).

Please use the recommend crimping tool as the performance may be affected by the type of the tool you are using.

#### Recommended crimp tools

Tool manufacturer	Part No.
Hozan Tool Industrial Co., Ltd.	P-75
Lobtex Co., Ltd.	AK15A
Nichifu Co., Ltd.	NH1

#### Manual crimp tool (Example)



### ●Contact removal tool



#### Notes on use of the connector

- 1. Always power off and disconnect the power cord before performing this work.
- 2. To maintain the waterproofness and cable clamp strength at a desired level, use a cable having a diameter within the specified diameter range. As the cable structure could also affect the performance, confirm the cable performance prior to actual use.
- 3. For procedure for use of harness, please contact our sales offices or service centers.



# HIROSE ELECTRIC CO.,LTD.

2-6-3,Nakagawa Chuoh,Tsuzuki-Ku,Yokohama-Shi 224-8540,JAPAN TEL: +81-45-620-3526 Fax: +81-45-591-3726

http://www.hirose.com

http://www.hirose-connectors.com