

Data sheet acquired from Harris Semiconductor SCHS035C – Revised September 2003

CMOS Quad Exclusive-OR Gate

High-Voltage Types (20-Volt Rating)

■ CD4030B types consist of four independent Exclusive-OR gates. The CD4030B provides the system designer with a means for direct implementation of the Exclusive-

The CD4030B types are supplied in 14-lead hermetic dual-in-line ceramic packages (F3A suffix), 14-lead dual-in-line plastic packages (E suffix), 14-lead small-outline packages (M, MT, M96, and NSR suffixes), and 14-lead thin shrink small-outline packages (PW and PWR suffixes).

MAXIMUM RATINGS, Absolute-Maximum Values:

DC SUPPLY-VOLTAGE RANGE, (VDD)


POWER DISSIPATION PER PACKAGE (PD):

CD4030B Types

Features:

- Medium-speed operation—tpHL, tpLH = 65 ns (typ.) at $V_{DD} = 10 \text{ V, C}_{L} = 50 \text{ pF}$
- 100% tested for quiescent current at 20 V
- Standardized, symmetrical output characteristics
- 5-V, 10-V, and 15-V parametric ratings
- Maximum input current of 1 µA at 18 V over full packagetemperature range; 100 nA at 18 V and 25°C
- Noise margin (over full package-temperature range):

■ Meets all requirements of JEDEC Tentative Standard No. 13B, "Standard Specifications for Description of 'B' Series CMOS Devices"



Applications:

- Even and odd-parity generators and checkers
- Logical comparators
- Adders/subtractors
- General logic functions


For T_A = +100°C to +125°C...... Derate Linearity at 12mW/°C to 200mW DEVICE DISSIPATION PER OUTPUT TRANSISTOR FOR TA = FULL PACKAGE-TEMPERATURE RANGE (All Package Types) 100mW OPERATING-TEMPERATURE RANGE (TA).....-55°C to +125°C STORAGE TEMPERATURE RANGE (T_{stg}).....-65°C to +150°C LEAD TEMPERATURE (DURING SOLDERING):

Voltages referenced to VSS Terminal)-0.5V to +20V

INPUT VOLTAGE RANGE, ALL INPUTS-0.5V to V_{DD} +0.5V DC INPUT CURRENT, ANY ONE INPUT ±10mA

At distance 1/16 ± 1/32 inch (1.59 ± 0.79mm) from case for 10s max +265°C


TERMINAL DIAGRAM Top View



RECOMMENDED OPERATING CONDITIONS

For maximum reliability, nominal operating conditions should be selected so that operation is always within the following ranges:

CHARACTERISTIC	LIM	:	
	MIN.	MAX.	UNITS
Supply-Voltage Range (For T _A = Full Package: Temperature Range)	3.	18	v



CD4030B Types

STATIC ELECTRICAL CHARACTERISTICS

CHARAC- TERISTIC	CONDITIONS			LIMITS AT INDICATED TEMPERATURES (°C)					UNI			
	v _o	VIN	V _{DD}					+25			Т	
	(v)	(V)	(V)	–55	-40	+85	+125	Min.	Тур.	Max.	s	
Quiescent	_	0,5	5	0.25	0.25	7.5	7.5		0.01	0.25		
Device		0,10	10	0.5	0.5	15	15	_	0.01	0.5	μA	
Current, I _{DD}	_	0,15	15	1	1	30	30	-	0.01	1	[
Max.	-	0,20	20	5	5	150	150	_	0.02	5		
Output Low (Sink)	0.4	0,5	5	0.64	0.61	0.42	0.36	0.51	1	_		
Current	0.5	0,10	10	1.6	1.5	1.1	0.9	1.3	2.6	_		
IOL Min.	1.5	0,15	15	4.2	4	2.8	2.4	3.4	6.8	-		
Output High	4.6	0,5	5	-0.64	-0.61	0.42		-0.51	-1	-	m	
(Source)	2.5	0,5	5	-2	-1.8	-1.3	-1.15	-1.6	-3.2	_	ŀ	
Current,	9.5	0,10	10	-1.6	-1.5	-1.1	-0.9	-1.3	-2.6		1	
IOH Min.	13.5	0,15	15	-4.2	-4	-2.8	-2.4	-3.4	-6.8		1	
Output Voltage:	_	0,5	5	0.05 – 0				0.05				
Low-Level,		0,10	10	0.05			-		0.05			
VOL Max.	-	0,15	15		0	.05		-	0	0.05	$]_{v}$	
Output Voltage:	_	0,5	5		4	.95		4.95	5		1 *	
High-Level,	_	0,10	10	9.95 9.95 10					_]		
V _{OH} Min.	_	0,15	15		14	.95		14.95	15	_		
Input Low Voltage, V _{IL} Max.	0.5,4.5	-	5		1	.5		_	_	1.5		
	1,9	1	10	3			-	-	3			
	1.5,13.5	-	15	4			_	_	4	l,		
Input High Voltage, V _{IH} Min.	0.5,4.5	_	5		3	3.5		3.5	_]	
	1,9	-	10			7	J	. 7	_	-		
	1.5,13.5	_	15			11		11	-			
Input Current IN Max.	-	0,18	18	±0.1	±0.1	±1	±1	_	±10 ⁻⁵	±0.1	μ/	

DYNAMIC ELECTRICAL CHARACTERISTICS at T $_A$ = 25°C; input t $_r$, t $_f$ = 20 ns, C $_L$ = 50 pF, R $_L$ = 200 K Ω

CHARACTERISTIC		CONDITIONS	LIMITS		UNITS	
		V _{DD} (V)				
			Тур.	Max.		
Propagation Delay Time,	^t PLH ^{, t} PHL	5	140	280	ns	
		10	65	130		
		15	50	100		
Transition Time,	tTHL ^{, t} TLH	5	100	200		
		10	50	100	ns	
		15	40	80		
Input Capacitance,	c _{IN}	Any Input	5	7.5	ρF	




Fig. 2 — Typical output low (sink) current characteristics.




Fig. 3 – Minimum output low (sink) current characteristics.




Fig. 4 — Typical output high (source) current characteristics.




Fig. 5 – Minimum output high (source) current characteristics.

CD4030B Types




Fig. 6 — Typical transition time as a function of load capacitance.




Fig. 7 — Typical propagation delay time as a function of load capacitance.




Fig. 8 — Typical propagation delay time as a function of supply voltage.




Fig. 9 — Typical dynamic power dissipation as a function of input frequency.




Fig. 10 - Quiescent-device current test circuit.




Fig. 11 - Input-voltage test circuit.




Fig. 12 - Input-current test circuit.





Fig. 13 – Dynamic power dissipation test circuit.



Dimensions and pad layout for CD4030BH.

Dimensions in parentheses are in millimeters and are derived from the basic inch dimensions as indicated. Grid graduations are in mils (10^{-3} inch).

14 LEADS SHOWN




NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

N (R-PDIP-T**)

16 PINS SHOWN

PLASTIC DUAL-IN-LINE PACKAGE



NOTES: A. All linear dimensions are in inches (millimeters).

B. This drawing is subject to change without notice.


Falls within JEDEC MS-001, except 18 and 20 pin minimum body Irngth (Dim A).

The 20 pin end lead shoulder width is a vendor option, either half or full width.

D (R-PDSO-G**)

PLASTIC SMALL-OUTLINE PACKAGE

8 PINS SHOWN



NOTES: A. All linear dimensions are in inches (millimeters).

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion, not to exceed 0.006 (0,15).

D. Falls within JEDEC MS-012

MECHANICAL DATA

NS (R-PDSO-G**)

14-PINS SHOWN

PLASTIC SMALL-OUTLINE PACKAGE



NOTES:


- . All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



PW (R-PDSO-G**)

14 PINS SHOWN

PLASTIC SMALL-OUTLINE PACKAGE



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.

D. Falls within JEDEC MO-153

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
		Telephony	www.ti.com/telephony
		Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments

Post Office Box 655303 Dallas, Texas 75265

Copyright © 2003, Texas Instruments Incorporated