Silicon PIN Photodiode

FEATURES

- Low capacitance
- High speed: $t_r = 30$ ns max. at $V_R = 5$ V; 10 ns max. at $V_R = 15$ V
- High responsivity
- · Housing electrically isolated
- Wave solderable
- · Mounting options

SMA single hole ST single hole SMA PCB ST PCB SMA 4 hole

DESCRIPTION

The HFD3002-002/XXX PIN Photodiode is designed for high speed use in fiber optic receivers. It has a large area detector, providing efficient response to 50 - 1000 mm diameter fibers at wavelengths of 650 to 950 nanometers. The HFD3002-002/XXX is comprised of an HFD3002 PIN photodiode which is mounted in a fiber optic connector which aligns the component's optical axis with the axis of the optical fiber.

The HFD3002-002/XXXs case is electrically isolated from the anode and cathode terminals to enhance the EMI/RFI shielding which increases the sensitivity and speed. The housing acts as a shield for the PIN photodiode component.



Silicon PIN Photodiode

ELECTRO-OPTICAL CHARACTERISTICS (T_C = 25°C unless otherwise stated)

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	TEST CONDITIONS
Peak Response Wavelength	λ_{P}		850		nm	
Flux Responsivity (1)	R				A/W	$\lambda = 850 \text{ nm}$
			0.6			50 μm core fiber, 0.20 μA
		0.45	0.6			100 μm core fiber, 0.28 μA
			0.55			200 μm core fiber, 0.40 μA
			0.30			1000 µm core fiber, 0.53 µA
Dark Leakage Current	I _D		0.05	2	nA	$V_R = 5 V$
Reverse Breakdown Voltage	B _{VR}	110	250		V	$I_R = 10 \text{ mA}$
Package Capacitance	С		1.4		pF	$V_R = 5 V, f = 1 MHz$
Rise Time	t _R				ns	
10-90%			17	30		$V_R = 5 V$
			5	10		$V_{R} = 15 \text{ V}$
			1			$V_{R} = 90 \text{ V}$
Field of View	FoV		85		Degrees	

Notes

ABSOLUTE MAXIMUM RATINGS

(Tcase = 25°C unless otherwise noted)

Storage temperature -65 to +150°C


Operating temperature -55 to +125°C

Lead solder temperature 260°C for 10 s

Case/cathode (anode) voltage 110 V

Case/cathode (anode) voltage 110 V
Power dissipation 200 mW
Reverse voltage 110 V

Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods of time may affect reliability.





^{1.} Responsivity is measured with a fiber optic cable centered on the mechanical axis, using an 850 nm LED as the optical source to the fiber

Silicon PIN Photodiode

ORDER GUIDE

Description	Catalog Listing
Standard silicon PIN photodiode	HFD3002-002/XXX

MOUNTING OPTIONS

Substitute XXX with one of the following 3 letter combinations

 SMA single hole
 - AAA

 ST single hole
 - BAA

 SMA PCB
 - ABA

 ST PCB
 - BBA

 SMA 4 hole
 - ADA

 Dimensions on page 441


CALITION

Fig. 1

The inherent design of this component causes it to be sensitive to electrostatic discharge (ESD). To prevent ESD-induced damage and/or degradation to equipment, take normal ESD precautions when handling this product.




Rise/Fall Time vs Reverse Bias Voltage




FIBER INTERFACE


Honeywell detectors are designed to interface with multimode fibers with sizes (core/cladding diameters) ranging from 50/125 to 200/230 microns. Honeywell performs final tests using 100/140 micron core fiber. The fiber chosen by the end user will depend upon a number of application issues (distance, link budget, cable attenuation, splice attenuation, and safety margin). The 50/125 and 62.5/125 micron fibers have the advantages of high bandwidth and low cost, making them ideal for higher bandwidth installations. The use of 100/140 and 200/230 micron core fibers results in greater power being coupled by the transmitter, making it easier to splice or connect in bulkhead areas. Optical cables can be purchased from a number of sources.


Fig. 2 Package Capacitance vs Reverse Bias Voltage



Silicon PIN Photodiode








European Connectorized Receivers

Honeywell receiver components are available in the following connector styles. Each style has a three-digit reference used in the order guides.


SMA SINGLE HOLE MOUNTING (REF.: AAA)







ST SINGLE HOLE MOUNTING (REF.: BAA)





SMA PCB MOUNTING (REF.: ABA)






Honeywell Optoelectronics reserves the right to make changes at any time in order to improve design and supply the best products possible.

European Connectorized Receivers

ST PCB MOUNTING (REF.: BBA)



SMA 4 HOLE MOUNTING (REF.: ADA)



