

date 07/15/2015

page 1 of 11

SERIES: PSA-1100 **DESCRIPTION:** AC-DC HOT-SWAP POWER SUPPLY

FEATURES

- up to 1100 W continuous power
- high power density 25.34 W/in³
- slim line 1U form factor
- PMBus[™] communication for monitoring and control
- front to back (-F) and back to front (-B) airflow versions
- power factor correction
- 3.3 Vdc or 5 Vdc standby voltage (2 A) options
- redundant (N+1) operation
- blind mate connections for hot-swap
- DROOP current sharing or forced current sharing (optional)
- remote on/off control, power good signal












MODEL	output voltage	output current	output power	ripple and noise¹	efficiency ²
	(Vdc)	max (A)	max (W)	max (mVp-p)	typ (%)
PSA-1100-12-F	12	92	1100	120	93.5
PSA-1100-12-B ^{3,4,5}	12	92	1100	120	93.5

Notes: 1. Measured at 20 MHz bandwidth at an oscilloscope jack on the output with 0.1 µF ceramic and two 180 µF polymer capacitors at a 2" distance from V1 output connector.

2. At 230 Vac input, 550 W.

- 3. At $100\sim240$ Vac input, maximum of 1100 W at Ta=29°C. 4. At $100\sim240$ Vac input, maximum of 740 W at Ta=50°C.
- 5. At 200~240 Vac input, maximum of 1100 W at Ta=48°C.
- 6. All specifications measured at: Ta=25°C and 220 Vac input voltage unless otherwise specified.

PART NUMBER KEY



F = AC input connector to DC output connector B = DC output connector to AC input connector

INPUT


parameter	conditions/description	min	typ	max	units
voltage		90		264	Vac
frequency		47		63	Hz
current	at 90 Vac at 180 Vac			14.4 8.0	Arms Arms
inrush current	at 115 Vac, cold start at 230 Vac, cold start		20 40		A A
leakage current				1.5	mArms
power factor correction	at 115 Vac, full load	0.95			

OUTPUT - V1 (MAIN OUTPUT)

parameter	conditions/description	min	typ	max	units
line regulation			±1.5		%
load regulation			±1.5		%
load capacitance				30,000	μF
transient response	25% step load, 1A/µs slew rate, recovery to 1% within 1 ms			5	%
start-up time				1.5	S
hold-up time	at 230 Vac, full load	12			ms
remote sense	between both output terminals		0.3		V
current share accuracy (Droop) ¹	over 10% to 100% load		±4		А
LED in disease.	AC OK: "green" to indicate AC above the lower limit that is required to sustain normal operation				
LED indicator	DC OK: "green" to indicate module in normal operating condition				

Notes: 1. Droop regulation of $\pm 1.0\%$ for an overall combined regulation allowance of $\pm 1.5\%$

PSA-1100 Droop Regulation Profile



Module % Full Load Current

OUTPUT - V2 (STANDBY OUTPUT)

parameter	conditions/description	min	typ	max	units
output voltage	selectable		3.3/5		Vdc
output current		0		2	А
ripple and noise ²				100	mVp-p
line regulation			±2		%
load regulation			±2		%
load capacitance				2200	μF
transient response	25% step load, 1A/ μ s slew rate, recovery to 1% within 1 ms			5	%
start-up time				1.5	S

Notes: 2. Measured at 20 MHz bandwidth at an oscilloscope jack on the output with 100 µF low ESR capacitor at 0.5" from V2 output connector.

PROTECTIONS

parameter	conditions/description	min typ	max max	units
over voltage protection	V1: latch off V2: latch off	13.2 110	14.5 120	Vdc %
over current protection	V1: auto recovery V2	101.2	128.8 3	A A
over temperature protection	auto recovery	55		°C

SAFETY & COMPLIANCE

parameter	conditions/description	min	typ	max	units				
insulation safety rating / test voltage	input to output, reinforced input to chassis, basic		Vrms Vrms						
isolation voltage	output to chassis V2 to chassis/ground								
grounding	the output signals are referenced to the A return connection	A2 and B2							
safety approvals	EN60950-1:2006+A11+A1+A12, IEC6099 CAN/CSA-C22.2 No.60950-1-07+A1:2013 R12.11(NRTL Route), EEC/93/68/LVD, 20	1, UL 60950-1:2007							
conducted emissions	FCC 15 Sub Part B, EN55022, Class A: tes	sted with resistive load							
radiated emissions	FCC 15 Sub Part B, EN55022, Class A: tes	sted with resistive load							
harmonic compliance	EN/IEC 61000-3-2:2009, Class A Harmon Compliance Level: 230 Vac line voltage; 1								
flicker	EN/IEC 61000-3-3:2009 limits as specifie flicker and voltage fluctuations	d in the standard:							
electrostatic discharge	EN/IEC 61000-4-2, ±8 kV operational air contact discharge: all parameters to remaset up to be defined								
RF electro-magnetic field. amplitude modulated	EN/IEC 61000-4-3 80~1000 MHz, 10 V/m Modulation (1 kHz): all parameters to renset up to be defined								
immunity to fast transients	EN/IEC 61000-4-4 Power lines: ±2 kV: al within limits, test set up to be defined	l parameters to remain							
surges (mains)	EN/IEC $61000-4-5 \pm 1 \text{kV}$ line to line, $\pm 2 \text{ k}$ Criteria A: all parameters to remain within be defined								
RF continuous conducted	EN/IEC 61000-4-6 150 kHz~80 MHz 3Vrn Criteria A: all parameters to remain within be defined								
voltage dips/ interruptions	IEC 61000-4-11 30% reduction for 10 ms 100 ms: Reset is permitted must be selfre the PSU shall not latch up during any brown	ecovering. Additionally,							
MTBF	as per Telcordia SR-332, Issue 2, Sept 20 component stress method at Ta=40°C, fu				hours				
RoHS	2011/65/EU								
WEEE	2012/19/EU								

ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature ¹		0		50	°C
storage temperature	non-condensing	-40		70	°C
operating humidity	non-condensing	10		90	%
storage humidity		5		90	%

Notes: 1. PSA-1100-12-B: At 100~240 Vac input, maximum of 1100 W at Ta=29°C. At 100~240 Vac input, maximum of 740 W at Ta=50°C. At 200~240 Vac input, maximum of 1100 W at Ta=48°C.

ENVIRONMENTAL (CONTINUED)

parameter	conditions/description	min	typ	max	units
acoustic	ISO 7779-1999			60	dB LpAm
cold ¹	IEC 68 Part 2 – 1: at -10°C minimum for 4 hours				
dry heat	IEC 68 Part 2 – 2: at 50°C minimum for 4 hours				
damp heat, cyclic	IEC 68 Part 2 - 30: at 20~45°C, 30~95 %RH				
low air pressure (operating)	IEC 68 Part 2 - 13: at 10,000 feet, 697 mbar				
vibration (sinusoidal)	IEC 68 Part 2 – 6: at 10~58 Hz, 0.075 mm; 58~500 Hz, 10 m/s², 1 octave/minute, 10 cycles/ main axis	EC 68 Part 2 – 6: at 10~58 Hz, 0.075 mm; 8~500 Hz, 10 m/s², 1 octave/minute, 10 cycles/			
shock	IEC 68 Part 2 – 27: at 300 m/s², 11 ms, half sine wave 3 shocks/main axis		30		G
bump	IEC 68 Part 2 – 29: at 150 m/s², 6 ms, half sine wave 900 bumps/main axis				G

Notes: 1. The module shall start up at -10°C, however it is not required that the full specification is achieved until the operational internal temperature has risen to 0°C.

MECHANICAL


parameter	conditions/description	min	typ	max	units		
dimensions	12.65 x 2.145 x 1.575 (321.3 x 54.5 x 40.0 mm)				inches		
weight			1.1		kg		
cooling / airflow	integral fan						
material flammability	UL 94V-0						
AC input	IEC320/C14						
DC output	Tyco Electronics P/N 2-1926734-2 mates with Tyco Electronics P/N 2-1926739-5						


MECHANICAL DRAWING

units: inches [mm] tolerance:

X.XX ±0.02 [0.50] X.XXX ±0.010 [0.25]







DC OUTPUT PIN ASSIGNMENTS

PII	N	FUNCTION	DESCI	RIPTION	HIGH / LOW LEVEL	Imax
1,2,3	,4,5	12 V output return	V1 (-VE) mai	n output return		
6,7,8,	9,10	12 V output	V1 (+VE)	main output		
	A1	Vstandby +VE	positive output	of standby (V2)		
	A2	signal/logic return	common with	V1 & V2 returns		
Ī	А3	I ² C address select	analog I ² C ad	ldress selection		
signal	A4	SCL	communicat	ions clock line		
signal pin row			disables power on ex	traction (recessed pin)		
"A"			pin status	module		
	A5	PSKILL_H	open circuit	"off"		
			logic "1"	"off"		
			logic "0"	"on"		
	B1	Vstandby +VE	positive output	of standby (V2)		
İ	B2	signal/logic return	common with	V1 & V2 Returns		
	B3	not use	res	erved		
signal pin row "B"		PS_ON_L	internally pulled up PSKILL_H is co	to 3.3 V via 3.01 kΩ if nnected to return		
	B4	(remote_ON_L)	open to A2/B2	short to A2/B2		
		/	"off"	"on"		1.05 mA
	B5	Ishare (optional)	active current shari	ng bus (recessed pin)		
	C1	Vstandby +VE		positive output of standby (V2)		
ļ	C2	not use		erved		
Ì	C3	SDA	communic	cations data		
-:			SMBus interrupt line			
signal pin row	C4	SMB_ALERT_L	logic "1"	"good"	>2.1 V	
"C"			logic "0"	"fault"	<0.4 A	-5 mA
İ			DC OK Signal	(recessed pin)		
	C5	DC_OK_H	logic "1"	"good"	>2.1 V	
			logic "0"	"fault"	<0.4 A	-5 mA
	D1	Vstandby +VE	positive output	of standby (V2)		
Ì	D2	not use		erved		
-:	D3	V1 Vsense (-VE)	V1 negativ	ve sense line		
signal pin row	D4	not use	-	erved		
. "D"			selects the voltage	e of V2 recessed pin		
	D5	Vstandby_select	open circuit	short circuit		
		(V2)	3.3 V	5 V		
	E1	Vstandby +VE	positive output	of standby (V2)		
ļ	E2	not use		erved		
ļ	E3 V1 Vsense (+VE)			e sense line		
signal			· ·	source alarm		
pin row "E"	E4	AC_OK_H	logic "1"	"good"	> 2.1 V	
			logic "0"	"fault"	< 0.4 A	-5 mA
-	E5	PS_present	active low, recessed pin,	passive signal to detect p	presence of module, host t m of 5 mA when module i	o provide pull u

APPLICATION NOTES

Digital Interface

The PSA-1100 is provided with a digital communications interface that is based upon a subset of the SMBus™ & PMBus™ Protocols.

The communication interface is a Two Wire Interface (TWI) using devices hardware compatible with I2C.

The interface is based upon the I²C Protocol developed by Philips Semiconductors (now NXP). Reference to the "I²C Bus Specification and User Manual" UM10204 Rev.03 - 19 June 2007 is recommended.

Slave Addresses

The device is selected by setting the Slave Address (Pin A3) either by an external resistor network or by direct connection to logic "high" or "low". Either method interfaced to the appropriate I/O port of the internal I²C device. Therefore the device can be set to respond to all addresses in the range from binary 1011 0000 to 1011 0110 (where the last bit is for read/ write that is always set at "0" for initial addressing).

- Connection of Pin A3 to a logic "low" will provide an address of B0 (1011 0000)
- Connection of Pin A3 to a logic "high" (or leaving open circuit) will provide an address of B6 (1011 0110)

To achieve the full range of four potential address combinations Pin A3 requires to be connected to an external resistor that will create an internal analogue voltage that is interpreted by the internal I²C device to derive the following address combinations:

	Possible Module Slave Address Combinations										
External Resistor Value (Ohms)					Bits	R/W	HEX				
	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0			
820	1	0	1	1	0	0	0	0	В0		
2700	1	0	1	1	0	0	1	0	B2		
5600	1	0	1	1	0	1	0	0	B4		
8200	1	0	1	1	0	1	1	0	В6		

APPLICATION NOTES (CONTINUED)

General Information

Refer to the PMBus™/SMBus specification for details on read/write operations when dealing with Byte, Word or Block process calls. Packet Error Correction (PEC) and Address Resolution Protocol (ARP) are not supported. If the PMBus™ master tries to read more bytes than the length of the data selected by the command code, the additional bytes will be sent as 0xFF. The PMBus™ slave device may apply clock stretching by holding the clock line (SCL) low after a command to indicate that it is busy processing data. A master device on the PMBus™ may attempt to continue with the communications but must first wait until the clock line is released. Clock stretching times will vary depending on the data being processed and/or if there are any higher priority events during the response but shall not exceed 25 ms.

PMBus™ COMMAND SUBSET

The following is subset of commands (extracted from the "PMBus Power System Management Protocol Specification; Part II Command Language; Rev 1.2, 6 September 2010") and apply on a per module basis, (although certain commands could be applied "globally"). For a full definition of the individual command refer to the above referenced PMBus™ specification.

Note: Hex Command 88h, 89h, 8Bh, 8Ch divide decimal value by 100.

Command (HEX)	Command Name	No. of Bytes	Read / Write	Command Description
01h	OPERATION	1	w	The OPERATION command is used to turn the unit on & off in conjunction with the CONTROL (short; last make, first make pin). The unit remains in the commanded mode until the command is toggled or the unit removed from its slot; in which case the CONTROL pin is de-asserted and overrules the OPERATION command.
03h	CLEAR_FAULTS	0	W	Clear fault data
78h	STATUS_BYTE	1	R	Lower byte returned from the STATUS_WORD
79h	STATUS_WORD	2	R	The command returns two bytes of data relating to the unit fault condition. CUI may elect to provide a subset of information.
88h	READ_VIN	2	R	Provides the measured input voltage of the power module in volts.
89h	READ_IIN	2	R	Provides the measured input current of the power module in Amps.
8Bh	READ_VOUT	2	R	Provides the measured output voltage of the power module in volts.
8Ch	READ_IOUT	2	R	Provides the measured output current of the power module in Amps.
8Dh	READ_TEMPERATURE_1	2	R	This command shall return a select component temperature used by the power module, in degrees Celsius.
8Eh	READ_TEMPERATURE_2	2	R	This command shall return the prevailing internal ambient of the power module, in degrees Celsius.
90h	READ_FAN_SPEED_1	2	R	Provides the measured fan speed in the power module in RPM.
96h	READ_POUT	2	R	This command shall return the calculated output being delivered by the power module, in Watts.
97h	READ_PIN	2	R	This command shall return the calculated input being drawn by the power module, in Watts.
98h	PMBUS_REVISION	1	R	PMBus™ Revision
99h	MFR_ID	8	R	The command returns the ASCII string for manufacturer's ID.
9Ah	MFR_MODEL	12	R	The command returns the ASCII string manufacturer's model.
9Bh	MFR_REVISION	2	R	The command returns the ASCII string manufacturer's revision (example case "01").
9Dh	MFR_DATE	4	R	The command returns the ASCII string manufacturer's date code (example case "0913").
9Eh	MFR_SERIAL	8	R	The command returns manufacturers serial number.

APPLICATION NOTES (CONTINUED)

PMBus™ Non-Standard Extended Command Subset

Command (HEX)	Command Name	No. of Bytes	Read / Write	Command Description
16h	SOFTWARE VERSION	4	R	Read vendor specific firmware revision (ASCII string). Example case "A100"

Remote On/Off (PMBus™ Operation Command 0x01)

This command can be used to turn the unit on and off via the PMBus™ interface.

If B4 (REMOTE_ENABLE) is HIGH (enabled) then the PMBus™ Remote On/Off function can turn the unit off and on. If B4 (REMOTE_ENABLE) is LOW (disabled) then the PMBus $^{\text{TM}}$ Remote On/Off function cannot turn the unit on or off and can be ignored.

The bit encoding of the data byte of the command is as follows.

Bits [7:6]	Bits [5:4]	Bits [3:2]	Bits [1:0]	Unit State
00	XX	XX	XX	Off
01	XX	XX	XX	Off
10	00	XX	XX	On
10	01	01	XX	On
10	01	10	XX	On
10	10	01	XX	On
10	10	10	XX	On

If any other bit pattern is received take no action.

If the power supply is turned off by this command then set the OFF bit (6 of the low byte) of the status word to 1. Otherwise set it to 0.

APPLICATION NOTES (CONTINUED)

Status Word

This command is a two byte structure (High and Low bytes). The PMBus™ specification (Table 15) details the structure and content of the word. Note that unsupported bits shall be set to "0"

Status Word (79h); Low Byte

Byte	Bit #	PMBus™ Bit Name	Definition
	Bit 7	BUSY	Not Supported
	Bit 6	OFF	Pulse Width Modulator enable status: 1 = PWM disabled 0 = PWM enabled
	Bit 5	VOUT_OV	Output over voltage fault 1 = OVP has occurred 0 = OVP has not occurred
Low	Bit 4	IOUT_OC	OCP; the unit has entered overload protection. 1 = OCP has occurred 0 = OCP has not occurred
	Bit 3	VIN_UV	Incoming AC under voltage: 1 = AC is not OK 0 = AC is OK
	Bit 2	TEMPERATURE	Over Temperature fault 1 = OTP has occurred 0 = OTP has not occurred
	Bit 1	CML	Not Supported
	Bit 0	NONE OF THE ABOVE	Not Supported

Status Word; High Byte

Byte	Bit #	PMBus™ Bit Name	Definition
	Bit 7	VOUT	Voltage Fault or Warning uVP fault only
	Bit 6	IOUT/POUT	Not Supported
	Bit 5	INPUT	Not Supported
	Bit 4	MFR	Auxiliary Specific Failure
High	Bit 3	POWER_GOOD#	Not Supported
-	Bit 2	FAN	Fan Failure 1 = Fan has failed 0 = Fan has not failed
	Bit 1	OTHER	Not Supported
	Bit 0	UNKNOWN	Not Supported

DEMO BOARD

Accessories				
Description	CUI Part Number	Vendor/Part Number		
Demo Board¹	01T-156801-1			
DC Output Mating Connector	22P-S00065-4	TEConn 2-1926739-5		
I ² C dongle ²		Microchip DV164122		
AC power cord ³		Qualtek 312019-01		

Notes:

J1

J2

J6

1. This demo board is intended for user connection to evaluate the power supply in the laboratory by qualified personnel. Please take necessary safety precautions during product evaluation.

2. The PICkit Serial Analyzer is an USB-based tool used to direct communication between a PC and an external serial device. The kit comes complete with hardware (supporting I2C™, SMBus, SPI and USART protocols), an easy-to-use GUI (to configure and display communications) and a target demonstration board for out-of-the-box functionality. http://www.microchip.com/stellent/idcplg?IdcService=SS_GET_PAGE&nodeId=1406&dDocName=en028600

3. For North American use only

Demo Board Power Connections

+ Standby Output

+12V Output

12V Return

J7	Standby Output Return
	1.500 1.600
2.800	P3 P4 P4 P5 P8 P8 P9 R1 P9 R1 R2 P9 ISHARE SENSE SENSE P2 LRTN REM PRES PAC PAC DC OK NC PAC DC NC DC NC DC NC DC DC NC DC NC DC NC DC NC DC D
	2.850

Dei	no	Board Connections/Settings		
P1		DC Output Mating Connector		
P2		Control & Status Signals		
	1	Logical Return		
	2	Remote ON (override by P7)		
	3	Present		
	4	AC_OK		
	5	DC_OK		
	6	NC		
Р3		I ² C Dongle Connection		
	1	SMB		
	2	SCL		
	3	SDA		
	4	Logical Return		
	5	VDD		
	6	NC		
P4		Jumper to Local Sense+, remove jumper for remote sense		
P5		Jumper to Local Sense-, remove jumper for remote sense		
P6		Jumper to Select 5V Standby, remove jumper to set 3.3V Standby		
Р7		Jumper to ON, remove jumper for Remote ON/OFF		
P8		Jumper to set I^2C A0 = 0, remove jumper to set address by host		
Р9		Control & Status Signals		
	1	NC		
	2	NC		
	3	NC		
	4	ISHARE (optional force sharing)		
	5	SENSE+ (override by P4)		
	6	SENSE- (override by P5)		

Additional Resources: Product Page | 3D Model

CUI Inc | SERIES: PSA-1100 | DESCRIPTION: AC-DC HOT-SWAP POWER SUPPLY date 07/15/2015 | page 11 of 11

REVISION HISTORY

rev.	description	date
1.0	initial release	05/07/2015
1.01	updated datasheet	07/15/2015

The revision history provided is for informational purposes only and is believed to be accurate.



Headquarters 20050 SW 112th Ave. Tualatin, OR 97062 **800.275.4899**

Fax 503.612.2383 **cui**.com techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.